



OA825 Series



80 x 25mm
(3.15" x 1.0")



Frame	Diecast Aluminum	<u>Operating Temperature</u> Ball Bearing -20C ~ +80C Sleeve Bearing -10C ~ +50C <u>Life Expectancy</u> Ball Bearing 60,000 hours (L10 at 40C) Sleeve Bearing 30,000 hours (L10 at 40C) <u>Dual Voltage</u> Connection via 4x leads. Fans can be configured for 115V or 230V operation.		
Impeller	PBT, UL94V-O plastic			
Connection	2x Lead Wires 22 AWG or terminals			
Motor	Shaded pole, impedance protected	m0		
Bearing System	Dual ball or Sleeve			
Insulation Resistance	>100M ohm between lead-wire and frame (500VDC)			
Dielectric Strength	1 min at 1500 VAC, 50/60Hz			

Model Number	Speed (RPM)	Airflow (CFM)	Noise (dB)	Volts AC	Voltage Range	Watts	Max. Static Pressure (\"H2O)
OA825AP-11-1*	3000	25	28	115	80~130	9	.21
OA825AP-11-2*	2300	18	24	115	80~130	6	.14
OA825AP-11-3*	1900	16	19	115	80~130	4	.11
OA825AP-22-1*	3000	25	28	230	160~260	9	.21
OA825AP-22-2*	2300	18	24	230	160~260	6	.14
OA825AP-22-3*	1900	16	19	230	160~260	4	.11
OA825AP-11/22-1W**	3000	25	28	115/230	80~260	9	.21
OA825AP-11/22-2W**	2300	18	24	115/230	80~260	6	.14
OA825AP-11/22-3W**	1900	16	19	115/230	80~260	4	.11

* Indicate "TB" (Terminal Ball Bearing), "WB" (12" Wire Leads, Ball Bearing), "TS" (Terminal, Sleeve Bearing), "WS" (12" Wire Leads, Sleeve Bearing)
 ** Indicate "B" (Ball Bearing) or "S" (Sleeve Bearing)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OA825AP-22-3TB](#) [OA825AP-11-1TB](#) [OA825AP-11-1WB](#) [OA825AP-11-3TB](#) [OA825AP-11-3WB](#) [OA825AP-22-1TB](#)
[OA825AP-22-1WB](#) [OA825AP-22-2WB](#) [OA825AP-22-2TB](#) [OA825AP-11-2WB](#) [OA825AP-22-3WB](#) [OA825AP-11-2TB](#)
[OA825AP-11/22-1WB](#) [OA825AP-1/2-1WB](#) [OA825AP-1/2-3WB](#) [OA825AP-1/2-2WB](#)