


LXQ Series

- Endurance with ripple current : 5,000 hours at 105°C
- Downsized and higher ripple version of LXG series
- Non solvent resistant type
- RoHS Compliant




SPECIFICATIONS


Items	Characteristics			
Category	Temperature Range			
Temperature Range	-25 to +105°C			
Rated Voltage Range	160 to 450V _{dc}			
Capacitance Tolerance	±20% (M)		(at 20°C, 120Hz)	
Leakage Current	I ≤ 3√CV Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20°C after 5 minutes)			
Dissipation Factor (tanδ)	Rated voltage (V _{dc})	160 to 400V	420 & 450V	(at 20°C, 120Hz)
	tanδ (Max.)	0.15	0.20	
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (V _{dc})	160 to 400V	420 & 450V	(at 120Hz)
	Z(-25°C)/Z(+20°C)	4	8	
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for 5,000 hours at 105°C.			
	Capacitance change	≤±20% of the initial value		
	D.F. (tanδ)	≤200% of the initial specified value		
	Leakage current	≤The initial specified value		
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.			
	Capacitance change	≤±15% of the initial value		
	D.F. (tanδ)	≤150% of the initial specified value		
	Leakage current	≤The initial specified value		

DIMENSIONS [mm]

Terminal Code : VS (φ22 to φ35) : Standard




Terminal Code : LI (φ30, φ35)



The standard design has no plastic disc.

PART NUMBERING SYSTEM



Please refer to "Product code guide (snap-in type)"

◆ **STANDARD RATINGS**

WV (Vdc)	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/ 105°C, 120Hz)	Part No.	WV (Vdc)	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/ 105°C, 120Hz)	Part No.
160	390	22×25	0.15	1.32	ELXQ161VSN391MP25S	200	1,200	30×50	0.15	2.88	ELXQ201VSN122MR50S
	560	22×30	0.15	1.66	ELXQ161VSN561MP30S		1,200	35×35	0.15	2.88	ELXQ201VSN122MA35S
	560	25.4×25	0.15	1.68	ELXQ161VSN561MQ25S		1,500	35×40	0.15	3.34	ELXQ201VSN152MA40S
	680	22×35	0.15	1.87	ELXQ161VSN681MP35S		1,800	35×45	0.15	3.74	ELXQ201VSN182MA45S
	680	25.4×30	0.15	1.88	ELXQ161VSN681MQ30S		1,800	35×50	0.15	3.82	ELXQ201VSN182MA50S
	680	30×25	0.15	1.96	ELXQ161VSN681MR25S	220	270	22×25	0.15	1.10	ELXQ221VSN271MP25S
	820	22×40	0.15	2.09	ELXQ161VSN821MP40S		330	22×30	0.15	1.19	ELXQ221VSN331MP30S
	1,000	22×45	0.15	2.36	ELXQ161VSN102MP45S		390	25.4×25	0.15	1.39	ELXQ221VSN391MQ25S
	1,000	22×50	0.15	2.41	ELXQ161VSN102MP50S		470	22×35	0.15	1.55	ELXQ221VSN471MP35S
	1,000	25.4×35	0.15	2.38	ELXQ161VSN102MQ35S		470	25.4×30	0.15	1.56	ELXQ221VSN471MQ30S
	1,000	30×30	0.15	2.40	ELXQ161VSN102MR30S		470	30×25	0.15	1.63	ELXQ221VSN471MR25S
	1,000	35×25	0.15	2.55	ELXQ161VSN102MA25S		560	22×40	0.15	1.73	ELXQ221VSN561MP40S
	1,200	25.4×40	0.15	2.66	ELXQ161VSN122MQ40S		560	30×30	0.15	1.79	ELXQ221VSN561MR30S
	1,200	25.4×45	0.15	2.71	ELXQ161VSN122MQ45S		680	22×45	0.15	1.94	ELXQ221VSN681MP45S
	1,200	30×35	0.15	2.69	ELXQ161VSN122MR35S		680	22×50	0.15	1.99	ELXQ221VSN681MP50S
	1,200	30×40	0.15	2.77	ELXQ161VSN122MR40S		680	25.4×35	0.15	1.96	ELXQ221VSN681MQ35S
	1,200	35×30	0.15	2.86	ELXQ161VSN122MA30S		680	30×35	0.15	2.02	ELXQ221VSN681MR35S
	1,500	25.4×50	0.15	3.08	ELXQ161VSN152MQ50S		680	35×25	0.15	2.10	ELXQ221VSN681MA25S
	1,500	30×45	0.15	3.17	ELXQ161VSN152MR45S		820	25.4×40	0.15	2.20	ELXQ221VSN821MQ40S
	1,500	35×35	0.15	3.22	ELXQ161VSN152MA35S		820	25.4×45	0.15	2.24	ELXQ221VSN821MQ45S
	1,800	30×50	0.15	3.53	ELXQ161VSN182MR50S		820	30×40	0.15	2.29	ELXQ221VSN821MR40S
	1,800	35×40	0.15	3.66	ELXQ161VSN182MA40S		820	35×30	0.15	2.36	ELXQ221VSN821MA30S
	2,200	35×45	0.15	4.14	ELXQ161VSN222MA45S		1,000	25.4×50	0.15	2.51	ELXQ221VSN102MQ50S
	2,700	35×50	0.15	4.68	ELXQ161VSN272MA50S		1,000	30×45	0.15	2.59	ELXQ221VSN102MR45S
180	330	22×25	0.15	1.21	ELXQ181VSN331MP25S		1,000	35×35	0.15	2.63	ELXQ221VSN102MA35S
	470	22×30	0.15	1.52	ELXQ181VSN471MP30S	250	1,200	30×50	0.15	2.88	ELXQ221VSN122MR50S
	470	25.4×25	0.15	1.52	ELXQ181VSN471MQ25S		1,200	35×40	0.15	2.98	ELXQ221VSN122MA40S
	560	22×35	0.15	1.70	ELXQ181VSN561MP35S		1,500	35×45	0.15	3.41	ELXQ221VSN152MA45S
	560	30×25	0.15	1.78	ELXQ181VSN561MR25S		1,800	35×50	0.15	3.82	ELXQ221VSN182MA50S
	680	22×40	0.15	1.91	ELXQ181VSN681MP40S	315	220	22×25	0.15	1.01	ELXQ251VSN221MP25S
	680	25.4×30	0.15	1.88	ELXQ181VSN681MQ30S		270	22×30	0.15	1.20	ELXQ251VSN271MP30S
	820	22×45	0.15	1.99	ELXQ181VSN821MP45S		330	25.4×25	0.15	1.32	ELXQ251VSN331MQ25S
	820	25.4×35	0.15	2.16	ELXQ181VSN821MQ35S		390	22×35	0.15	1.44	ELXQ251VSN391MP35S
	820	30×30	0.15	2.17	ELXQ181VSN821MR30S		390	25.4×30	0.15	1.43	ELXQ251VSN391MQ30S
	820	35×25	0.15	2.31	ELXQ181VSN821MA25S		390	30×25	0.15	1.51	ELXQ251VSN391MR25S
	1,000	22×50	0.15	2.25	ELXQ181VSN102MP50S		470	22×40	0.15	1.62	ELXQ251VSN471MP40S
	1,000	25.4×40	0.15	2.43	ELXQ181VSN102MQ40S		560	22×45	0.15	1.80	ELXQ251VSN561MP45S
	1,000	25.4×45	0.15	2.47	ELXQ181VSN102MQ45S		560	22×50	0.15	1.84	ELXQ251VSN561MP50S
	1,000	30×35	0.15	2.46	ELXQ181VSN102MR35S		560	25.4×35	0.15	1.78	ELXQ251VSN561MQ35S
	1,200	25.4×50	0.15	2.75	ELXQ181VSN122MQ50S		560	30×30	0.15	1.83	ELXQ251VSN561MR30S
	1,200	30×40	0.15	2.77	ELXQ181VSN122MR40S		560	35×25	0.15	1.91	ELXQ251VSN561MA25S
	1,200	35×30	0.15	2.86	ELXQ181VSN122MA30S		680	25.4×40	0.15	2.00	ELXQ251VSN681MQ40S
	1,500	30×45	0.15	3.17	ELXQ181VSN152MR45S		680	25.4×45	0.15	2.04	ELXQ251VSN681MQ45S
	1,500	30×50	0.15	3.22	ELXQ181VSN152MR50S		680	30×35	0.15	2.06	ELXQ251VSN681MR35S
	1,500	35×35	0.15	3.22	ELXQ181VSN152MA35S		680	35×30	0.15	2.15	ELXQ251VSN681MA30S
	1,800	35×40	0.15	3.66	ELXQ181VSN182MA40S		820	25.4×50	0.15	2.28	ELXQ251VSN821MQ50S
	1,800	35×45	0.15	3.74	ELXQ181VSN182MA45S		820	30×40	0.15	2.33	ELXQ251VSN821MR40S
	2,200	35×50	0.15	4.22	ELXQ181VSN222MA50S		820	30×45	0.15	2.39	ELXQ251VSN821MR45S
200	270	22×25	0.15	1.10	ELXQ201VSN271MP25S		820	35×35	0.15	2.38	ELXQ251VSN821MA35S
	390	22×30	0.15	1.38	ELXQ201VSN391MP30S	315	1,000	30×50	0.15	2.68	ELXQ251VSN102MR50S
	390	25.4×25	0.15	1.39	ELXQ201VSN391MQ25S		1,000	35×40	0.15	2.72	ELXQ251VSN102MA40S
	470	22×35	0.15	1.55	ELXQ201VSN471MP35S		1,200	35×45	0.15	3.05	ELXQ251VSN122MA45S
	560	22×40	0.15	1.73	ELXQ201VSN561MP40S		1,500	35×50	0.15	3.49	ELXQ251VSN152MA50S
	560	25.4×30	0.15	1.71	ELXQ201VSN561MQ30S		150	22×25	0.15	0.80	ELXQ3B1VSN151MP25S
	560	30×25	0.15	1.78	ELXQ201VSN561MR25S		180	22×30	0.15	0.92	ELXQ3B1VSN181MP30S
	680	22×45	0.15	1.81	ELXQ201VSN681MP45S		180	25.4×25	0.15	0.94	ELXQ3B1VSN181MQ25S
	680	25.4×35	0.15	1.87	ELXQ201VSN681MQ35S		220	22×35	0.15	1.04	ELXQ3B1VSN221MP35S
	680	30×30	0.15	1.98	ELXQ201VSN681MR30S		220	30×25	0.15	1.17	ELXQ3B1VSN221MR25S
	680	35×25	0.15	2.10	ELXQ201VSN681MA25S		270	22×40	0.15	1.18	ELXQ3B1VSN271MP40S
	820	22×50	0.15	2.18	ELXQ201VSN821MP50S		270	25.4×30	0.15	1.19	ELXQ3B1VSN271MQ30S
	820	25.4×40	0.15	2.09	ELXQ201VSN821MQ40S		330	22×45	0.15	1.33	ELXQ3B1VSN331MP45S
	820	30×35	0.15	2.22	ELXQ201VSN821MR35S		330	25.4×35	0.15	1.37	ELXQ3B1VSN331MQ35S
	1,000	25.4×45	0.15	2.35	ELXQ201VSN102MQ45S		330	30×30	0.15	1.40	ELXQ3B1VSN331MR30S
	1,000	25.4×50	0.15	2.39	ELXQ201VSN102MQ50S		330	35×25	0.15	1.49	ELXQ3B1VSN331MA25S
	1,000	30×40	0.15	2.53	ELXQ201VSN102MR40S		390	22×50	0.15	1.48	ELXQ3B1VSN391MP50S
	1,000	35×30	0.15	2.61	ELXQ201VSN102MA30S		390	25.4×40	0.15	1.52	ELXQ3B1VSN391MQ40S
	1,200	30×45	0.15	2.84	ELXQ201VSN122MR45S		470	25.4×45	0.15	1.70	ELXQ3B1VSN471MQ45S

◆STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/ 105°C, 120Hz)	Part No.	WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/ 105°C, 120Hz)	Part No.
315	470	30×35	0.15	1.71	ELXQ3B1VSN471MR35S	400	470	30×45	0.15	1.81	ELXQ401VSN471MR45S
	470	35×30	0.15	1.82	ELXQ3B1VSN471MA30S		470	30×50	0.15	1.84	ELXQ401VSN471MR50S
	560	25.4×50	0.15	1.88	ELXQ3B1VSN561MQ50S		470	35×40	0.15	1.90	ELXQ401VSN471MA40S
	560	30×40	0.15	1.92	ELXQ3B1VSN561MR40S		560	35×45	0.15	2.12	ELXQ401VSN561MA45S
	560	30×45	0.15	1.97	ELXQ3B1VSN561MR45S		680	35×50	0.15	2.39	ELXQ401VSN681MA50S
	560	35×35	0.15	2.00	ELXQ3B1VSN561MA35S	420	100	22×25	0.20	0.66	ELXQ421VSN101MP25S
	680	30×50	0.15	2.21	ELXQ3B1VSN681MR50S		120	22×30	0.20	0.75	ELXQ421VSN121MP30S
	680	35×40	0.15	2.29	ELXQ3B1VSN681MA40S		120	25.4×25	0.20	0.77	ELXQ421VSN121MQ25S
	820	35×45	0.15	2.57	ELXQ3B1VSN821MA45S		150	22×35	0.20	0.86	ELXQ421VSN151MP35S
	1,000	35×50	0.15	2.89	ELXQ3B1VSN102MA50S		180	22×40	0.20	0.96	ELXQ421VSN181MP40S
350	120	22×25	0.15	0.72	ELXQ351VSN121MP25S		180	22×45	0.20	0.98	ELXQ421VSN181MP45S
	150	22×30	0.15	0.84	ELXQ351VSN151MP30S		180	25.4×30	0.20	0.97	ELXQ421VSN181MQ30S
	180	25.4×25	0.15	0.94	ELXQ351VSN181MQ25S		180	25.4×35	0.20	1.01	ELXQ421VSN181MQ35S
	220	22×35	0.15	1.04	ELXQ351VSN221MP35S		180	30×25	0.20	1.02	ELXQ421VSN181MP25S
	220	22×40	0.15	1.06	ELXQ351VSN221MP40S		220	22×50	0.20	1.11	ELXQ421VSN221MP50S
	220	25.4×30	0.15	1.07	ELXQ351VSN221MQ30S		220	25.4×40	0.20	1.14	ELXQ421VSN221MQ40S
	220	30×25	0.15	1.13	ELXQ351VSN221MR25S		220	30×30	0.20	1.14	ELXQ421VSN221MR30S
	270	22×45	0.15	1.20	ELXQ351VSN271MP45S		220	35×25	0.20	1.22	ELXQ421VSN221MA25S
	270	25.4×35	0.15	1.24	ELXQ351VSN271MQ35S		270	25.4×45	0.20	1.29	ELXQ421VSN271MA45S
	270	30×30	0.15	1.27	ELXQ351VSN271MR30S		270	30×35	0.20	1.30	ELXQ421VSN271MR35S
	270	35×25	0.15	1.35	ELXQ351VSN271MA25S		270	35×30	0.20	1.38	ELXQ421VSN271MA30S
	330	22×50	0.15	1.36	ELXQ351VSN331MP50S		330	25.4×50	0.20	1.44	ELXQ421VSN331MQ50S
	330	25.4×40	0.15	1.39	ELXQ351VSN331MQ40S		330	30×40	0.20	1.48	ELXQ421VSN331MP40S
	330	30×35	0.15	1.43	ELXQ351VSN331MR35S		330	35×35	0.20	1.54	ELXQ421VSN331MA35S
	390	25.4×45	0.15	1.55	ELXQ351VSN391MQ45S		390	30×45	0.20	1.64	ELXQ421VSN391MR45S
	390	30×40	0.15	1.60	ELXQ351VSN391MR40S		390	35×40	0.20	1.73	ELXQ421VSN391MA40S
	390	35×30	0.15	1.66	ELXQ351VSN391MA30S		470	30×50	0.20	1.84	ELXQ421VSN471MR50S
	470	25.4×50	0.15	1.72	ELXQ351VSN471MQ50S		470	35×45	0.20	1.94	ELXQ421VSN471MA45S
	470	30×45	0.15	1.81	ELXQ351VSN471MR45S	450	560	35×50	0.20	2.17	ELXQ421VSN561MA50S
	470	35×35	0.15	1.83	ELXQ351VSN471MA35S		82	22×25	0.20	0.59	ELXQ451VSN820MP25S
	560	30×50	0.15	2.00	ELXQ351VSN561MR50S		100	22×30	0.20	0.69	ELXQ451VSN101MP30S
	560	35×40	0.15	2.07	ELXQ351VSN561MA40S		100	25.4×25	0.20	0.70	ELXQ451VSN101MQ25S
	680	35×45	0.15	2.34	ELXQ351VSN681MA45S		120	22×35	0.20	0.77	ELXQ451VSN121MP35S
	820	35×50	0.15	2.62	ELXQ351VSN821MA50S		150	22×40	0.20	0.88	ELXQ451VSN151MP40S
400	100	22×25	0.15	0.66	ELXQ401VSN101MP25S		150	22×45	0.20	0.90	ELXQ451VSN151MP45S
	120	22×30	0.15	0.75	ELXQ401VSN121MP30S		150	25.4×30	0.20	0.88	ELXQ451VSN151MQ30S
	150	22×35	0.15	0.86	ELXQ401VSN151MP35S		150	25.4×35	0.20	0.92	ELXQ451VSN151MQ35S
	150	25.4×25	0.15	0.86	ELXQ401VSN151MQ25S		150	30×25	0.20	0.93	ELXQ451VSN151MR25S
	180	22×40	0.15	0.96	ELXQ401VSN181MP40S		180	22×50	0.20	1.01	ELXQ451VSN181MP50S
	180	25.4×30	0.15	0.97	ELXQ401VSN181MQ30S		180	25.4×40	0.20	1.03	ELXQ451VSN181MQ40S
	180	30×25	0.15	1.02	ELXQ401VSN181MR25S		180	30×30	0.20	1.03	ELXQ451VSN181MR30S
	220	22×45	0.15	1.09	ELXQ401VSN221MP45S		180	35×25	0.20	1.10	ELXQ451VSN181MA25S
	220	25.4×35	0.15	1.12	ELXQ401VSN221MQ35S		220	25.4×45	0.20	1.16	ELXQ451VSN221MP45S
	220	35×25	0.15	1.22	ELXQ401VSN221MA25S		220	30×35	0.20	1.17	ELXQ451VSN221MR35S
	270	22×50	0.15	1.23	ELXQ401VSN271MP50S		220	35×30	0.20	1.24	ELXQ451VSN221MA30S
	270	25.4×40	0.15	1.26	ELXQ401VSN271MQ40S		270	25.4×50	0.20	1.31	ELXQ451VSN271MQ50S
	270	25.4×45	0.15	1.29	ELXQ401VSN271MQ45S		270	30×40	0.20	1.33	ELXQ451VSN271MR40S
	270	30×30	0.15	1.27	ELXQ401VSN271MR30S		270	35×35	0.20	1.39	ELXQ451VSN271MA35S
	330	25.4×50	0.15	1.44	ELXQ401VSN331MQ50S		330	30×45	0.20	1.51	ELXQ451VSN331MR45S
	330	30×35	0.15	1.43	ELXQ401VSN331MR35S		390	30×50	0.20	1.67	ELXQ451VSN391MR50S
	330	35×30	0.15	1.52	ELXQ401VSN331MA30S		390	35×40	0.20	1.73	ELXQ451VSN391MA40S
	390	30×40	0.15	1.60	ELXQ401VSN391MR40S		390	35×45	0.20	1.77	ELXQ451VSN391MA45S
	390	35×35	0.15	1.67	ELXQ401VSN391MA35S		470	35×50	0.20	1.98	ELXQ451VSN471MA50S

◆RATED RIPPLE CURRENT MULTIPLIERS

●Frequency Multipliers

Frequency (Hz)	50	120	300	1k	10k	50k
160 to 250V _{dc}	0.81	1.00	1.17	1.32	1.45	1.50
315 to 450V _{dc}	0.77	1.00	1.16	1.30	1.41	1.43

The endurance of capacitors is reduced with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise. When long life performance is required in actual use, the rms ripple current has to be reduced.