







GROUNDING STRAP (2 PLCS)



PARTIAL END VIEW
(MOUNTING PEG
OMITTED FOR CLARITY)



M3 THREADED INSERT (2 PLCS)



SEE "PARTIAL END VIEW"
FOR SOLDER TAIL LOCATIONS

NOTES:

- MATERIALS:**
HOUSING, TAIL ALIGNER, AND INSERT-MOLDED STICKS ARE GLASS FILLED LCP (LIQUID CRYSTAL POLYMER), U.L. 94 V-0, COLOR IS BLACK; THE FEMALE TERMINALS ARE BERYLLIUM COPPER, 0.010" THICK; AND THE OUTER SHELL IS LOW-CARBON STEEL, .020" THICK.
- TERMINAL PLATING:**
30 MICROINCHES/(0.76 MICROMETER) MINIMUM OF GOLD IN SELECTIVE AREA; 100 MICRO-INCHES MINIMUM OF TIN IN SELECTIVE AREA; ALL OVER NICKEL UNDERPLATE OVERALL.
- OUTER SHELL FINISH:**
150 MICROINCHES/(3.81 MICROMETER) MINIMUM OF BRIGHT TIN;
OVER 50 MICROINCHES/(3.81 MICROMETER) OF NICKEL; OVER
COPPER FLASH (OPTIONAL).
- PARTS CONFORM TO MOLEX PRODUCT SPECIFICATION *PS-71718-9999.
- PACKAGING PER MOLEX SPECIFICATION *PK-70873-0299.
- SEE SHEET #2 FOR PART NUMBERS, RECOMMENDED BOARD LAYOUT AND PANEL CUT-OUT.
- PART COMPLIES WITH CLASS B OF COSMETIC SPECIFICATION PS-45499-002


NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS
WITHOUT THIS LABEL MAY CONTAIN
PRODUCT WITH LEAD.


71718-2001	.120*.010
71718-2000	.079*.010
ITEM NUMBER	DIM. A

2	F1
1	H
SHT	REV


ADD NOTE 7 EC NO: UCP2006-3051 DRAWN BY: BARRA 2006/07/10 CHKD: JORGAN 2006/07/10 APPR: MILLER 2006/07/11 REV	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH ONLY		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE .050 PITCH LFH 200 CKT RIGHT ANGLE I/O RECEPTACLE SALES ASSY MOLEX MOLEX INCORPORATED		
			mm	INCH	DRAWN BY	DATE						
			4 PLACES	± .005	± .005	GLT	1995/05/15					
			3 PLACES	± .010	± .010	CHECKED BY	DATE					
			2 PLACES	± .010	± .010	GLT	1995/05/15					
			1 PLACE	± .010	± .010	APPROVED BY	DATE					
			ANGULAR ±1/2°		GW	1995/05/15						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
					SEE TABLE		SDA-71718-2***		1 OF 2			
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							



RECOMMENDED P.C. BOARD LAYOUT
(COMPONENT SIDE SHOWN)



RECOMMENDED PANEL CUT-OUT DIMENSIONS
(ALL TOLERANCES $\pm .003$ UNLESS INDICATED OTHERWISE)



LTR.		REVISIONS		LTR.		REVISIONS		DIMENSIONS SHOWN $\frac{1}{16}$ INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR $\pm 1/2^\circ$		TITLE .050" PITCH LFH, 200 CKT. RIGHT ANGLE I/O RECEPTACLE. SALES ASSEMBLY		MFG. SH. REV. 71718	
								5 PLACE $\pm .010$ INCH 2 PLACE $\pm$ METRIC 1 PLACE $\pm$		PART NO. SEE CHART		SHEET NO. 2	
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MOLEX INCORPORATED L15LEJLL 60532 U.S.A.		DATE 05/15/95	
								DRWG. BY: GLT APP'D. BY: GWF		DRWG. NO. SDA-71718-2***		DIV. SIZE CPP C	
								SCALE 2:1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			