


## Model 6294 Minipincer® Test Clip To Straight Sheathed Banana Plug



### FEATURES:

- Attaches to component leads up to .090" (2.3 mm)
- Pincer test lead interfaces directly into the most popular multimeters configured with 4 mm sheathed safety jacks, including Amprobe, Fluke, H-P, Tektronix and Wavetek.
- For added safety, the pincer and banana plug body insulation material is fire retardant Nylon 6, UL94V-0 rated.
- Plug is molded directly to the cable in an integral one-piece design and the wire is double crimped for a long lasting connection.
- Multi-leaf banana spring material is nickel plated Beryllium Copper for extended insertion life & low contact resistance.
- High strand count silicone insulated wire offers excellent flexibility and high temperature resistance.

### MATERIALS:

Pincer: Body: Nylon 6 – Fire Retardant – UL94 V-O Rated, Color per part number

Pincer Contact: Beryllium Copper, Gold Plated

Wire: 18 AWG, 65 x 36 Tinned Copper, Insulation – Silicone, .144" (3.66 mm) O.D., Color per P/N

Banana Plug: Body - Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated

Insulation - Polypropylene, Fire Retardant UL94 V-2 Rated, Color per part number

### RATINGS:

IEC 1010-2-031, Category II, P2 Compliant

Operating Voltage: 300 V RMS

Current: 5 Amperes

### ORDERING INFORMATION: Model 6294-48-\*

Standard Length: 48" (122 cm) \*= Color Code, -0 Black and -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6294-48-0](#) [6294-48-2](#)