

SPECIFICATIONS

Material: Boot: APM-RUBRGLAS (transparent silicone rubber) conforms to A-A-59588, Class III Grade 50.

Temperature Range: HEXSEALS: -94°F to +400°F

Pressure Range: Dust tight and splashproof.

Resistant to: Salt spray, weather, sunlight, ozone, corona and most acids.



Shelf Life: Excess of 25 years.

Operational Life: 10,000 actuations, minimum.

Notes:

1. Mounting screws are supplied in lengths shown unless otherwise specified.
2. New sizes and types of RUBRGLAS-SEELS[®] are being added regularly. Please request other types and styles as required.

Agency Recognition: Front Panel mounted Circuit Breaker Boots are UL-listed to UL Std. 50, types 1, 2, 3, 12, 12K, and 13. Back-of-Panel mounted Circuit Breaker boots are UL-listed to UL Std. 50, type 1. Also meet CSA standards.



NOTES:

ASSEMBLY CONSISTS OF 1 BOOT, MAT'L APM RUBRGLAS[®], ORDER SEPARATELY,

2#6-32 APM SEELSKREWS[®] LENGTH=3/8.

UNLESS OTHERWISE NOTED TOLERANCES ARE ± 1/32

BACK-OF-PANEL MOUNTING

I	RUBBER MAT'L CHANGED, WALL THICKNESS TOL. 0.010 CHANGED TO 0.005, HOLE DIM. Ø0.147" CHANGED TO Ø0.149", DELETED TO "DESIGN TO MEET MIL-5423" and DELETED TO SEELSKREW INFORMATION	S. GOK	10.05.09
H	CAD COMPUTER GENERATED		01.03.03
G	ADDED NOTES	T.C.	09.16.68
F	REDRAWN, ADDED NEW SPECS, CLEARED PRINT	NKS	08.09.67
REV.	DESCRIPTION		DATE
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.			
TITLE: CIRCUIT BREAKER BOOT, CIRCUIT BREAKER TOGGLE APM-HEXSEAL CORPORATION		ENG.	S. GOK
		DWN.	G.W.
		CHKD.	J. CELLA
FINISH: 50 DUROMETER TRANSPARENT		SCALE	DWG. NO.
		1 : 1	HE-1076

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[HE1076](#)