


CMSH3-40FL

**SURFACE MOUNT
SILICON SCHOTTKY RECTIFIER
3 AMP, 40 VOLTS**



SMBFL CASE



www.centrasemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMSH3-40FL is an extremely efficient silicon Schottky rectifier with low total conduction losses packaged in the low profile SMBFL case. The SMBFL fits on existing industry standard SMB mounting pad layouts.

MARKING CODE: CS340FL

FEATURES:

- High current capability (3.0A)
- Low leakage current (100 μ A MAX @ 40V)
- Low forward voltage (0.5V MAX @ 3.0A)
- Low package profile (1.0mm)
- Flammability classification UL94V-0

APPLICATIONS:

- Reverse polarity protection
- Voltage clamping
- DC-DC output rectification
- Power management

MAXIMUM RATINGS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

	SYMBOL		UNITS
Peak Repetitive Reverse Voltage	V_{RRM}	40	V
DC Blocking Voltage	V_R	40	V
RMS Reverse Voltage	$V_{R(RMS)}$	28	V
Average Forward Current ($T_L=125^{\circ}\text{C}$)	I_O	3.0	A
Peak Forward Surge Current, $t_p=8.3\text{ms}$	I_{FSM}	80	A
Operating and Storage Junction Temperature	T_J, T_{stg}	-65 to +150	$^{\circ}\text{C}$
Thermal Resistance	θ_{JL}	15	$^{\circ}\text{C/W}$

ELECTRICAL CHARACTERISTICS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	TYP	MAX	UNITS
I_R	$V_R=40\text{V}$	15	100	μA
V_F	$I_F=3.0\text{A}$	0.46	0.50	V
C_J	$V_R=4.0\text{V}, f=1.0\text{MHz}$	150		pF


R1 (27-June 2012)

CMSH3-40FL

SURFACE MOUNT
SILICON SCHOTTKY RECTIFIER
3 AMP, 40 VOLTS



SMBFL CASE - MECHANICAL OUTLINE



LEAD CODE:

- 1) Cathode
- 2) Anode

MARKING CODE: CS340FL

DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.035	0.044	0.90	1.10
B	0.031	0.048	0.80	1.20
C	0.006	0.010	0.15	0.25
D	0.137	0.146	3.50	3.70
E	0.161	0.178	4.10	4.50
F	0.200	0.217	5.10	5.50
G	0.074	0.083	1.90	2.10

SMBFL (REV: R0)

R1 (27-June 2012)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[CM SH3-40FL TR13](#)