

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		A4	REVISED PER ECO-11-004820	11MAR11	RK	HMR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN PLATED, COPPER ALLOY.
SCREWS: 6-32, STEEL, .0002 MIN ZINC PLATED WITH CLEAR CHROMATE COATING.


ELECTRICAL:
RATED CURRENT UL/CSA:
CLASS C: 25A, 300V
CLASS D: 5A, 600V
WIRE RANGE: 12-22 AWG.

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX.


- 1 SCREWS ARE BOTTOMED.
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SEE FIGURE 2 OBSOLETE



RECOMMENDED PCB LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S SCHLEGEL	5/26/04	 TE Connectivity		
		CHK	S YODER	5/26/04			
		APVD	S YODER	5/26/04	NAME		
		PRODUCT SPEC			6DBL-XX-006 ASSEMBLY		
		APPLICATION SPEC			-		
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT	-	A300779	C-3-1437651-4	-	
CUSTOMER DRAWING		SCALE	NTS	SHEET	1 OF 1	REV	A4