





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		W	REVISED PER ECO-08-007327	02OCT08	BM	WM



- 1 MATERIAL:
HOUSING — POLYPHENYLENE OXIDE
TERMINALS — HIGH STRENGTH COPPER ALLOY PLATED WITH .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, .000030 MIN TOTAL ON MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
2. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
- 3 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
4. WIRE SIZE: 26, 27 & 28 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION ø1.14 [.045] IS ACCEPTABLE FOR MOST APPLICATIONS.
- 5 CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

OBSOLETE	GRAY	552390-4
	BLACK	552390-1
	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SALLEY 10-JAN-80	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK V. SLACK 11-JAN-80				
DIMENSIONS: mm [INCHES]		APVD G. WARD 11-JAN-80	NAME PLUG ASSEMBLY, 50 POSITION E-SLOT, W/ 4-40 HOLES CHAMP-LOK			
		PRODUCT SPEC				
		APPLICATION SPEC	SIZE A2		CAGE CODE 00779	DRAWING NO C=552390
		MATERIAL	WEIGHT -		RESTRICTED TO -	
		FINISH	CUSTOMER DRAWING		SCALE 2:1	SHEET 1 of 1
					REV W	