




		65.33 [2.572]	32.66 [1.286]	66.59 [2.622]	64.05 [2.522]	49	100		6-104655-1
		58.97 [2.322]	29.48 [1.161]	60.24 [2.372]	57.70 [2.272]	44	90		6-104655-0
		52.63 [2.072]	26.31 [1.036]	53.89 [2.122]	51.35 [2.022]	39	80		5-104655-9
		46.28 [1.822]	23.13 [.911]	47.54 [1.872]	45.00 [1.772]	34	70		5-104655-8
		39.93 [1.572]	19.96 [.786]	41.19 [1.622]	38.65 [1.522]	29	60		5-104655-7
		33.58 [1.322]	16.78 [.661]	34.84 [1.372]	32.30 [1.272]	24	50		5-104655-6
		27.23 [1.072]	13.61 [.536]	28.49 [1.122]	25.95 [1.022]	19	40		5-104655-5
		20.88 [.822]	10.43 [.411]	22.14 [.872]	19.60 [.772]	14	30		5-104655-4
		14.53 [.572]	7.26 [.286]	15.79 [.622]	13.25 [.522]	9	20		5-104655-3
		11.98 [.472]	5.99 [.236]	13.25 [.522]	10.72 [.422]	7	16		5-104655-2
		8.18 [.322]	4.08 [.161]	9.44 [.372]	6.90 [.272]	4	10		5-104655-1
		65.33 [2.572]	32.66 [1.286]	66.59 [2.622]	64.05 [2.522]	49	100		1-104655-1
		58.97 [2.322]	29.48 [1.161]	60.24 [2.372]	57.70 [2.272]	44	90		1-104655-0
		52.63 [2.072]	26.31 [1.036]	53.89 [2.122]	51.35 [2.022]	39	80		104655-9
		46.28 [1.822]	23.13 [.911]	47.54 [1.872]	45.00 [1.772]	34	70		104655-8
		39.93 [1.572]	19.96 [.786]	41.19 [1.622]	38.65 [1.522]	29	60		104655-7
		33.58 [1.322]	16.78 [.661]	34.84 [1.372]	32.30 [1.272]	24	50		104655-6
		27.23 [1.072]	13.61 [.536]	28.49 [1.122]	25.95 [1.022]	19	40		104655-5
		20.88 [.822]	10.43 [.411]	22.14 [.872]	19.60 [.772]	14	30		104655-4
		14.53 [.572]	7.26 [.286]	15.79 [.622]	13.25 [.522]	9	20		104655-3
		11.98 [.472]	5.99 [.236]	13.25 [.522]	10.72 [.422]	7	16		404655-2
		8.18 [.322]	4.08 [.161]	9.44 [.372]	6.90 [.272]	4	10		104655-1
FINISH		E	D	C	B	A	NUMBER OF POSITIONS		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATE HELM 08/07/91		CHK D. GORENC 8/12/91		APVD D. FORKER 8/12/91		NAME	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC		SIZE	
0 PLC ± .		1 PLC ± .		2 PLC ± .		3 PLC ± .		4 PLC ± .	
ANGLES		FINISH		WEIGHT		CUSTOMER DRAWING		SCALE 10:1	
MATERIAL HOUSING: LCP, COLOR-BLACK POST: PHOS. BRONZE HOLD: WOVN. COPPER ALLOY		SEE TABLE		108-1332		114-7010		A1 00779 104655	
								SHEET 1 OF 1	
								REV 3	