


STYLE B
(MALE)



STYLE C
(STRIP)

NOTES:

1. FINISH: SILVER PLATE 200 μ IN MIN THICK.
2. FINISH: NICKEL PLATE 40 μ IN MIN THICK.
3. FINISH: GOLD PLATE 10 μ IN MIN THICK.
4. FINISH: NICKEL PLATE 50 μ IN MIN THICK.
5. FINISH: NICKEL PLATE 100 μ IN MIN THICK.
6. NOT USED.
7. NOT USED.
8. NOT USED.
9. NOT USED.
10. NOT USED.
11. PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS, 6-8 AS 6 OVER 8.
12. MATERIAL: CDA172, BeCu.
13. MATERIAL: STAINLESS STEEL.

14 PRODUCT IS SOLD BY THE FOOT.

15 FINISH: PREPLATED SILVER 200 uIN MIN, OVER NICKEL .040 uIN MIN.

16 REELED PRODUCT.

17 PRELIMINARY PART NUMBER.

18 OBSOLETE PART NUMBER.

19 OBSOLETEPARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		NOT AVAILABLE			--	--	--	--	03088	4-192039-5		
		NOT AVAILABLE			--	--	--	--	03087	4-192039-4		
		NOT AVAILABLE			--	--	--	--	03051	4-192039-3		
		NOT AVAILABLE			--	--	--	--	03050	4-192039-2		
	OBSOLETE	B	[.036]	[.58]	12	16.51[.650]	UNPL	43	0.20[.008]	03119	4-192039-1	
		B	[.032]	[.58]	12	14.22[.560]	1-2	43	0.15[.006]	03124	4-192039-0	
		NOT AVAILABLE			--	--	--	--	--	3-192039-9		
	OBSOLETE	B	[.038]	[.46]	12	12.7[.500]	--	34	0.20[.008]	03122	3-192039-8	
		B	[.038]	[.46]	12	12.7[.500]	1-2	34	0.20[.008]	03121	3-192039-7	
		B	[.038]	[.46]	12	12.7[.500]	UNPL	34	0.20[.008]	03048	3-192039-6	
		B	[.032]	[.46]	12	12.7[.500]	1-2	--	0.15[.006]	03129	3-192039-5	
OBSOLETE	B	[.032]	[.46]	12	12.7[.500]	UNPL	34	0.15[.006]	03110	3-192039-4		
	OBSOLETE	B	[.034]	[.33]	12	9.52[.375]	1-2	24	0.20[.008]	03148	3-192039-3	
		--						--	--	03042	3-192039-2	
		SUPERSEDED BY 2-192039-7				--	--	--	--	03041	3-192039-1	
	OBSOLETE	B	[.036]	[.31]	12	7.9[.311]	3-2	21	0.20[.008]	03082	3-192039-0	
		B	[.036]	[.31]	12	7.9[.311]	1-2	21	0.20[.008]	03036	2-192039-9	
	OBSOLETE				--	--	--	--	--	03035	2-192039-8	
	OBSOLETE	B	[.036]	[.31]	12	7.9[.311]	UNPL	21	0.20[.008]	03066	2-192039-7	
	OBSOLETE	B	[.036]	[.30]	12	7.37[.291]	UNPL	20	0.20[.008]	03120	2-192039-6	
		NOT AVAILABLE			--	--	--	--	--	03034	2-192039-5	
		NOT AVAILABLE			--	--	--	--	--	03030	2-192039-4	
		B	[.036]	[.30]	12	6.3[.248]	1-2	17	0.20[.008]	03027	2-192039-3	
		B	[.036]	[.30]	12	6.3[.248]	UNPL	17	0.20[.008]	03026	2-192039-2	
OBSOLETE	B	[.033]	[.27]	12	6.3[.248]	1-2	16	0.20[.008]	03140	2-192039-1		
		B	[.033]	[.27]	12	6.3[.248]	UNPL	16	0.20[.008]	03139	2-192039-0	
B		[.036]	[.25]	12	6.0[.236]	3-2	15	0.20[.008]	03024	1-192039-9		
B		[.034]	[.20]	12	4.0[.157]	4	9	0.20[.008]	03017	1-192039-8		
	OBSOLETE	B	[.034]	[.20]	12	4.0[.157]	3-2	9	0.20[.008]	03016	1-192039-7	
		B	[.034]	[.20]	12	4.0[.157]	UNPL	9	0.20[.008]	03071	1-192039-6	
		--						--	--	03015	1-192039-5	
		B	[.032]	[.20]	12	4.0[.157]	3-2	9	0.15[.006]	03014	1-192039-4	
		B	[.032]	[.20]	12	4.0[.157]	4	9	0.15[.006]	03128	1-192039-3	
		B	[.032]	[.20]	12	4.0[.157]	UNPL	9	0.15[.006]	03073	1-192039-2	
		B	[.020]	[.20]	13	4.0[.157]	UNPL	9	0.12[.005]	03091	1-192039-1	
	C	[.038]		12	--	3-2	--	0.20[.008]	03115	1-192039-0		
	NOT AVAILABLE			12	--	--	--	--	--	192039-9		
	OBSOLETE		C	[.038]		12	--	1-2	--	0.20[.008]	03116	192039-8
			C	[.038]		12	--	UNPL	--	0.20[.008]	03078	192039-7
OBSOLETE		C	[.034]		12	--	3-2	--	0.15[.006]	03003	192039-6	
		C	[.034]		12	--	1-2	--	0.15[.006]	03094	192039-5	
		C	[.034]		12	--	UNPL	--	0.15[.006]	03057	192039-4	
		C	[.020]		13	--	UNPL	--	0.12[.005]	03138	192039-3	
	OBSOLETE				--	--	--	--	03079	192039-2		
	NOT AVAILABLE			--	--	--	--	--	03067	192039-1		
		STYLE	LH	FREE DIA	MAT'L (NOTE)	MATING DIA REF	PLATING	NUM LOUV	MAT'L THK	REF	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09-12-91		RA JAYNE		Tyco Electronics Corporation	
		CHK 09-12-91		RA JAYNE		Harrisburg, PA 17105	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME	
		0 PLC ± —		PRODUCT SPEC		CONTACT BAND,	
		1 PLC ± —		—		LAIIS, MALE	
		2 PLC ± .02		APPLICATION SPEC		—	
		3 PLC ± .010		—		SIZE	
4 PLC ± —		ANGLES		CAGE CODE		DRAWING NO	
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
SEE TABLE		—		—		A2 00779 C-192039	
CUSTOMER DRAWING				SCALE		SHEET	
				NTS		1 OF 2	
						REV K1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD

K

SEE SHEET 1

-

-

-

19

OBSOLETE

B

[.038]

[.46]

12

12.7[.500]

3-2

34

0.20[.008]

--

5-192039-9

16

17

C

[.034]

--

12

--

15

--

.006

--

5-192039-8

B

[.036]

[.25]

12

6.0[.236]

UNPL

15

.008

--

5-192039-7

B

[.036]

[.33]

12

9.52[.375]

UNPL

24

.008

--

5-192039-6

B

[.032]

[.58]

12

14.22[.560]

UNPL

43

.006

--

5-192039-5

B

[.033]

[.20]

12

4.0[.157]

5

9

0.20[.008]

--

5-192039-4

B

12

6.0[.236]

5

16

0.20[.008]

--

5-192039-3

SUPERSEDED BY

2-192039-0

--

--

--

--

5-192039-2

19

OBSOLETE

B

[.036]

[1.71]

12

44.78[1.763]

3-2

130

0.15[.006]

--

5-192039-1

18

OBSOLETE

B

[.034]

[3.50]

12

98.55[3.880]

UNPL

92

0.15[.006]

03126

5-192039-0

19

NOT AVAILABLE

--

--

--

--

03084

4-192039-9

19

B

[.036]

[1.91]

12

50.8[2.000]

UNPL

145

0.20[.008]

03096

4-192039-8

OBSOLETE

B

[.036]

[1.71]

12

44.78[1.763]

1-2

130

0.15[.006]

03125

4-192039-7

OBSOLETE

B

[.036]

[1.71]

12

44.78[1.763]

UNPL

130

0.15[.006]

03145

4-192039-6

STYLE

LH

FREE DIA

MATL (NOTE)

MATING ϕ REF

PLATING

NUM LOUV

MAT'L THK

REF

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 11-04-91 RA JAYNE

CHK 11-04-91 RA JAYNE

APVD -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: INCHES

MATERIAL SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± .02

3 PLC ± .010

4 PLC ± -

ANGLES ± -

FINISH SEE TABLE

Tyco Electronics Corporation
Harrisburg, PA 17105

CONTACT BAND,
LAIHS, MALE

SIZE A2

CAGE CODE 00779

DRAWING NO C=192039

RESTRICTED TO -

SCALE NTS

SHEET 2 OF 2

REV K1

AMP 1471-9 REV 31MAR2000