


LTA-Series




The LTA-Series Mini Tippet Snap-in rocker switches are illuminated, single pole and double-insulated. These AC rated switches are also suitable for low voltage DC applications. A variety of actuators, colors and terminations can be specified with ratings up to 20 amps.

Specifications




- Certifications*: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon or Polycarbonate
- Bezel Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



.069[1.75] DIA	.156[3.96] DIA	.055[1.40] DIA	
.250[6.35]	.375[9.52]	.250[6.35]	6.000[152.40]
	.250[6.35]	.187[4.74]	.500[12.70]
.250 TAB (Q.C.)	SOLDER LUG	.187 TAB (Q.C.)	INTEGRATED WIRE LEAD (no exposed conductors)
TERMINAL TYPE			



LTA	20	1	-	T	R	-	B	-	/	125N
SERIES	RATING	TERMINATION			ACTUATOR COLOR			LENS COLOR ^{2,3}		
LTA OFF-NONE-ON SINGLE POLE	10	5A 250VAC	0	SOLDER LUG		ROCKER		A	AMBER	
		10A 125VAC	1	.250 TAB (QC)		A	AMBER	C	CLEAR	
		1/2HP 125-250VAC	3	.187 TAB (QC)		C	CLEAR	G	GREEN	
	11	5A 250VAC	5	WIRE LEAD		G	GREEN ³	LU	BLUE	
		10A 125VAC				R	RED	R	RED	
		5A (TUNGSTEN)								
		125VAC L								
	20	10A 250VAC				PADDLE ¹				
		15A 125VAC				B	BLACK			
		3/4HP 125-250VAC				W	WHITE			
	21	10A 250VAC								
		15A 125VAC								
	22	10A 250VAC								
		15A 125VAC								
		20A 125-250VAC H								
		3/4HP 125-250VAC								

NOTES:

Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "BEZEL" to the end of the catalog number. (ex.) LTA201-TR-B/12V/BEZEL
 Imprinting is available. Please specify when ordering.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

¹ Custom colors are available. Consult factory.

² Neon lamps (125 volt or 250 volt) not recommended with green or blue colored indicators.

³ Specify lens color only if actuator style is P or PS.