





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-15-001229	27JAN2015	NK	DR
	D3	REVISED PER ECO-17-008809	19JUN2017	RS	DR

- 1 WIRE SIZE IS 22-16 AWG.
- 2 WIRE INSULATION DIA: $\phi 2.692-3.581$
[$\phi .106-.141$]
- 3 BODY MATERIAL THICKNESS IS 0.787 ± 0.050
[$.031\pm .002$]
- 4 600 VOLT MAX.
- 5 CIRCULAR MIL AREA:
509-3,260 ($0.26\text{mm}^2-1.65\text{mm}^2$).
- 6 MAXIMUM TEMPERATURE 105°C [221°F]

LOOSE PIECE	1000	131443
PACKAGING TYPE	QTY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 29MAR06	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 28MAR06					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 1°	APVD T MICHELUTTI 28MAR06	NAME TERMINAL, TAB, PLASTI-GRIP 22-16 AWG				
		PRODUCT SPEC —					
		APPLICATION SPEC 114-2157	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO —
		MATERIAL INSULATION: PVC BODY: COPPER PER ASTM B152	FINISH INSULATION COLOR: RED BODY: TIN PLATE PER ASTM B545	WEIGHT —	A3	00779	
CUSTOMER DRAWING					SCALE 5:1	SHEET 1 OF 1	REV D3