

RoHS compliant

**Very High Sensitivity,
50 mW (nominal operating)
Relay with LT style
pin layout**

TX-S RELAYS

FEATURES

1. **Nominal operating power:**
High sensitivity of 50mW
By using the highly efficient polar magnetic circuit "seesaw balance mechanism", a nominal operating power of 50 mW (minimum operating power of 32 mW) has been achieved.
2. **Compact size**
15.0(L) × 7.4(W) × 8.2(H) .591(L) × .291(W) × .323(H)
3. **High contact reliability**
High contact reliability is achieved by the use of gold-clad twin crossbar contacts, low-gas formation materials, mold sealing the coil section, and by controlling organic gas in the coil.
***We also offer a range of products with AgPd contacts suitable for use in low level load analog circuits (Max. 10V DC 10 mA).**
4. **Outstanding surge resistance.**
Surge breakdown voltage between open contacts:
1,500 V 10×160 μ sec. (FCC part 68)
Surge breakdown voltage between contact and coil:
2,500 V 2×10 μ sec. (Telcordia)

5. **Low thermal electromotive force (approx. 0.3 μ V)**


The structure of the mold-sealed body block of the coil section achieves nominal operating power of 50 mW and high sensitivity, along with low thermal electromotive force, reduced to approximately 0.3 μ V.

6. **Sealed construction allows automatic washing.**

TYPICAL APPLICATIONS

1. **Communications**
(XDSL, Transmission)
2. **Measurement**
3. **Security**
4. **Home appliances, and audio/visual equipment**
5. **Medical equipment**

ORDERING INFORMATION



Contact arrangement
2: 2 Form C

Surface-mount availability
Nil: Standard PC board terminal type
SA: SA type

Operating function
Nil: Single side stable
LT: 2 coil latching

Terminal shape
Nil: Standard PC board terminal or surface-mount terminal

Nominal coil voltage (DC)
3, 4.5, 6, 9, 12, 24V

Contact material
Nil: Standard contact (Ag+Au clad)
1: AgPd contact (low level load); AgPd+Au clad (stationary), AgPd (movable)

Packing style
Nil: Tube packing
X: Tape and reel (picked from 1/3/4/5-pin side)
Z: Tape and reel packing (picked from the 8/9/10/12-pin side)

TX-S

TYPES

1. Standard PC board terminal

Contact arrangement	Nominal coil voltage	Single side stable Part No.	2 coil latching Part No.
2 Form C	3V DC	TXS2-3V	TXS2-LT-3V
	4.5V DC	TXS2-4.5V	TXS2-LT-4.5V
	6V DC	TXS2-6V	TXS2-LT-6V
	9V DC	TXS2-9V	TXS2-LT-9V
	12V DC	TXS2-12V	TXS2-LT-12V
	24V DC	TXS2-24V	TXS2-LT-24V

Standard packing: Tube: 40 pcs.; Case: 1,000 pcs.

Note: Please add "-1" to the end of the part number for AgPd contacts (low level load).

2. Surface-mount terminal

1) Tube packing

Contact arrangement	Nominal coil voltage	Single side stable Part No.	2 coil latching Part No.
2 Form C	3V DC	TXS2SA-3V	TXS2SA-LT-3V
	4.5V DC	TXS2SA-4.5V	TXS2SA-LT-4.5V
	6V DC	TXS2SA-6V	TXS2SA-LT-6V
	9V DC	TXS2SA-9V	TXS2SA-LT-9V
	12V DC	TXS2SA-12V	TXS2SA-LT-12V
	24V DC	TXS2SA-24V	TXS2SA-LT-24V

Standard packing: Tube: 40 pcs.; Case: 1,000 pcs.

Note: Please add "-1" to the end of the part number for AgPd contacts (low level load).

2) Tape and reel packing

Contact arrangement	Nominal coil voltage	Single side stable Part No.	2 coil latching Part No.
2 Form C	3V DC	TXS2SA-3V-Z	TXS2SA-LT-3V-Z
	4.5V DC	TXS2SA-4.5V-Z	TXS2SA-LT-4.5V-Z
	6V DC	TXS2SA-6V-Z	TXS2SA-LT-6V-Z
	9V DC	TXS2SA-9V-Z	TXS2SA-LT-9V-Z
	12V DC	TXS2SA-12V-Z	TXS2SA-LT-12V-Z
	24V DC	TXS2SA-24V-Z	TXS2SA-LT-24V-Z

Standard packing: Tape and reel: 500 pcs.; Case: 1,000 pcs.

Notes: 1. Tape and reel packing symbol "-Z" is not marked on the relay. "X" type tape and reel packing (picked from 1/2/3/4-pin side) is also available.

2. Please add "-1" to the end of the part number for AgPd contacts (low level load). (Ex. TXS2SA-3V-1-Z)

RATING

1. Coil data

1) Single side stable

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Max. applied voltage (at 20°C 68°F)
3V DC	80%V or less of nominal voltage* (Initial)	10%V or more of nominal voltage* (Initial)	16.7mA	180Ω	50mW	150%V of nominal voltage
4.5V DC			11.1mA	405Ω		
6V DC			8.3mA	720Ω		
9V DC			5.6mA	1,620Ω		
12V DC			4.2mA	2,880Ω		
24V DC			2.9mA	8,229Ω		

2) 2 coil latching

Nominal coil voltage	Set voltage (at 20°C 68°F)	Reset voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)		Coil resistance [±10%] (at 20°C 68°F)		Nominal operating power	Max. applied voltage (at 20°C 68°F)
			Set coil	Reset coil	Set coil	Reset coil		
3V DC	80%V or less of nominal voltage* (Initial)	80%V or less of nominal voltage* (Initial)	23.3mA	23.3mA	129Ω	129Ω	70mW	150%V of nominal voltage
4.5V DC			15.6mA	15.6mA	289Ω	289Ω		
6V DC			11.7mA	11.7mA	514Ω	514Ω		
9V DC			7.8mA	7.8mA	1,157Ω	1,157Ω		
12V DC			5.8mA	5.8mA	2,057Ω	2,057Ω		
24V DC			6.3mA	6.3mA	3,840Ω	3,840Ω	150mW	150mW

*Pulse drive (JIS C 5442-1986)

2. Specifications


Characteristics	Item	Specifications
Contact	Arrangement	2 Form C
	Initial contact resistance, max.	Max. 100 mΩ (By voltage drop 6 V DC 1A)
	Contact material	Standard contact: Ag+Au clad, AgPd contact (low level load): AgPd+Au clad (stationary), AgPd (movable)
Rating	Nominal switching capacity	1 A 30 V DC (resistive load)
	Max. switching power	30 W (DC) (resistive load)
	Max. switching voltage	110V DC
	Max. switching current	1 A
	Min. switching capacity (Reference value)*1	10μA 10mV DC
	Nominal operating power	50 mW (3 to 12 V DC), 70 mW (24 V DC) 70 mW (3 to 12 V DC), 150 mW (24 V DC)
	Insulation resistance (Initial)	Min. 1,000MΩ (at 500V DC) Measurement at same location as "Initial breakdown voltage" section.
Electrical characteristics	Breakdown voltage (Initial)	Between open contacts 750 Vrms for 1min. (Detection current: 10mA)
		Between contact and coil 1,800 Vrms for 1min. (Detection current: 10mA)
	Between contact sets	1,000 Vrms for 1min. (Detection current: 10mA)
Electrical characteristics	Surge breakdown voltage (Initial)	Between open contacts 1,500 V (10×160μs) (FCC Part 68)
		Between contacts and coil 2,500 V (2×10μs) (Telcordia)
	Temperature rise (at 20°C 68°F)	Max. 50°C (By resistive method, nominal coil voltage applied to the coil; contact carrying current: 1A.)
Mechanical characteristics	Operate time [Set time] (at 20°C 68°F)	Max. 5 ms [Max. 5 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.)
		Release time [Reset time] (at 20°C 68°F)
	Shock resistance	Functional Min. 750 m/s ² (Half-wave pulse of sine wave: 6 ms; detection time: 10μs.)
Mechanical characteristics	Destructive	Min. 1,000 m/s ² (Half-wave pulse of sine wave: 6 ms.)
	Vibration resistance	Functional 10 to 55 Hz at double amplitude of 3.3 mm (Detection time: 10μs.)
		Destructive 10 to 55 Hz at double amplitude of 5 mm
Expected life	Mechanical	Min. 5×10 ⁷ (180 cpm)
	Electrical	Min. 2×10 ⁵ (1 A 30 V DC resistive) (at 20 cpm)
Conditions	Conditions for operation, transport and storage*2	Ambient temperature: -40°C to +70°C -40°F to +158°F; Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature)
	Max. operating speed (at rated load)	20 cpm
Unit weight		Approx. 2 g .071 oz

Notes: *1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load. (AgPd contact type is available for low level load switching [10V DC, 10mA max. level])


*2 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT (Page 24).

REFERENCE DATA

1. Maximum switching capacity




2. Life curve



3. Mechanical life

Tested sample: TXS2-4.5V, 10 pcs.
Operating speed: 180 cpm




TX-S

4. Electrical life (1 A 30 V DC resistive load)


Tested sample: TXS2-4.5V, 6 pcs.

Operating speed: 20 cpm

Change of pick-up and drop-out voltage



Change of contact resistance




5-(1). Coil temperature rise

Tested sample: TXS2-4.5V, 6 pcs.

Point measured: Inside the coil

Ambient temperature: 25°C 77°F, 70°C 158°F




5-(2). Coil temperature rise

Tested sample: TXS2-24V, 6 pcs.


Point measured: Inside the coil

Ambient temperature: 25°C 77°F, 70°C 158°F




6-(1). Operate and release time (with diode)

Tested sample: TXS2-4.5V, 10 pcs.




6-(2). Operate and release time (without diode)

Tested sample: TXS2-4.5V, 10 pcs.




7. Ambient temperature characteristics

Tested sample: TXS2-4.5V, 5 pcs.




8-(1). High frequency characteristics (Isolation)

Tested sample: TXS2-4.5V, 2 pcs.




8-(2). High frequency characteristics (Insertion loss)

Tested sample: TXS2-4.5V, 2 pcs.




9-(1). Malfunctional shock (single side stable)

Tested sample: TXS2-4.5V, 6 pcs.




9-(2). Malfunctional shock (latching)

Tested sample: TXS2-LT-4.5V, 6 pcs.




10. Thermal electromotive force


Tested sample: TXS2-4.5V, 6 pcs.




11-(1). Influence of adjacent mounting
Tested sample: TXS2-4.5V, 6 pcs.




11-(2). Influence of adjacent mounting
Tested sample: TXS2-4.5V, 6 pcs.




11-(3). Influence of adjacent mounting
Tested sample: TXS2-4.5V, 6 pcs.




12. Pulse dialing test
(35 mA 48V DC wire spring relay load)
Tested sample: TXS2-4.5V, 6 pcs.



Change of pick-up and drop-out voltage



Change of contact resistance




Note: Data of surface-mount type are the same as those of PC board terminal type.

DIMENSIONS (mm inch)

The CAD data of the products with a **CAD Data** mark can be downloaded from: <http://industrial.panasonic.com/ac/e/>

1. Standard PC board terminal and Self clinching terminal


CAD Data




Type	External dimensions (General tolerance: $\pm 0.3 \pm .012$)		PC board pattern (Bottom view) (Tolerance: $\pm 0.1 \pm .004$)	
	Single side stable type	2 coil latching type	Single side stable type	2 coil latching type
Standard PC board terminal				

Schematic (Bottom view)

Single side stable



2 coil latching



(Deenergized condition)

(Reset condition)

