


Glass Passivated Junction Plastic Rectifier

SUPERECTIFIER®



DO-201AD

FEATURES

- Superectifier structure for high reliability condition
- Cavity-free glass-passivated junction
- Low leakage current, typical I_R less than 0.1 μA
- Low forward voltage drop
- High forward surge capability
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

TYPICAL APPLICATIONS

For use in high voltage rectification of power supply, inverters, converters, freewheeling diodes, and snubber circuit application.

MECHANICAL DATA

Case: DO-201AD, molded epoxy over glass body
Molding compound meets UL 94 V-0 flammability rating
Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: Color band denotes cathode end

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	3.0 A
V_{RRM}	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V
I_{FSM}	125 A
I_R	5.0 μA
V_F	1.2 V, 1.1 V
T_J max.	175 °C
Package	DO-201AD
Diode variations	Single die

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)									
PARAMETER	SYMBOL	GP30A	GP30B	GP30D	GP30G	GP30J	GP30K	GP30M	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current 0.375" (9.5 mm) lead length at $T_A = 55$ °C	$I_{F(AV)}$	3.0							A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	125							A
Maximum full load reverse current, full cycle average 0.375" (9.5 mm) lead length at $T_A = 55$ °C	$I_{R(AV)}$	100							μA
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +175							°C



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)											
PARAMETER	TEST CONDITIONS		SYMBOL	GP30A	GP30B	GP30D	GP30G	GP30J	GP30K	GP30M	UNIT
Maximum instantaneous forward voltage	3.0 A		V _F	1.2		1.1					V
Maximum reverse current at rated DC blocking voltage		T _A = 25 °C	I _R	5.0						μA	
		T _A = 125 °C		100							
Maximum reverse recovery time	I _F = 0.5 A, I _R = 1.0 V, I _{rr} = 0.25 A		t _{rr}	5.0							μs
Typical junction capacitance	4.0 V, 1 MHz		C _J	40							pF

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)										
PARAMETER	SYMBOL	GP30A	GP30B	GP30D	GP30G	GP30J	GP30K	GP30M	UNIT	
Typical thermal resistance	R _{θJA} ⁽¹⁾	20								°C/W
	R _{θJL} ⁽¹⁾	10								

Note

(1) Thermal resistance from junction to ambient and from junction to lead at 0.375" (9.5 mm) lead length, PCB mounted

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
GP30J-E3/54	1.28	54	1400	13" diameter paper tape and reel
GP30J-E3/73	1.28	73	1000	Ammo pack packaging

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)




Fig. 1 - Forward Current Derating Curve








Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[GP30A/54](#) [GP30A-E3/4](#) [GP30A-E3/51](#) [GP30A-E3/54](#) [GP30AHE3/54](#) [GP30B/4](#) [GP30B/54](#) [GP30B-E3/23](#) [GP30B-E3/4](#) [GP30B-E3/51](#) [GP30B-E3/54](#) [GP30B-E3/73](#) [GP30BHE3/54](#) [GP30BHE3/73](#) [GP30D/23](#) [GP30D/54](#) [GP30D-E3/23](#) [GP30D-E3/4](#) [GP30D-E3/51](#) [GP30D-E3/54](#) [GP30D-E3/73](#) [GP30DHE3/54](#) [GP30DHE3/73](#) [GP30DL-E3/22](#) [GP30DL-E3/72](#) [GP30DLHE3/72](#) [GP30G/23](#) [GP30G/4](#) [GP30G/54](#) [GP30GE/54](#) [GP30G-E3/23](#) [GP30G-E3/4](#) [GP30G-E3/51](#) [GP30G-E3/54](#) [GP30GE-E3/54](#) [GP30GEHE3/54](#) [GP30GHE3/54](#) [GP30GHE3/73](#) [GP30J/4](#) [GP30J-E3/23](#) [GP30J-E3/4](#) [GP30J-E3/51](#) [GP30J-E3/54](#) [GP30J-E3/73](#) [GP30JHE3/54](#) [GP30JHE3/73](#) [GP30K/23](#) [GP30K/4](#) [GP30K/54](#) [GP30K-E3/23](#) [GP30K-E3/4](#) [GP30K-E3/51](#) [GP30K-E3/54](#) [GP30K-E3/73](#) [GP30KHE3/54](#) [GP30KHE3/73](#) [GP30M/23](#) [GP30M/4](#) [GP30M/54](#) [GP30M-E3/23](#) [GP30M-E3/4](#) [GP30M-E3/51](#) [GP30M-E3/54](#) [GP30M-E3/73](#) [GP30MHE3/54](#) [GP30MHE3/73](#) [GP30A/1](#) [GP30A/4](#) [GP30A-E3/1](#) [GP30B/1](#) [GP30B/23](#) [GP30B-E3/1](#) [GP30D/1](#) [GP30D/4](#) [GP30D-E3/1](#) [GP30DL/22](#) [GP30G/1](#) [GP30G-E3/1](#) [GP30J/1](#) [GP30J/23](#) [GP30J/54](#) [GP30J-E3/1](#) [GP30K/1](#) [GP30K-E3/1](#) [GP30M/1](#) [GP30M-E3/1](#)