



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER					SIG.			E2
		E1	P1	P2	P3	P4	1	2	3	
51712-003-- NOTE: 3	D C B A									
										
										
										



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
PC	[N/A]	POWER
G	[6.86]	SIGNAL
K	[5.59]	SIGNAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecr no.	dr	date	linear		0.X ± 0.3		COPY		www.fciconnect.com	
A	V03-0808	MEM	7/21/03			0.XX ± 0.13		projection		title 4P + 12S VERTICAL PRESS FIT HEADER	
B	DG06-0011	CS	01/09/06			0.XXX ± 0.051					
C	DG07-0357	JULIA	09/10/07	angles		0° ± 2°		MM		product family	PwrBlade
				dr	M. MOSTOLLER	7/21/03		scale	1:1	size	dwg no
				enrg	M. MOSTOLLER	7/21/03				A	51712-003
				chr	H. BREWBAKER	7/21/03					
				appd	M. MOSTOLLER	7/21/03					
sheet index	revision	sheet		C	C	C	C				
				1	2	3	4				

cage code 22526




Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51712-003--
NOTE: 3



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com			
litr	ecn no.	dr	date	linear	0.X ±0.3		projection 	COPY	title 4P + 12S VERTICAL PRESS FIT HEADER				
C			0.XX ±0.13										
			0.XXX ±0.051										
				angles	0° ±2°			scale 1:1	product family PwrBlade	size A	dwg no 51712-003	code 213 sheet 2	
			dr	M. MOSTOLLER	7/21/03								
			enrg	M. MOSTOLLER	7/21/03								
			chr	H. BREWBAKER	7/21/03								
				appd	M. MOSTOLLER	7/21/03							
sheet index	revision sheet												

cage code 22526


Pro/E



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor, Property of FCI. Copyright FCI.

PRODUCT NUMBER

51712-003__
NOTE: 3

[illegible]

cage code	22526
-----------	-------

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER

51712-003--
NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

3. PLATING:
51712-003 ,51712-003LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.

4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

9 $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER .001 [0.03]
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.

10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

11 CONNECTOR KEEP-OUT ZONE.

12. FOR PRESS FIT APPLICATION USE FCI CAM TOOL 430169-XXX.

mat'l code				tolerances unless otherwise specified				CUSTOMER			
ltr	ecn no.	dr	date	linear	linear	linear	linear	COPY	projection	title	www.fciconnect.com
C					$0.X \pm 0.3$					4P + 12S	
					$0.XX \pm 0.13$					VERTICAL PRESS FIT HEADER	
					$0.XXX \pm 0.051$						
				angles	$0^\circ \pm 2^\circ$						
				dr	M. MOSTOLLER	7/21/03				product family	PwrBlade
				enrg	M. MOSTOLLER	7/21/03				size	dwg no
				chr	H. BREWBAKER	7/21/03				A	51712-003
				appd	M. MOSTOLLER	7/21/03				code	213
sheet index	revision	sheet								sheet	4

Pro/E

cage code 22526