


Panel
Cutout

Electrical Characteristics	
Nominal Impedance:	75 ohms
Frequency Range:	DC to 2 GHz
Operating Voltage (rms):	250 V maximum at sea level
Mechanical Characteristics	
Mating Cycles:	200 cycles minimum
Environmental Characteristics	
Temperature Range:	-55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated
2	Contact	Brass, nickel plated
3	Dielectric	Polypropylene
4	Washer	Brass, nickel plated
5	Nut	Brass, nickel plated

CAD Issue	SN	3	20 May 03
Up Issue	RS	2	31 Jul 00
First Issue	DH	1	12 Jun 97
DESCRIPTION OF REVISION	APPVD	ISS	DATE

 Cinch Connectivity Solutions 7-13 Russel Way, Widford Industrial Estate, Chelmsford,Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515 Fax: +44 (0) 1245 358938	SCALE: Not To Scale	DRAWN BY:	S Nash	F Panel Mount Jack	PART NUMBER:	
	DIMENSIONS: mm	CHECKED BY:	P Couzens		VF310	
	TOLERANCES: ± 0.2mm unless otherwise stated	APPROVED BY:	P Couzens		PAGE: 1 of 1	
		DATE:	20 May 03			