


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO.	SPC-F005	Effective:	12/21/98	Doc No.	860
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	SAS	07/21/99	JC	2/11/00	DJC	4/28/00	



**SPECIFICATIONS:**

1. DO-IT-YOURSELF Ø4mm RETRACTILE SLEEVE STACKING BANANA PLUG, SCREW ATTACHMENT.
2. INSULATOR BODY: POLYACETAL
3. PLUG BODY: BRASS, NICKEL PLATED
4. CONTACT SPRING: BECU, NICKEL PLATED
5. VOLTAGE: 500V
6. CURRENT: 36A MAX.
7. TEMPERATURE: -20°C TO +80°C
8. CONDUCTOR: SIZE Ø.090 (12AWG)
9. INSULATION: Ø.156
10. STRIP LENGTH: .25 (6.4)

<b>DISCLAIMER</b> ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE, AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.				<b>SPC TECHNOLOGY</b>			
Tolerances Unless Otherwise Specified		DRAWN BY:		DATE:		DRAWING TITLE:	
Fractions ± 1/32		SCOTT SERRITELLA		07/21/99		RETRACTILE PLUG, SCREW ATTACHMENT, BLACK	
Decimals .XX ± .01		CHECKED BY:		DATE:		SIZE DWG. NO.	
.XXX ± .005		JOHN COLE		2/11/00		A 2275	
		APPROVED BY:		DATE:		ELECTRONIC FILE	
		DANIEL CAREY		4/28/00		92N4637.DWG	
						REV	
						A	
						SHEET: 1 OF 1	