

> You are here: Home > Products > Cooling > EcoBreeze Air Economizers

- Product Category
- Room Air Conditioners
    - > Uniflair Chilled Water
    - > Uniflair Direct Expansion
    - > EcoBreeze Air Economizers
    - > Portable Cooling
    - > Room Cooling Accessories
  - Close Coupled Air Conditioners (4)
  - Air Distribution (4)
  - Chillers and Heat Rejection (3)

< Return to Cooling

## EcoBreeze Air Economizers

### EcoBreeze Module 400/3/50 Vac



Modular, Indirect Air Economizer for Medium to Large Data Centers

**Includes:** Door key, Installation guide, Operations and maintenance manual

**Standard Lead Time:** Special Order - Call for Quoted Lead Times

★★★★★  
Be the first to [write a review](#)

+ [More Images](#)

ACEC101

Contact Sales

- Email Technical Specifications
- Printer Friendly

General	
Compressor Type	Scroll
Refrigerant Charge	3.18 KG
Air Flow	2359.74 lps
Input	
Number of Power Cords	1
Nominal Input Voltage	400 (3PH)
Input Frequency	50 Hz
Physical	
Maximum Height	2616.00 mm
Maximum Width	2836.00 mm
Maximum Depth	1014.00 mm
Net Length	2.92m
Net Weight	1227.27 KG
Shipping Weight	1227.27 KG
Shipping Height	2769.00 mm
Shipping Width	2921.00 mm
Shipping Depth	1143.00 mm
Color	White
Conformance	
Regulatory Approvals	CE
Standard Warranty	1 year (parts only)
Environmental Compliance	REACH: Contains No SVHCs