



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		FI	REVISED PER ECO-11-005294	06APR2011	RK	HMR

D


D



282857-3 AS SHOWN

C

C



SEE DETAIL L	15.24	3	2-282857-6
-	127.00	25	2-282857-5
-	121.92	24	2-282857-4
-	116.84	23	2-282857-3
-	111.76	22	2-282857-2
-	106.68	21	2-282857-1
-	101.60	20	2-282857-0
-	96.52	19	1-282857-9
-	91.44	18	1-282857-8
-	86.36	17	1-282857-7
-	81.28	16	1-282857-6
-	76.20	15	1-282857-5
-	71.12	14	1-282857-4
-	66.04	13	1-282857-3
-	60.96	12	1-282857-2
-	55.88	11	1-282857-1
-	50.80	10	1-282857-0
-	45.72	9	282857-9
-	40.64	8	282857-8
-	35.56	7	282857-7
-	30.48	6	282857-6
-	25.40	5	282857-5
-	20.32	4	282857-4
-	15.24	3	282857-3
-	10.16	2	282857-2

MARKING	A	POSN	PART NUMBER
---------	---	------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

S. WELDON

24SEP2003

CHK

C. RICHARD

24SEP2003

APVD

C. RICHARD

24SEP2003

DIMENSTONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0

1 PLC ±.2

2 PLC ±.25

3 PLC ±0

4 PLC ±0

ANGLES ±2°

FINISH

MATERIAL

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

NAME

TE Connectivity

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-282857

-

SCALE

4:1

SHEET

1

OF

2

REV

FI

RECOMMENDED PC BOARD LAYOUT

SCALE 5:1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

2

3

1

2

3

DETAIL

L

1

MATERIALS AND FINISH:

HOUSING: PA 6-6, UL 94-V0, COLOR:GREEN.

CLAMP: BRASS, NICKEL PLATED.

TERMINAL: BRASS, TIN PLATED.

CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2.

SUITABLE FOR 1,6-2,4mm. PCB THICKNESS.

3.

END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4.

WIRE SIZE RANGE

SOLID WIRE: 0.03-4mm² (11 AWG)

STRANDED WIRE: 0.03-2.5mm² (13 AWG)

5.

RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE No E60677.

6.

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

7

NOT CUMULATIVE TOLERANCE.

8

NUMERICAL SEQUENCE: FROM LEFT TO RIGHT, WIRE ENTRY SIDE.

9

INK MARKING: WHITE COLOR.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S.WELDON

24SEP2003

CHK
C.RICHARD

24SEP2003

APVD
C.RICHARD

24SEP2003

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

0 PLC

±0

1 PLC

±.2

2 PLC

±.25

3 PLC

±0

4 PLC

±0

ANGLES

±2°

FINISH

NAME

TERMINAL BLOCK, PCB MOUNT, SIDE WIRE ENTRY, STACKING W/INTERLOCK, 5.08mm PITCH

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-282857

RESTRICTED TO

-

SCALE

4:1

SHEET

2

OF

2

REV

F1

1471-9 (3/11)