





D

C

B

A



RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 THICK P.C. BOARD

1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
2. 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
3. 0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL.
4. 0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL.
5. 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

OBSOLETE	BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770859-1
	BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770859-0
	BRASS, GOLD	2	NYLON, UL94V-0	WHITE	-770859-2
	BRASS, TIN-LEAD	3	NYLON, UL94V-0	WHITE	-770859-4
	MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER CHK R JONES APVD R JONES PRODUCT SPEC	OBJUN05 29JUL2003 29JUL2003	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME HEADER ASSEMBLY, 15 CKT, DOUBLE ROW VERTICAL MINI UNIVERSAL MATE-N-LOK	
MATERIAL -		FINISH -		SIZE A1	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 8:1		SHEET 1 OF 1	REV J2