

Printed-circuit board connector - MC 0,5/ 4-G-2,5 THT - 1963447

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




The figure shows a 10-position version of the product

Header, nominal current: 4 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, color: black, contact surface: Tin, mounting: THR soldering, User information and design recommendations for through hole reflow technology can be found under "Downloads"

Why buy this product

- ✓ Designed for integration into the SMT soldering process



Key Commercial Data

Packing unit	50 STK
Minimum order quantity	50 STK
GTIN	 4 017918 912277
GTIN	4017918912277

Technical data

Dimensions

Length [l]	10.1 mm
Pitch	2.5 mm
Dimension a	7.5 mm
Width [w]	11.9 mm
Constructional height	8.1 mm
Height [h]	11.9 mm
Length of the solder pin	3.8 mm
Pin dimensions	0,8 x 0,8
Hole diameter	1.4 mm

General

Range of articles	MC 0,5/...-G-THT
Insulating material group	IIIa

Printed-circuit board connector - MC 0,5/ 4-G-2,5 THT - 1963447

Technical data

General

Rated surge voltage (III/3)	1.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	32 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	4 A
Maximum load current	4 A
Insulating material	PA
Flammability rating according to UL 94	V0
Color	black
Number of positions	4

Standards and Regulations


Connection in acc. with standard	EN-VDE
	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing




Drilling diagram



Printed-circuit board connector - MC 0,5/ 4-G-2,5 THT - 1963447

Dimensional drawing



Approvals

Approvals

Approvals

VDE Gutachten mit Fertigungsüberwachung / IECCEB Scheme / CCA / EAC / cULus Recognized

Ex Approvals

Approval details

VDE Gutachten mit Fertigungsüberwachung		http://www.vde.com/en/Institute/OnlineService/ VDE-approved-products/Pages/Online-Search.aspx	40013394
Nominal current I_N	4 A		
Nominal voltage U_N	32 V		

IECCEB Scheme		http://www.iecee.org/	DE1-56068-B1B2
Nominal current I_N	4 A		
Nominal voltage U_N	32 V		

CCA	CCA/ DE1 34250		
Nominal current I_N	4 A		
Nominal voltage U_N	32 V		

Printed-circuit board connector - MC 0,5/ 4-G-2,5 THT - 1963447

Approvals

EAC		B.01742
-----	---	---------

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-19930913
		B	
Nominal current IN		4 A	
Nominal voltage UN		125 V	

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>