

Schottky Diode



RoHS
Compliant



Features:

- For surface mounted application
- Easy pick and place
- Metal to silicon rectifier, majority carrier conduction
- Low power loss, high efficiency
- High current capability, low VF
- High surge current capability
- Plastic material
- Epitaxial construction
- High temperature soldering : 260°C/10 seconds at terminals

Mechanical Data

Case	: Moulded plastic
Terminals	: Pure tin plated, lead free
Polarity	: Indicated by cathode band
Packing	: 16mm tape per EIA STD RS-481
Weight	: 0.21g

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Type Number	Symbol	SS32	SS33	SS35	SS39	Units
Max. Recurrent Peak Reverse Voltage	V _{RRM}	20	30	50	90	V
Max. RMS Voltage	V _{RMS}	14	21	35	63	
Max. DC Blocking Voltage	V _{DC}	20	30	50	90	
Max. Average Forward Rectified Current at TL	I _(AV)	3				A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	100		70		
Max. Instantaneous Forward Voltage (Note 1) IF = 3A at 25°C at 100°C	V _F	0.5 0.4		0.75 0.65	0.85 0.7	V
Max. DC Reverse Current at TA = 25°C at Rated DC Blocking Voltage at TA = 125°C	I _R	0.5			0.6	mA
		20	10	20	mA	
Typical Junction Capacitance (Note 2)	R _{θJL} R _{θJA}	17 55				°C/W
Operating Temperature Range	T _J	-55 to +125		-55 to +150		°C
Storage Temperature Range	T _{STG}	-55 to +150				

Notes 2. Pulse Test with PW = 300 µseconds, 1% Duty Cycle.

www.element14.com
www.farnell.com
www.newark.com



Ratings and Characteristic Curves (SS32 THRU SS310)

FIG.1- Maximum Forward Current Derating Curve




FIG.2- Maximum Non-Repetitive Peak Forward Surge Current




FIG.3- Typical Forward Characteristics





FIG.4- Typical Reverse Characteristics



Schottky Diode



FIG.5- Typical Junction Capacitance






FIG.6- Typical Transient Thermal Impedance



Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Diode, Schottky, 3A, 20V	SS32
Diode, Schottky, 3A, 30V	SS33
Diode, Schottky, 3A, 50V	SS35
Diode, Schottky, 3A, 90V	SS39

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.