




① ALL MARKING, 06 CHARS
APPROX AS SHOWN
PER (AMP 106-7008)

△ FILL DRILL POINTS WITH
YELLOW LACQUER...

 ENG. CONTROL ONLY - 48754

3					
1	1	C	308032-3	INDENTER	12
2	2	-	2-21000-8	SCREW	11
2	2	C	1-59681-8	WASHER	10
2	2	C	306363	SLEEVE	9
2	2	D	3-304668-5	SPRING	8
1	1	B	307130-2	LOCATOR	7
1	1	C	308031-3	ANVIL	6
2	2	D	302380	SPRING	5
2	2	A	301905	ADJUSTMENT KEY ASS'Y	4
4	4	-	4-23657-8	SCREW	3
2	2	C	301913	INSERT INSULATION	2
4	4	C	306098-3	WASHER	1

				-1	OWG SIZE	NUMBER	NAME	REMARKS	ITEM NO.
REQUIRED PER ASSEMBLY					MATERIAL	HEAT TREAT			COATING OR PLATING
					WIRE RANGE 4	UNLESS OTHERWISE SPECIFIED	REMOVE BURRS, BREAK SHARP EDGES .015 R MAX DECIMALS: .00 & .005, .0001 & .0005, .00001 & .00005	— J —	
					AREA				
					CLASS	TYPED AMP 1-80 NO HOUR CLASS P160			AMP INCORPORATED HARRISBURG, PENNA.
					DR	J. J. Triguera 11-2-73	FIRST USED	69051	
					GIR	John J. Triguera 11-2-73	P.P.F.		
					KPP		LOC	B	NO 48754
					REV	11-2-73	SCALE	2-1	NAME DIE ASSEMBLY MOD-V
DESCRIPTION									

[illegible]