


Heavy Duty RTD Thermometer

Precision measurements over a wide Temperature range
With selectable 0.1° or 0.01° resolution

Features:

- Wide °F/°C measurements from -199.99 to 1562.0°F (-199.99 to 850.0° C)
- Selectable 0.1° or 0.01° display resolution
- Large 0.5" (13mm) 4-1/2 digit (20,000 count) LCD display
- Accurate to $\pm(0.1\% \text{ reading} + 0.4^\circ)$ under 200°F and $\pm(0.1\% \text{ reading} + 1.0^\circ)$ over 200°F
- Built-in linearity correction with fast response
- Sampling time of 0.4 second
- Data Hold to freeze the displayed value
- Built-in RS-232 PC serial interface with optional Data Acquisition software
- Accepts proprietary 4-wire Pt-100Ω RTD probes with $\pm[0.3 + (0.005 \times \text{measured temperature})^\circ\text{C}]$ accuracy
- Dimensions: 7.1 x 2.8 x 1.3" (180 x 72 x 32mm)
Weight: 10oz (285g)
- Complete with protective rubber holster and 9V battery
- Probes are sold separately



Optional 380340 Datalogger and 407001 Data Acquisition software

Ordering Information:

- 407907Heavy Duty RTD Thermometer
 407907-NIST407907 w/ NIST Certificate
 850187RTD General Purpose Probe, -200° to 500°C
 850186RTD Stainless Steel Surface Probe, -200° to 250°C
 850189RTD Stainless Steel Air Probe, -200° to 400°C
 156119117V AC Adaptor
 407001Data Acquisition software program and cable
 140001Hard vinyl carrying case

