


FIG 1

IPL1-106-01-XXX-D-P SHOWN



NOTES:


- 1. © REPRESENTS A CRITICAL DIMENSION.
- 2. NOTE DELETED.

DO NOT

SCALE FROM

THIS PRINT

- 3. MINIMUM TERMINAL RETENTION: 1 LB.
- 4. PARTS TO BE MOLDED TO POSITION.
- 5. POST MUST BE WITHIN .005[.13] OF EACH OTHER.
- 6. ALL PIN TO PIN DIMENSIONS TO BE MEASURED
- FROM TIP TO TIP. 7. NOTE DELETED.
- 8. DIMENSION TO BE MEASURED AT BEND.
- 9. TIP TO BE FLUSH TO .015 BELOW TOP OF SHROUD.
- 10. BOTH ROWS TO BE SYMMETRIC WITHIN .010[0.25].
- 11.THIS NUMBER REPRESENTS THE NUMBER OF POSITIONS PER ROW ONLY AND IS NOT INTENDED TO BE USED IN POSITION NUMBERING.
- 12. 1 OR 2 GATE PADS TO BE PRESENT AT VENDOR DISCRETION.



IPL1-1XX-XX-XXX-D-XX-X-XX No OF POSITIONS -02 THRU -25 (PER ROW) LEAD STYLE -01: THROUGH HOLE

(USE T-1S64-XX-XX)

-02: SURFACE MOUNT (SEE FIG 2, SHT 2) (USE T-1S64-XX-XX)

PLATING SPECIFICATION-

- -F: FLASH SELECTIVE (USE T-1S64-XX-F)
- -L: LIGHT SELECTIVE (USE T-1S64-XX-L)
- -S: SELECTIVE (USE T-1S64-XX-S)
- -H: HEAVY GOLD (T-1S64-XX-H) -FM: FLASH SELECTIVE/MATTE TIN TAILS (USE T-1S64-XX-F)
- -LM: LIGHT SELECTIVE/MATTE TIN TAILS (USE T-1S64-XX-L)
- -SM: SELECTIVE/MATTE TIN TAILS (USE T-1S64-XX-S)
- -STL: SELECTIVE/ TIN/LEAD TAILS (USE T-1S64-XX-STL)

PACKAGING OPTION -TR: TAPE & REEL

(AVAILABLE WITH -02 LEAD STYLE ONLY) (MUST USE K-DOT-.256-.375-.005) (SEE FIG 8, SHT 3)

OPTION

-P: POLARIZATION (SEE FIG 1)

(USE IPL1-XX-D-P)

(NOT AVAILABLÉ W/ -K OR -G, OPTIONS)

-K: KEYED POLARIZATION (USE IPL1-XX-D-K) (SEE FIG 5, SHEET 3)

(NOT AVAILABLE W/ -P OR -G, OPTIONS)

-G: GUIDE POSTS (SEE FIG 6 & 7, SHEET 3) (USE IPL1-XX-D-GP) (NOT AVAILABLE W/-P, -K OPTIONS)

(LEAVE BLANK FOR NO POLARIZATION (SEE FIG 4, SHEET 3), SAMTEC WILL ONLY SUPPORT

EXISTING BUSINESS AS OF REV U)

-RA: RIGHT ANGLE (SEE FIG 3, SHT 2) (AVAILABLE WITH -01 LEAD STYLE ONLY)

ROW SPECIFICATION

-D: DOUBLE (USE IPL1-XX-D)




TABLE 1							
LEAD STYLE	ОРПОМ	TERMINAL 1	OAL REF	TERMINAL 2	OAL REF	-TR	
-01	NONE	T-1S64-07-X	.430[10.92]	N/A	N/A	N/A	
-01	-RA	T-1S64-09-X	.530[13.46]	T-1S64-10-X	.730[18.54]	N/A	
-02	NONE	T-1S64-08-X	.445[11.30]	N/A	N/A	K-DOT256375005	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE: **ANGLES DECIMALS** .XX: ±.01[.3] ± 2° .XXX: ±.005[.13]

TERMINAL: PHOS BRONZE

.XXXX: ±.0020[.051]

CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR

DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION

SHEET SCALE: 3:1

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

.100[2.54] DOUBLE ROW TERMINAL ASSEMBLY

IPL1-1XX-XX-XXX-D-XX-X-XX

C:\EnterpriseVault\DWG\MISC\MKTG\IPL1-1XX-XX-XXX-D-XX-X-XX-MKT.slddrw

DO NOT SCALE DRAWING

INSULATOR: LCP UL94-V0, COLOR: BLACK

-K INSULATOR: LCP UL94-V0, COLOR: NATURAL

BY: KEVIN B 03/11/02

SHEET 1 OF 3

REVISION AH

FIG 2
IPL1-106-02-XXX-D-P SHOWN
[DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1]






TABLE 2					
No OF POS.	COPLANARITY				
-02 THRU -05	.004[.10]				
-06 THRU -10	.005[.13]				
-11 THRU -25	.006[.15]				

-02: SURFACE MOUNT IN PROCESS 1




-02: SURFACE MOUNT IN PROCESS 2



PACKAGING VIEWS

(ASSEMBLIES TO HAVE POSITION #1 LOADED IN THE SAME DIRECTION AS ARROW ON TUBE, EXCEPT WITH -RA OPTION)




LEAD STYLE

-01

-01 (2 POSITION)

-01

-02



OPTION


NONE

NONE

-RA

NONE

PACKAGING TABLE




PACKAGING TUBE

PT-1-24-15-29

PT-TSM004-DV

PT-1-24-04-40


PT-1-24-02-08




	7
PLUG	
TP-07	
TP-07	

TP-07

TP-13



 $\frac{\text{FIG 3}}{\text{IPL1-106-01-XXX-D-RA-P SHOWN}} \\ \text{(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)}$



C:\EnterpriseVault\DWG\MISC\MKTG\IPL1-1XX-XX-XXX-D-XX-XX-MKT.slddrw

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMICE, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHER OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMICE, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322


DESCRIPTION:


.100[2.54] DOUBLE ROW TERMINAL ASSEMBLY


DWG.

IPL1-1XX-XX-XXX-D-XX-XX

BY: KEVIN B 03/11/02 SHEET 2 OF 3











FIG 4 (IPL1-106-01-XXX-D SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

SAMTEC WILL ONLY SUPPORT **EXISTING BUSINESS AS OF REV. U)**



<u>FIG 5</u> (IPL1-106-01-XXX-D-K SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 4)








FIG 6 (IPL1-106-01-XXX-D-RA-G SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 3)







<u>FIG 7</u> (IPL1-102-01-XXX-D-G SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)











FIG 8 (IPL1-106-02-XXX-D-TR SHOWN) (MUST USE K-DOT-.256-.375-.005) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 2)







PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

.100[2.54] DOUBLE ROW TERMINAL ASSEMBLY

IPL1-1XX-XX-XXX-D-XX-XX SHEET 3 OF 3

03/11/02 BY: KEVIN B