


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

10	11	96.52[3.800]	99.06[3.900]	78	12	9-534267-0
		91.44[3.600]	93.98[3.700]	74	12	8-534267-9
		88.90[3.500]	91.44[3.600]	72	12	8-534267-8
		86.36[3.400]	88.90[3.500]	70	12	8-534267-7
		83.82[3.300]	86.36[3.400]	68	12	8-534267-6
		81.28[3.200]	83.82[3.300]	66	12	8-534267-5
		78.74[3.100]	81.28[3.200]	64	12	8-534267-4
		76.20[3.000]	78.74[3.100]	62	12	8-534267-3
		71.12[2.800]	73.66[2.900]	58	12	8-534267-2
		68.58[2.700]	71.12[2.800]	56	12	8-534267-1
		66.04[2.600]	68.58[2.700]	54	12	8-534267-0
		63.50[2.500]	66.04[2.600]	52	12	7-534267-9
		55.88[2.200]	58.42[2.300]	46	12	7-534267-8
		53.34[2.100]	55.88[2.200]	44	12	7-534267-7
		50.80[2.000]	53.34[2.100]	42	12	7-534267-6
		45.72[1.800]	48.26[1.900]	38	12	7-534267-5
		40.64[1.600]	43.18[1.700]	34	12	7-534267-4
		38.10[1.500]	40.64[1.600]	32	12	7-534267-3
		33.02[1.300]	35.56[1.400]	28	12	7-534267-2
		25.40[1.000]	27.94[1.100]	22	12	7-534267-1
10	11	12.70[.500]	15.24[.600]	12	12	7-534267-0
		17.78[.700]	20.32[.800]	16	12	6-534267-9
		60.96[2.400]	63.50[2.500]	50	12	6-534267-8
		2.54[.100]	5.08[.200]	4	12	6-534267-7
		93.98[3.700]	96.52[3.800]	76	12	6-534267-6
		43.18[1.700]	45.72[1.800]	36	12	6-534267-5
		5.08[.200]	7.62[.300]	6	12	6-534267-4
			2.54[.100]	2	12 6	6-534267-3
		35.56[1.400]	38.10[1.500]	30	12	6-534267-2
		58.42[2.300]	60.96[2.400]	48	12	6-534267-1
		20.32[.800]	22.86[.900]	18	12	6-534267-0
		27.94[1.100]	30.48[1.200]	24	12	5-534267-9
		73.66[2.900]	76.20[3.000]	60	12	5-534267-8
		48.26[1.900]	50.80[2.000]	40	12	5-534267-7
		30.48[1.200]	33.02[1.300]	26	12	5-534267-6
		7.62[.300]	10.16[.400]	8	12	5-534267-5
		99.06[3.900]	101.60[4.000]	80	12	5-534267-4
		10.16[.400]	12.70[.500]	10	12	5-534267-3
		22.86[.900]	25.40[1.000]	20	12	5-534267-2
		15.24[.600]	17.78[.700]	14	12	5-534267-1
	FINISH	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002		 TE Connectivity			
		CHK J.OLSON 06NOV02					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU			
		APVD J.OLSON 06NOV02					
		PRODUCT SPEC 108-25022					
		APPLICATION SPEC 114-25018					
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± ±		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		WEIGHT		A2 00779		C=534267	
FINISH		CUSTOMER DRAWING		SCALE		SHEET	
				1:1		2 of 2	
						REV AB5	