

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

FT

0


CI

REVISED PER ECO-12-007964

02MAY2012

KH

MS



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.

2

SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3


RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.

4


IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.



NOT CUMULATIVE TOLERANCE.



282816-2 AS SHOWN




3.75 REF

3.25±0.15

1.00±0.02


10.0±0.1



125	13	1-282816-3
115	12	1-282816-2
105	11	1-282816-1
95	10	1-282816-0
85	9	282816-9
75	8	282816-8
65	7	282816-7
55	6	282816-6
45	5	282816-5
35	4	282816-4
25	3	282816-3
15	2	282816-2

DIM. A N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.2
1 PLC ±.2
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±2

MATERIAL

FINISH

DWN

E. ZANOLINI

CHK

D. BIEVENOUR

APVD

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING

STE

TE Connectivity

NAME

TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE CLOSED ENDS
10mm PITCH

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-282816

RESTRICTED TO

-

SCALE 3:1

SHEET

OF

REV

CI