


NAIS

1 Form A Slim Power Relay

LD-RELAYS

FEATURES



mm inch

1. Slim type: Width 7 mm .276 inch.

20.3(L)×7.0(W)×15.0(H) mm
.799(L)×.276(W)×.591(H) inch

2. Perfect for small load switching of home appliances

10⁵ switching operations possible with a 3A 250V AC resistive load.

3. Low operating power

Compact size, nominal operating power as low as 200mW.

4. High shock resistance

The relay withstands a functional shock resistance of 300m/s² [approx. 30 G more]

5. High insulation resistance

- Creepage distance and clearances between contact and coil: Min. 6 mm .236 inch(In compliance with IEC65)
- Surge withstand voltage between contact and coil: 10,000 V or more.

6. UL/CSA, VDE, TÜV approved.

SPECIFICATIONS

Contact

Arrangement		1 Form A
Initial contact resistance, max. (By voltage drop 6 V DC 1 A)		Max. 100 mΩ
Contact material		Silver alloy
Rating (resistive load)	Nominal switching capacity	
	3 A 277 V AC, 3 A 30V DC	
	Max. switching power	
	831 V A (AC), 90W (DC)	
Max. switching voltage		277 V AC, 30 V DC
Max. switching current		3 A
Expected life (min.operations)	Mechanical (at 180 cpm)	
	5×10 ⁶	
	Electrical (at 20 cpm)	3A 125V AC, 3A 30V DC
	(at rated load)	2×10 ⁵
		3A 250V AC
		10 ⁵

Coil

Nominal operating power	200 mW
-------------------------	--------

Remarks

- * Specifications will vary with foreign standards certification ratings.
^{*1} Measurement at same location as "Initial breakdown voltage" section.
^{*2} Detection current: 10mA
^{*3} Wave is standard shock voltage of ±1.2×50ms according to JEC-212-1981
^{*4} Excluding contact bounce time.
^{*5} Half-wave pulse of sine wave: 11 ms; detection time: 10 μs
^{*6} Half-wave pulse of sine wave: 6 ms
^{*7} Detection time: 10 μs
^{*8} Refer to 5. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT (Page 24).

Characteristics

Max. operating speed		20 cpm (at rated load)
Initial insulation resistance*1		Min. 1,000 MΩ (at 500 V DC)
Initial*2 breakdown voltage	Between open contacts	750 Vrms for 1 min.
	Between contact and coil	4,000 Vrms for 1 min.
Initial surge voltage between contact and coil*3		Min. 10,000 V
Operate time*4 (at nominal voltage)		Max. 10ms (at 20°C 68°F)
Release time (with diode)*4 (at nominal voltage)		Max. 10ms (at 20°C 68°F)
Temperature rise (at 70°C)		Max. 45°C with nominal coil voltage and at 3 A contact carrying current (resistance method)
Shock resistance	Functional*5	Min. 300 m/s²{approx. 30 G}
	Destructive*6	Min. 1,000 m/s²{approx. 100 G}
Vibration resistance	Functional*7	10 to 55Hz at double amplitude of 1.5mm
	Destructive	10 to 55Hz at double amplitude of 1.5mm
Conditions for operation, transport and storage*8 (Not freezing and condens- ing at low tempera- ture)	Ambient temp.	-40°C to +70°C -40°F to +158°F
	Humidity	5 to 85% R.H.
Unit weight		Approx. 4 g .141 oz

TYPICAL APPLICATIONS

- Air conditioner
- Refrigerator
- Hot water units
- Microwave ovens
- Fan heaters

ORDERING INFORMATION

Ex. A LD 1 12

Product name	Contact arrangement	Coil voltage(V DC)
LD	1: 1 Form A	4H: 4.5, 09: 9, 24: 24 05: 5, 12: 12 06: 6, 18: 18

UL/CSA, TÜV approved type is standard.


Note: Standard packing: Carton: 50pcs, Case: 1,000pcs

TYPES AND COIL DATA (at 20°C 68°F)


Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (max.) (Initial)	Drop-out voltage, V DC (min.) (Initial)	Coil resistance, Ω (±10%)	Nominal operating current, mA (±10%)	Nominal operating power, mW	Maximum allow- able voltage, V DC (at 20°C 68°F)
ALD14H	4.5	3.38	0.22	101	44.6	200	5.85
ALD105	5	3.75	0.25	125	40.0	200	6.5
ALD106	6	4.5	0.3	180	33.3	200	7.8
ALD109	9	6.75	0.45	405	22.2	200	11.7
ALD112	12	9	0.6	720	16.7	200	15.6
ALD118	18	13.5	0.9	1,620	11.1	200	23.4
ALD124	24	18	1.2	2,880	8.3	200	31.2

DIMENSIONS

mm inch




PC board pattern (Bottom view)



Tolerance: ±0.1±.004

Schematic (Bottom view)




Dimension:
Max. 1mm .039 inch:
1 to 3mm .039 to .118 inch:
Min. 3mm .118 inch:


General tolerance
±0.1 ±.004
±0.2 ±.008
±0.3 ±.012

REFERENCE DATA

1. Max. switching power




2. Life curve




3. Coil temperature rise


Sample: ALD112, 6 pcs.
Point measured: inside the coil
Contact current: 0 A, 3 A




4-(1). Operate time
Sample: ALD112, 6 pcs.



4-(2). Release time (without diode)
Sample: ALD112, 6 pcs.




4-(3). Release time (with diode)
Sample: ALD112, 6 pcs.




5-(1). Electrical life test
(3 A 250 V AC, resistive load)


Sample: ALD112, 6 pcs.
Operating speed: 20 cpm
Ambient temperature: room temperature
circuit:



Change of pick-up and drop-out voltage




Change of contact resistance




5-(2). Electrical life test
(3 A 30 V DC, resistive load)


Sample: ALD112, 6 pcs.
Operating speed: 20 cpm
Ambient temperature: room temperature
circuit:



Change of pick-up and drop-out voltage



Change of contact resistance



For Cautions for Use, see Relay Technical Information (Page 11 to 39).