

UNIDIRECTIONAL THYRISTOR SURGE SUPPRESSOR**APPLICATIONS**

- ✓ SLIC Line Card
- ✓ DBX Branch Exchange Switches
- ✓ FCC Part 68 Customer Premise Equipment
- ✓ Line Interface Modem
- ✓ ISDN Architecture Interface

IEC COMPATIBILITY (EN61000-4)



- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns
- ✓ 61000-4-5 (Surge): 8/20μs - 95A, L4(Line-Gnd), 48A, L4(Line-Line) & 83A, L2(Power)

FEATURES

- ✓ *Complies with: FCC Part 68, UL 1459, Bellcore 1089, ITU-K.20 & K.21*
- ✓ Peak Off-State Voltage: 58 Volts
- ✓ Surge Current Capability(See Table 1)
- ✓ ESD Protection > 40 kilovolts

MECHANICAL CHARACTERISTICS

- ✓ Molded Plastic DO-214AA Package
- ✓ Weight 2.5 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ Device Marking: Logo, Marking Code & Polarity Band or Notch on Top Surface


**DEVICE SYMBOL
(UNIDIRECTIONAL)**
**TABLE 1 - SURGE RATINGS**

SERIES	I_{PP} 2 X 10μs AMPS	I_{PP} 10 X 1000μs AMPS	I_{TSM} 60 Hz AMPS	di/dt AMPS/μs (See Note 1)	dv/dt AMPS/μs (See Note 1)
SA	125	40	20	500	2000

Note 1: Critical Rate of Rise for On-State Current (di/dt) and Off-State Voltage (dv/dt).

DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Surge Current - 50/60 Hz	I_{TSM}	60	Amps
Junction Temperature	T_J	-40 to 150	°C
Storage Temperature	T_{STG}	-55 to 150	°C
Thermal Resistance(Junction)	$R_{\theta ja}$	28	°C/Watt
Thermal Resistance(Ambient)	$R_{\theta ja}$	90	°C/Watt

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified									
PART NUMBER	DEVICE MARKING CODE	REPETITIVE PEAK OFF-STATE VOLTAGE	SWITCHING VOLTAGE	MINIMUM HOLDING CURRENT (See Fig. 4)	SWITCHING CURRENT	MAXIMUM OFF-STATE CURRENT (See Fig. 3)	MAXIMUM ON-STATE VOLTAGE (See Fig. 3)	ON-STATE CURRENT	TYPICAL CAPACITANCE
		V_{DRM} VOLTS	@ 100V/ μ s V_s VOLTS	$di/dt = 1A/ms$ I_H mA	I_S mA	@ V_{DRM} I_{DRM} μ A	@ I_T V_T VOLTS	I_T AMPS	@ 50V, 1 MHz C pF
PP0641SA	JD	58	70	150	800	5	5	1.0	90





FIGURE 4




FIGURE 5




FIGURE 6




FIGURE 7






FIGURE 7



PACKAGE OUTLINE & DIMENSIONS



TAPE & REEL PACKAGING:

Surface mount product is taped and reeled in accordance with EIA-481, reel quantities and sizes are as follows:

7 Inch Reel - 3,000 pieces per reel; 13 Inch Reel - N/A

ProTek Devices
2929 South Fair Lane, Tempe, AZ 85282
Tel: 602-431-8101 Fax: 602-431-2288
E-Mail: sales@protekdevices.com
Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.