



Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Drawings
 - PDFNon-Shrink P ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips € Within Results

Text Search: 'TV105-.75TL20Y'

Your search criteria matched only one product, shown below

TV105-.75TL20Y



- Non-Shrink oil resistant flexible clear tubing on reel
- Provides insulation and protection for lead wires wire harness assemblies soldered joints and components in electrical and electronic equipment
 - Material: Polyvinyl chloride (PVC)
 - Voltage Rating: 300V and 600V
 - All purpose flexible non -shrinkable
 - Resistant to heat and moisture
- Applicable Specifications:
- UL224 VW-1
 - CSA C22.2 No. 198.1 (OFT)
 - ASTM D-922 Grade CFR
 - MIL-I-631 Type F, Form U, Grade C- Class 1 Category 1

Part Number	TV105-.75TL20Y
RoHS Compliance Status	Compliant
Note	TV105-.75TL20Y replaces TV105-.75C20Y
Part Description	PVC NonShrink Tubing, 105°C rated
Material	Polyvinyl Chloride
Color	Black
CSA Certified	Yes
CSA Specification	CSA C22.2 No. 198.1 (OFT)
UL Recognized	E122770
UL Recognized Specification	UL224 VW-1
Flammability Rating	UL224 VW-1
Length Per Reel (ft.)	250
Length Per Reel (m)	76.2
Max. Inside Diameter (In.)	.786
Max. Inside Diameter (mm)	19.96
Max. Voltage Rating	600 V
Min. Inside Diameter (mm)	19.05
Minimum Inside Diameter (In.)	.750
Nominal Size	3/4
Pricing Description	Vinyl Tubing, .75" (19.1mm), 600V, Black
Temperature Range	-4°F to 221°F (20°C to 105°C)
Wall Thickness (In.)	.035
Wall Thickness (mm)	.89
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	€

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.