



✓ Active

TE CONNECTIVITY (TE)

N SERIES CABLE PLUG, LMR-240 C

Standard Coax | LM , LSR

6274532-1

TE Internal Number: 6274532-1

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

Connector Interface N Type

Connector Style Plug

Mated Outer Diameter (Approximate) 19.05 mm [.75 in]

Impedance (Ω) 50

Cable Type LMR-240

 **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

N SERIES CABLE PLUG

PDF [\(TIFF AVAILABLE\)](#)

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface N Type

Connector Style Plug

Connector & Contact Terminates To Wire & Cable

Electrical Characteristics

Impedance (Ω) 50

Body Features

Cable Connector Orientation Straight

Body Material Brass

Body Plating Material Silver

Contact Features

Crimp Type Hex

Ferrule Plating Material Silver

Center Contact Plating Material Gold

RF Connector Contact Configuration Captivated Contacts

Ferrule Material Brass

Termination Features

Termination Method to Wire & Cable Crimp

Dimensions

Mated Outer Diameter (Approximate) 19.05 mm [.75 in]

Usage Conditions

Cable Type LMR-240

Packaging Features

Packaging Method Carton

Other

Dielectric Material PTFE

Grade Commercial

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF