

TIL, TIG, TIH, TII-Series



The TI-Series Tippette rocker switches are available in single pole (TIL), double pole (TIG), three pole (TIH) and four pole (TII) versions. These switches are available with nylon snap-in or screw-type mounting brackets, are AC rated to 20 amps and suitable for low voltage DC applications. Multiple actuator options and colors are available, and many circuits have international approvals.

- Specifications**
- Certifications*: UL, CSA, and VDE
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Phenolic
 - Actuator Material: Nylon
 - Bracket/Bezel Material: Nylon or Steel
- * Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



TIG		K	5	1	-	6S	-	BL	-	NBL
SERIES		CIRCUIT		RATING ¹		ACTUATOR STYLE ²		ACTUATOR COLOR ³		
TIL	SINGLE POLE	SINGLE POLE		5	10A 250VAC	1C	CROSS SERRATED	BL	BLACK	
TIG	DOUBLE POLE	A ON-NONE-OFF			15A 125VAC	1F	SMOOTH W/	WH	WHITE	
TIH	THREE POLE	B ON-NONE-ON			3/4HP 125-250VAC		FLATTED CENTER			
TII	FOUR POLE	C ON-OFF-ON		6	3A 250VAC	1L	LONG LINED	BRACKET STYLE ⁴		
		DOUBLE, THREE OR			6A 125VAC	1S	SMOOTH ANGLED			
		FOUR POLE			1/4HP 125-250VAC	2L	LONG NARROW	A		
		K ON-NONE-OFF		9	10A 250VAC		SMOOTH	B		
		L ON-NONE-ON			15A 125VAC	6M ⁵	MATTE CURVED	C		
		M ON-OFF-ON			12(6)A 250VAC T85		(M, N OR W	H		
				72	20A 125-277VAC		BRACKETS ONLY)	FN	NARROW	
					1 1/2HP 125VAC	6S	SMOOTH CURVED	FW	WIDE	
					2HP 250VAC		(M, N OR W	MBL	MARINE	
							BRACKETS ONLY)	NBL		
						7N	WITCHES HAT	WBL	WATERSHEDDING	
							(NARROW)			
						7P	WITCHES HAT			
						7S	TOGGLE			
TERMINATION/FUNCTION										
		FUNCTION		SOLDER LUG		.250 TAB (QC)	.187 TAB (QC)	SCREW TERM.	WIRE LEAD	PC TERM.
		ON-NONE-OFF		0	1	3	4	5	6	
		(ON)-NONE-OFF		A	B	D	E	F	G	
		ON-NONE-(OFF)		L	M	R	S	T	U	
		ON-NONE-ON		0	1	3	4	5	6	
		ON-NONE-(ON)		A	B	D	E	F	G	
		ON-OFF-ON		0	1	3	4	5	6	
		ON-OFF-(ON)		A	B	D	E	F	G	
		(ON)-OFF-(ON)		L	M	R	S	T	U	

NOTES:

Shading indicates standard configurations.

Dust covers for single and double pole are available, consult factory.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

1 Horsepower rating for code 5 is applicable to certain circuits only. Consult factory for specifics.

Rating Code 9 for TIG-Series only with maintained A, B, K, L and M Circuits, and N Bracket Style, terminals 0 or 1 only.

Rating Code 72 for TIG-Series only, in maintained circuits, with N or W Bracket Style only.

2 For double actuator with or without interlock or other actuator styles,consult factory.

Imprinting available on smooth face rockers.

3 Glossy finish is standard. Custom colors are available. Consult factory.

4 Barbs are available on FN style bracket to accommodate panel thicknesses of .062, .100, .125, .156 and .250. Specify after bracket selection. (ex.) FN/125

MBL, NBL & WBL brackets are molded in black. If white is desired, specify as MWH, NWH & WWH.

Bracket Styles D, E and G available. Consult factory.

Bracket Style M consists of LNP rocker, neoprene seal, syntech grease, dummy rivets. M, N and W brackets supplied in two pole bases.

MBL does not have UL, CSA approvals.

Bracket style H available with actuator styles 7N and 7P only.

5 Actuator & Bracket Finish is a matched set.

Special Circuits for Tippette Rocker Switches

CIRCUIT	POSITION 1	POSITION 2	POSITION 3
PROGRESSIVE TWO CIRCUIT			
GG	BOTH CIRCUITS ON	ONE CIRCUIT ON	OFF
GG	BOTH CIRCUITS (ON)	ONE CIRCUIT ON	OFF
SINGLE POLE TRIPLE THROW			
GE	ON	ON	ON
TWO CIRCUIT			
GH	CIRCUIT 1 ON	BOTH CIRCUITS ON	CIRCUIT 2 ON
GP	CIRCUIT 2 ON	CIRCUIT 1 ON	OFF
REVERSING DOUBLE POLE DOUBLE THROW			
GO	ON	OFF	ON
GX	ON	NONE	ON



TII

SOLDER LUG	.250 TAB (Q.C.)	.187 TAB (Q.C.)
TERMINAL TYPE		
SCREW (ASSEMBLED)	WIRE LEAD	PRINTED CIRCUIT

Actuator Styles/Dimensions: in. [mm]



1L

TIL, TIG, TIH, TII




1C

TIL, TIG, TIH, TII



1S

TIL, TIG, TIH, TII



1F

TIG, TII



2L

TIL, TIG, TIH, TII




6S

TIG




7S

TIG



7N

TIG



7P

TIG

NOTES:
Additional momentary circuits are available. Consult factory for details.

Bracket Dimensions: in. [mm]



TAPPED HOLE

Standard with
A & B Brackets



CLEARANCE HOLE

Standard with
C Bracket



MOUNTING HOLE

(Nylon Snap-in Brackets)

Panel Thickness:

.030 min. - .250 max.

* Angled corners are suggested for optimum fit. Standard rectangular cutout is acceptable.

TIL	TIG	TII	TIH



FN

TIL, TIG, TIH, TII
METAL, SNAP-IN



FW

TIL, TIG, TIH, TII
METAL, SNAP-IN

MARINE / STD / WATERSHEDDING



MBL, NBL, WBL

TIG
BLACK NYLON, SNAP-IN

NOTES

Double brackets supplied on TII-Series when B style bracket is specified. Consult factory for dimensional information.

* Available in both clearance and tapped hole options. Please specify when ordering.