


OPTION A



CIRCUIT NO. 1
SLOT OR ARROW



SECTION C-C



PRE-LOADED
ASSEMBLY



FINAL
ASSEMBLY

WIRE (SEE NOTE 3)

- NOTES:
1. MATERIAL:
HOUSING: POLYESTER(PBT), GLASS FILLED, UL94 V-0,
COLOR: BLACK
TERMINAL: PHOSPHOR BRONZE
2. FINISH:
TIN: 3.81 MICROMETERS/150 MICROINCHES MINIMUM TIN
OVER NICKEL UNDERPLATE OVERALL
3. TO BE USED WITH 26 AWG STRANDED WIRE WITH (1.35)/.053
DIAMETER MAXIMUM INSULATION
4. SEE TABLE FOR AVAILABLE CIRCUIT SIZES
5. STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING
MAY BE AVAILABLE, REQUEST DRAWING PK-70400
6. PARTS STACKABLE END TO END ON (2.54)/.100 CENTERS
7. PRODUCT SPECIFICATION: PS-70400
8. SEE DRAWING SDA-70400-**** (SHEET 3) FOR OPTIONAL
HOUSING DETAILS
9. 4 CIRCUIT SHOWN
10. TO MATE WITH MOLEX 2.54/.100 CENTERLINE HEADERS
11. 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS

CKT. SIZE	A	B	EDP. NO.
2	(2.54) .100	(5.05) .199	I4-60-0023
3	(5.08) .200	(7.59) .299	I4-60-0033
4	(7.62) .300	(10.13) .399	I4-60-0043
5	(10.16) .400	(12.67) .499	I4-60-0053
6	(12.70) .500	(15.21) .599	I4-60-0063
7	(15.24) .600	(17.75) .699	I4-60-0073
8	(17.78) .700	(20.29) .799	I4-60-0083
9	(20.32) .800	(22.83) .899	I4-60-0093
10	(22.86) .900	(25.37) .999	I4-60-0103
11	(25.54) 1.000	(27.91) 1.099	I4-60-0113
12	(27.94) 1.100	(30.45) 1.199	I4-60-0123
13	(30.48) 1.200	(32.99) 1.299	I4-60-0133
14	(33.02) 1.300	(35.53) 1.399	I4-60-0143
15	(35.56) 1.400	(38.07) 1.499	I4-60-0153
16	(38.01) 1.500	(40.61) 1.599	I4-60-0163
17	(40.64) 1.600	(43.15) 1.699	I4-60-0173
18	(43.18) 1.700	(45.69) 1.799	I4-60-0183
19	(45.72) 1.800	(48.23) 1.899	I4-60-0193
20	(48.26) 1.900	(50.77) 1.999	I4-60-0203
21	(50.80) 2.000	(53.31) 2.099	I4-60-0213
22	(53.34) 2.100	(55.85) 2.199	I4-60-0223
23	(55.88) 2.200	(58.39) 2.299	I4-60-0233
24	(58.42) 2.300	(60.93) 2.399	I4-60-0243
25	(60.96) 2.400	(63.47) 2.499	I4-60-0253

I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
B	26 AWG.

PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
TIN	NONE

REMOVE ENG NO. EC NO: UCP2011-110 DRWN:MSI BARRA 2010/10/19 CHKD:J MORGAN 2010/10/19 APPR:SMILLER 2010/11/24	DESCRIPTION	QUALITY SYMBOLS F =0 F =0 F =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY MSI BARRA	DATE 2010/10/19	TITLE ASSY,SL CONNECTOR SINGLE ROW 2.54/.100 GRID				
			4 PLACES	± ---	± ---	CHECKED BY WAZ	DATE 1984/10/09					
			3 PLACES	± ---	± .010	APPROVED BY SMILLER	DATE 2010/11/24					
			2 PLACES	± 0.25	± .014	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
1 PLACE	± 0.35	± ---	SEE TABLE		SDA-70400-0176-0199		1 OF 1					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									