


BD CONNECTOR (3.5mm)

3.5mm pitch/Disconnectable Crimp style connectors



Board-to-wire connector with high withstanding voltage, used for power supply of LCD (Liquid Crystal Display) back light.

- Secure locking mechanism
- · High withstand voltage design
- Low profile
- Compatibility

Specifications ——

• Current rating: 1.0A AC, DC (AWG #24)

Voltage rating: 1,400V AC, DC
Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/10m Ω max.

After environmental testing/20m Ω max.

• Insulation resistance: 1,000M Ω min. • Withstanding voltage: 3,000V AC/minute

• Applicable wire: AWG #28 to #24

* Compliant with RoHS.

* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.


* Contact JST for details.

Standards -


Recognized E60389

PC board layout (viewed from component side) and Assembly layout


Through-hole type



SMT type



Contact



Model No.	Applicable wire		Inculation (D. (mm)	Oltre / road
	mm ²	AWG#	InsulationO.D. (mm)	Q ty / reer
SBHS-002T-P0.5A	0.08~0.22	28~24	0.9~1.7	10,000

Material and Finish

Phosphor bronze, tin-plated (reflow treatment)


RoHS compliance

Note: Contact JST for SBHS-002T-P0.5.

	Crimping	Applicator			
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies	
ODUO COST DO FA	4 D 16041	MKS-L	MK/SBHS-002-05	APLMK SBHS002-05	
SBHS-002T-P0.5A	AP-K2N	_	_	_	

BD CONNECTOR (3.5mm)

Housing




Circuits	Model No.	Q'ty / bag		
2	BDMR-02VS-2	1,000		
Material				

PA 66, UL94V-0, natural (white)

RoHS compliance

Header



Through-hole type

Circuits	Model No.	Q'ty / box
2	S02-BDS-3-B	1,000

Material and Finish

Press pin: Brass, Copper-undercoated, tin-plated (reflow treatment) Wafer: Heat resisting resin, UL94V-0, natural (ivory) Solder tab: Brass, Copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label.

SMT type

Circuits	Model No.	Q'ty / reel
2	SM02-BDS-3-TB	1,000

Material and Finish

Post: Brass, Copper-undercoated, tin-plated (reflow treatment) Wafer: Heat resisting resin, UL94V-0, natural (ivory) Solder tab: Brass, Copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label. Note: The product listed above is supplied on embossed tape.