


"FF08GAF" SERIES FAN FILTERS

Description: **Fan Filter 115/230 Va.c.**



Type of material:

PC/ABS Alloy, PA 66 GF13 HSL for elastic clips

Standard color:

RAL 7035, other colors on request

Protection degree:

IP54, according to EN 60529 std
Type 12, according to UL 508 std

Fixing system:

by elastic clips, otherwise by four self-threading screws

Plate thickness:

from 1 mm to 2 mm

Storage temperature:

from -40°C to +70°C

Motor Lifetime L10 at 40°C (approx.):

over 40,000 h

Motor protection:

impedance

Earth connection:

(by M4 screw on fan's casing)

Electrical connection:

UL 3266 AWG22 lead wires

Appliance class:

class I

Type of filter media:

thermo-linked progressive structure synthetic fibre

Filtering class:

class G3, according to EN 779

Degree of separation:

85% - DIN 24185

Dust retention capacity:

600 g/m²

Note:

filter media is washable about 10 times


Weight:

0.542 Kg



Approvals:

CE, UL E237844

technical drawing (standard flow)



mounting cut-out



Model	Voltage (V)	Frequency (Hz)	Rated Current (A)	Rated Power (W)	Max Air Flow** (m3/h)	Static Pressure (Pa)	Fan Noise [db(A)]	Rated Temp. Range (°C)	Approvals
FF08GA115UF	115 V a.c.	50/60	0.145/0.127	12/10	22/26	41/57	37.0/42.0	-10 ÷ +55	CE; cURus
FF08GA230UF	230 V a.c.	50/60	0.078/0.068	12/11	22/26	41/57	37.0/42.0	-10 ÷ +55	CE; cURus

data with uncertainty of 15%

All specifications, data and drawing are subject to change without notice and are approximate. Please refer to our terms of sales including our warranty and limited liabilities clauses.