



FCIconnect.com

Copyright FCI

PRODUCT NUMBER
71991-YXXXLF

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 6.

OPTIONAL LETTER

H: HIGH TEMPERATURE PRODUCT.

NUMBER OF POSITIONS PER ROW: 02 TO 50.

PLATING CODE

3= 0.76µm GOLD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

4= 5µm TIN-LEAD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

8= 0.38µm GOLD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0
LOW TEMPERATURE: COLOR BLUE
HIGH TEMPERATURE: COLOR GREY.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 0.08 = 20.24$ mm
- 5 - RECOMMENDED IR PROFIL PER TA 842.
- 6 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.




b - MANUFACTURING PROCESS COMPATIBILITY



- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.


c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-22-008



mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX							
ltr ecn na dr date				tolerances unless otherwise specified				mm		title BtB RECEPT. VERT DR TMT							
R F10132 DLE 01.02.06		angles		Linear												±0.3	
S F04.0347 DLE 04.09.27																	
T F06-0137 DLE 06.02.27				±2°				scale 5:1		dwg no sheet 1 of 2 size 71991 A3							
U F06-0204 DLE 06.06.20		dr		D LEGRAND		04.09.27											
V F06-0323 DLE 06.11.21		enr		P NIZZI		04.09.27											
P F10110 GCO 01.01.16				chr		D LEGRAND		04.09.27		type CUSTOMER Drawing							
				appd		P NZ		04.09.27									
sheet index		revision		V B													
		sheet		1 Z													



mat'l. code				surface		tolerance		projection		product family	
SEE SHEET 1				ISO 1302 ✓		ISO 406 ISO 1101		⌀		DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm		title	
A	F04-0347	DLE	04.09.27	angles		±0.3		↔		BtB RECEIPT.	
B	F06-0204	DLE	06.06.20	linear				scale 5:1		VERT DR TMT	
				±2°						dwg no	
				dr		D LEGRAND		04.09.27		sheet 2 of 2	
				engr		P NIZZI		04.09.27		size	
				chr		D LE		04.09.27		A4	
				appd		P NZ		04.09.27		type	
										CUSTOMER	
										Drawing	
sheet index	revision										
	sheet										