

HPR7XXC

5 WATT UNREGULATED SIP DC/DC CONVERTER

FEATURES

- ROHS COMPLIANT
- EFFICIENCY >80%
- SIP PACKAGE
- HIGH POWER DENSITY: >16 WATTS/INCH³



- LOW COST
- SINGLE AND DUAL OUTPUTS
- INTERNAL INPUT AND OUTPUT FILTERING
- SIX-SIDED SHIELDING

DESCRIPTION


The HPR7XXC Series provides high power densities where space is critical. The small SIP package measures only 2.2" x .3" x .4" (56 x 9 x 10 mm). Designed for high density boards, the package is non-conductive, which presents advantages over painted metal enclosures.

The series includes many different voltage models (other input and output voltages are available upon request), all set in a low thermal resistance molding compound, called Iso-ThermoFlex™, which provides excellent heat dissipation of internal components. The use of surface mount devices and manufacturing processes, combined with the encapsulation process, assure the user that the product is more environmentally rugged than any other DC/DC converter of its type.

Operation down to no load will not impact the reliability of the series, although this product has a 10mA minimum load for specification purposes. It is recommended that all pins be used for current carrying capacity even though duplicate pin-outs are internally connected.

The HPR7XXC has 500VDC isolation barrier between input and output, offering the designer maximum flexibility in grounding options and polarity configurations. The outstanding MTTF, superior reliability, and low cost make it an excellent choice for any high power-density applications.

MECHANICAL



ELECTRICAL CHARACTERISTICS

Specifications typical at $T_A = +25^{\circ}\text{C}$, nominal input voltage, rated output current unless otherwise specified.

MODEL	NOMINAL INPUT VOLTAGE (VDC)	RATED OUTPUT VOLTAGE (VDC)	RATED OUTPUT CURRENT (mA)	INPUT CURRENT		REFLECTED RIPPLE CURRENT (mAp-p)	EFFICIENCY (%)
				NO LOAD (mA)	RATED LOAD (mA)		
HPR700C	5	5	1000	70	1250	15	80
HPR703C	5	± 5	± 500	70	1250	15	80
HPR704C	5	± 12	± 208	70	1190	15	84
HPR705C	5	± 15	± 167	70	1190	15	84
HPR706C	12	5	1000	25	490	15	80
HPR710C	12	± 12	± 208	25	490	15	85
HPR711C	12	± 15	± 167	25	490	15	85
HPR712C	15	5	1000	20	407	15	82
HPR717C	15	± 15	± 167	20	392	15	85

Note: Other input to output voltage options may be available. Please consult factory.

COMMON SPECIFICATIONS

Specifications typical at $T_A = +25^{\circ}\text{C}$, nominal input voltage, rated output current unless otherwise specified.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
INPUT Voltage Range		4.75	5	5.25	VDC
		11.4	12	12.6	VDC
		14.2	15	15.8	VDC
Voltage Rise Time	See Application Note: "Capacitive Loading Effects on Start-Up of DC/DC Converters"				
ISOLATION Rated Voltage Test Voltage Resistance Capacitance Leakage Current	60 Hz, 10 seconds $V_{ISO} = 240\text{VAC}, 60\text{Hz}$	500			VDC
		500			Vpk
			1		GW
			55		pF
			5		μArms
OUTPUT Rated Power Voltage Setpoint Accuracy Temperature Coefficient Ripple & Noise Voltage	Rated Load, Nominal V_{IN} BW = DC to 10MHz BW = 10Hz to 2MHz $I_L = 10\text{mA}, V_{OUT} = 5\text{V}$ $I_L = 10\text{mA}, V_{OUT} = \pm 12\text{V}$ $I_L = 10\text{mA}, V_{OUT} = \pm 15\text{V}$		5		W
			± 3		%
			± 0.05		%/Deg C
			50		mVp-p
			5		mVrms
				5.75	VDC
				13.10	VDC
REGULATION Line Regulation Load Regulation (5V out only) Load Regulation (All other Models)	High Line to Low Line Rated Load to No Load Rated Load to No Load		1.2		%/%Vin
			15		%
			10		%
GENERAL Switching Frequency Package Weight MTTF per MIL-HDBK-217, Rev. E Ground Benign	Circuit Stress Method $T_A = +25^{\circ}\text{C}$		170		kHz
			7		g
			2000		kHr
TEMPERATURE Specification Operation Storage		-25	+25	+70	$^{\circ}\text{C}$
		-40		+85	$^{\circ}\text{C}$
		-40		+110	$^{\circ}\text{C}$

ABSOLUTE MAXIMUM RATINGS





Internal Power Dissipation.....1.7W
Short Circuit Protection.....Momentary
Lead Temperature (soldering, 10 seconds max).....+300 $^{\circ}\text{C}$

ORDERING INFORMATION

Device Family _____ **HPR** **7XX** **C**
HPR indicates DC/DC converter
Model Number _____
RoHS Compliant _____

TYPICAL PERFORMANCE CURVES

Specifications typical at $T_A = +25^\circ\text{C}$, rated input voltage, rated output current unless otherwise specified.



THROUGH-HOLE SOLDERING INFORMATION

These devices are intended for wave soldering or manual soldering.

They are not intended to be subject to surface mount processes under any circumstances.

The normal wave soldering process can be used with these devices where the device is subjected to a maximum wave temperature of 260°C for a period of no more than 10 seconds. Within this time and temperature range, the integrity of the device's plastic body will not be compromised and internal temperatures within the converter will not exceed 175°C . Care should be taken to control manual soldering limits identical to that of wave soldering.

The information provided herein is believed to be reliable; however, MuraTA POWER SOLUTIONS assumes no responsibility for inaccuracies or omissions. MuraTA POWER SOLUTIONS assumes no responsibility for the use of this information, and all use of such information shall be entirely at the user's own risk. Prices and specifications are subject to change without notice. No patent rights or licenses to any of the circuits described herein are implied or granted to any third party. MuraTA POWER SOLUTIONS does not authorize or warrant any MuraTA POWER SOLUTIONS product for use in life support devices/systems or in aircraft control applications.



Murata Power Solutions, Inc.

11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A.

Tel: (508) 339-3000 (800) 233-2765 Fax: (508) 339-6356

www.murata-ps.com email: sales@murata-ps.com ISO 9001 & ISO 14001 REGISTERED

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.
© 2008 Murata Power Solutions, Inc.

USA: Mansfield (MA), Tel: (508) 339 3000, email: sales@murata-ps.com

Canada: Toronto, Tel: (866) 740 1232, email: toronto@murata-ps.com

UK: Milton Keynes, Tel: +44 (0)1908 615232, email: mk@murata-ps.com

France: Montigny Le Bretonneux, Tel: +33 (0)1 34 60 01 01, email: france@murata-ps.com

Germany: München, Tel: +49 (0)89-544334-0, email: ped.munich@murata-ps.com

Japan: Tokyo, Tel: 3-3779-1031, email: sales_tokyo@murata-ps.com

Osaka, Tel: 6-6354-2025, email: sales_osaka@murata-ps.com

China: Shanghai, Tel: +86 215 027 3678, email: shanghai@murata-ps.com

Guangzhou, Tel: +86 208 221 8066, email: guangzhou@murata-ps.com

Singapore: Parkway Centre, Tel: +65 6348 9096, email: singapore@murata-ps.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[HPR700C](#) [HPR703C](#) [HPR704C](#) [HPR705C](#) [HPR706C](#) [HPR709C](#) [HPR710C](#) [HPR711C](#) [HPR712C](#) [HPR715C](#)
[HPR716C](#) [HPR717C](#)