

4

3

2

1


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B2	REVISED PER ECO-11-005150	29MAR2011	RK	HMR

1 FOR FURTHER INFORMATION SEE DATA SHEET FOR HS SERIES-ALUMINIUM HOUSED RESISTORS

2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE AND TOLERANCE, PLEASE REFER TO DMF


M6 ST/STEEL TERMINAL STUDS.
EACH SUPPLIED WITH:-
2 OFF M6 ST/STEEL FULL NUTS
2 OFF M6/STEEL PLAN WASHERS

GOLD ANODISED
ALUMINIUM HOUSINGS




HSC200
ALUMINIUM HOUSED
POWER RESISTOR

RoHS Compliant



SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L LUONG 10.MAR.03		TE Connectivity											
		CHK J CATCHPOLE 10.MAR.03													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HSC200 ALUMINIUM HOUSED POWER RESISTOR -											
		0 PLC ±0.5 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±5°													
MATERIAL -		FINISH -		PRODUCT SPEC -		APPLICATION SPEC -		SIZE A3		CAGE CODE 00779		DRAWING NO C=1630019		RESTRICTED TO -	
CUSTOMER DRAWING										SCALE 1:1		SHEET 1 OF 1		REV B2	