

# NCP4523

## CMOS 3CH-LDOs for RF Unit

The NCP4523 Series are multi voltage regulator ICs with high output voltage accuracy, extremely low supply current, low noise, low ON-resistance and high ripple rejection by CMOS process. The NCP4523 Series contain three voltage regulators. Each of these voltage regulators in the NCP4523 Series consists of a voltage reference unit, an error amplifier, resistors for setting output voltage, a current limit circuit and a chip enable circuit.

The chip enable function contributes to prolong battery life. Further, regulators in the NCP4523 Series are with low dropout voltage, excellent load transient response and line transient response, thus the NCP4523 series are very suitable for the power supply for hand-held communication equipment.

The output voltage of each regulator is fixed with high accuracy by laser trim.

Since the package for these ICs is SSOP-8, high density mounting of the ICs on boards is possible.

### Features

- Ultra-Low Supply Current
- Low Standby Current
- Low Dropout Voltage
- High Ripple Rejection, Typical 70 dB ( $f = 1.0$  kHz)
- High Output Voltage Accuracy,  $\pm 2.0\%$
- Excellent Load Transient Response and Line Transient Response
- Small Package 8-Pin SSOP
- Maximum Input Voltage 6.0 V
- Pb-Free Packages are Available


### Applications

- Power Source for Cellular Phones such as GSM, CDMA and Personal Handy-Phone System
- Power Source for Electrical Appliances such as Cameras, VCRs, Camcorders, etc.
- Power Source for Battery-Powered Equipment




**ON Semiconductor®**

<http://onsemi.com>




**SSOP-8  
G SUFFIX  
CASE 487**

### MARKING DIAGRAM



xxxx = Product Code  
yy = Lot Number

### PIN ASSIGNMENT



(Top View)

**SSOP-8**

### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 22 of this data sheet.

### DEVICE MARKING INFORMATION

See general marking information in the device marking section on page 22 of this data sheet.

# NCP4523

## PIN DESCRIPTION

| Pin Number         | Symbol            | Description     |
|--------------------|-------------------|-----------------|
| NCP4523G<br>SSOP-8 |                   |                 |
| 1                  | V <sub>OUT1</sub> | Output Pin      |
| 2                  | V <sub>OUT2</sub> | Output Pin      |
| 3                  | V <sub>OUT3</sub> | Output Pin      |
| 4                  | GND               | Ground Pin      |
| 5                  | CE3               | Chip Enable Pin |
| 6                  | CE2               | Chip Enable Pin |
| 7                  | CE1               | Chip Enable Pin |
| 8                  | V <sub>DD</sub>   | Input Pin       |

## ABSOLUTE MAXIMUM RATINGS

| Rating                                                                                    | Symbol            | Value                        | Unit |
|-------------------------------------------------------------------------------------------|-------------------|------------------------------|------|
| Input Voltage                                                                             | V <sub>IN</sub>   | 7.0                          | V    |
| Input Voltage (CE Pin)                                                                    | CE                | -0.3 ~ V <sub>IN</sub> + 0.3 | V    |
| Output Voltage                                                                            | V <sub>OUT</sub>  | -0.3 ~ V <sub>IN</sub> + 0.3 | V    |
| Output Current (V <sub>OUT1</sub> )                                                       | I <sub>OUT1</sub> | 200                          | mA   |
| Output Current (V <sub>OUT2</sub> )                                                       | I <sub>OUT2</sub> | 100                          | mA   |
| Output Current (V <sub>OUT3</sub> )                                                       | I <sub>OUT3</sub> | 100                          | mA   |
| Power Dissipation                                                                         | P <sub>D</sub>    | 300                          | mW   |
| Operating Temperature Range                                                               | T <sub>opt</sub>  | -40 ~ 85                     | °C   |
| Storage Temperature Range                                                                 | T <sub>stg</sub>  | -55 ~ 125                    | °C   |
| Electrostatic Discharge Sensitivity (ESD)<br>Human Body Model (HBM)<br>Machine Model (MM) | ESD               | 2000<br>200                  | V    |

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

# NCP4523

## ELECTRICAL CHARACTERISTICS

VR1 ( $T_{opt} = 25^{\circ}\text{C}$ )

| Characteristics                        | Conditions                                                                                  | Symbol                          | Min           | Typ       | Max           | Unit                    |
|----------------------------------------|---------------------------------------------------------------------------------------------|---------------------------------|---------------|-----------|---------------|-------------------------|
| Output Voltage                         | $V_{IN} - V_{OUT} = 1.0\text{ V}$<br>$1.0\text{ mA} \leq I_{OUT} \leq 30\text{ mA}$         | $V_{OUT}$                       | $\times 0.98$ | –         | $\times 1.02$ | V                       |
| Output Current                         | $V_{IN} - V_{OUT} = 1.0\text{ V}$                                                           | $I_{OUT}$                       | 150           | –         | –             | mA                      |
| Load Regulation                        | $V_{IN} - V_{OUT} = 1.0\text{ V}$<br>$1.0\text{ mA} \leq I_{OUT} \leq 80\text{ mA}$         | $\Delta V_{OUT}/\Delta I_{OUT}$ | –             | 12        | 40            | mV                      |
| Dropout Voltage                        | Refer to Electrical Characteristic by Output Voltage (VR1)                                  | $V_{DIF}$                       | –             | –         | –             | –                       |
| Supply Current                         | $V_{IN} - V_{OUT} = 1.0\text{ V}$                                                           | $I_{SS}$                        | –             | 70        | 120           | $\mu\text{A}$           |
| Supply Current (Standby)               | $V_{IN} - V_{OUT} = 1.0\text{ V}$<br>$V_{CE} = \text{GND}$                                  | $I_{standby}$                   | –             | 0.1       | 1.0           | $\mu\text{A}$           |
| Line Regulation                        | $V_{OUT} + 0.5\text{ V} \leq V_{IN} \leq 6.0\text{ V}$<br>$I_{OUT} = 30\text{ mA}$          | $\Delta V_{OUT}/\Delta V_{IN}$  | –             | 0.05      | 0.20          | %/V                     |
| Ripple Rejection                       | $f = 1.0\text{ kHz}$ , sinusoidal $0.5\text{ V}_{p-p}$<br>$V_{IN} - V_{OUT} = 1.0\text{ V}$ | RR                              | –             | 70        | –             | dB                      |
| Input Voltage                          | –                                                                                           | $V_{IN}$                        | –             | –         | 6.0           | V                       |
| Output Voltage Temperature Coefficient | $I_{OUT} = 50\text{ mA}$<br>$-40^{\circ}\text{C} \leq T_{opt} \leq 85^{\circ}\text{C}$      | $\Delta V_{OUT}/\Delta T$       | –             | $\pm 100$ | –             | ppm/ $^{\circ}\text{C}$ |
| Short Current Limit                    | $V_{OUT} = 0\text{ V}$                                                                      | $I_{LIM}$                       | –             | 50        | –             | mA                      |
| CE Pull-down Resistance                | –                                                                                           | $R_{DN}$                        | 2.5           | 5.0       | 10            | $\text{M}\Omega$        |
| CE Input Voltage "H"                   | –                                                                                           | $V_{CEH}$                       | 1.5           | –         | $V_{IN}$      | V                       |
| CE Input Voltage "L"                   | –                                                                                           | $V_{CEL}$                       | 0.00          | –         | 0.25          | V                       |
| Output Noise                           | $\text{BW} = 10\text{ Hz} - 100\text{ kHz}$                                                 | $e_n$                           | –             | 60        | –             | $\mu\text{V}_{rms}$     |

## ELECTRICAL CHARACTERISTICS BY OUTPUT VOLTAGE (VR1)

| Output Voltage<br>$V_{OUT}$ (V) | Dropout Voltage $V_{DIF}$ (V) |      |      |
|---------------------------------|-------------------------------|------|------|
|                                 | Condition                     | Typ  | Max  |
| $2.0 \leq V_{OUT} \leq 2.4$     | $I_{OUT} = 150\text{ mA}$     | 0.35 | 0.55 |
| $2.5 \leq V_{OUT} \leq 2.7$     |                               | 0.30 | 0.45 |
| $2.8 \leq V_{OUT} \leq 3.3$     |                               | 0.22 | 0.35 |

# NCP4523

## ELECTRICAL CHARACTERISTICS

VR2 ( $T_{opt} = 25^{\circ}\text{C}$ )

| Characteristics                        | Conditions                                                                                  | Symbol                          | Min           | Typ       | Max           | Unit                       |
|----------------------------------------|---------------------------------------------------------------------------------------------|---------------------------------|---------------|-----------|---------------|----------------------------|
| Output Voltage                         | $V_{IN} - V_{OUT} = 1.0\text{ V}$<br>$1.0\text{ mA} \leq I_{OUT} \leq 30\text{ mA}$         | $V_{OUT}$                       | $\times 0.98$ | –         | $\times 1.02$ | V                          |
| Output Current                         | $V_{IN} - V_{OUT} = 1.0\text{ V}$                                                           | $I_{OUT}$                       | 80            | –         | –             | mA                         |
| Load Regulation                        | $V_{IN} - V_{OUT} = 1.0\text{ V}$<br>$1.0\text{ mA} \leq I_{OUT} \leq 50\text{ mA}$         | $\Delta V_{OUT}/\Delta I_{OUT}$ | –             | 12        | 40            | mV                         |
| Dropout Voltage                        | Refer to Electrical Characteristic<br>by Output Voltage (VR2)                               | $V_{DIF}$                       | –             | –         | –             | –                          |
| Supply Current                         | $V_{IN} - V_{OUT} = 1.0\text{ V}$                                                           | $I_{SS}$                        | –             | 70        | 120           | $\mu\text{A}$              |
| Supply Current (Standby)               | $V_{IN} - V_{OUT} = 1.0\text{ V}$<br>$V_{CE} = \text{GND}$                                  | $I_{standby}$                   | –             | 0.1       | 1.0           | $\mu\text{A}$              |
| Line Regulation                        | $V_{OUT} + 0.5\text{ V} \leq V_{IN} \leq 6.0\text{ V}$<br>$I \leq 30\text{ mA}$             | $\Delta V_{OUT}/\Delta V_{IN}$  | –             | 0.05      | 0.20          | V                          |
| Ripple Rejection                       | $f = 1.0\text{ kHz}$ , sinusoidal $0.5\text{ V}_{p-p}$<br>$V_{IN} - V_{OUT} = 1.0\text{ V}$ | RR                              | –             | 70        | –             | dB                         |
| Input Voltage                          | –                                                                                           | $V_{IN}$                        | –             | –         | 6.0           | V                          |
| Output Voltage Temperature Coefficient | $I_{OUT} = 30\text{ mA}$<br>$-40^{\circ}\text{C} \leq T_{opt} \leq 85^{\circ}\text{C}$      | $\Delta V_{OUT}/\Delta T$       | –             | $\pm 100$ | –             | ppm/<br>$^{\circ}\text{C}$ |
| Short Current Limit                    | $V_{OUT} = 0\text{ V}$                                                                      | $I_{LIM}$                       | –             | 50        | –             | mA                         |
| CE Pull-down Resistance                | –                                                                                           | $R_{DN}$                        | 2.5           | 5.0       | 10            | $\text{M}\Omega$           |
| CE Input Voltage “H”                   | –                                                                                           | $V_{CEH}$                       | 1.5           | –         | $V_{IN}$      | V                          |
| CE Input Voltage “L”                   | –                                                                                           | $V_{CEL}$                       | 0.00          | –         | 0.25          | V                          |
| Output Noise                           | $\text{BW} = 10\text{ Hz} - 100\text{ kHz}$                                                 | $e_n$                           | –             | 60        | –             | $\mu\text{V}_{rms}$        |

## ELECTRICAL CHARACTERISTICS BY OUTPUT VOLTAGE (VR2)

| Output Voltage<br>$V_{OUT}$ (V) | Dropout Voltage $V_{DIF}$ (V) |      |      |
|---------------------------------|-------------------------------|------|------|
|                                 | Condition                     | Typ  | Max  |
| $2.0 \leq V_{OUT} \leq 2.4$     | $I_{OUT} = 80\text{ mA}$      | 0.22 | 0.38 |
| $2.5 \leq V_{OUT} \leq 2.7$     |                               | 0.20 | 0.38 |
| $2.8 \leq V_{OUT} \leq 3.3$     |                               | 0.16 | 0.24 |

# NCP4523

## ELECTRICAL CHARACTERISTICS


VR3 (T<sub>opt</sub> = 25°C)

| Characteristics                        | Conditions                                                                              | Symbol                          | Min           | Typ       | Max           | Unit   |
|----------------------------------------|-----------------------------------------------------------------------------------------|---------------------------------|---------------|-----------|---------------|--------|
| Output Voltage                         | $V_{IN} - V_{OUT} = 1.0 \text{ V}$<br>$1.0 \text{ mA} \leq I_{OUT} \leq 30 \text{ mA}$  | $V_{OUT}$                       | $\times 0.98$ | –         | $\times 1.02$ | V      |
| Output Current                         | $V_{IN} - V_{OUT} = 1.0 \text{ V}$                                                      | $I_{OUT}$                       | 80            | –         | –             | mA     |
| Load Regulation                        | $V_{IN} - V_{OUT} = 1.0 \text{ V}$<br>$1.0 \text{ mA} \leq I_{OUT} \leq 50 \text{ mA}$  | $\Delta V_{OUT}/\Delta I_{OUT}$ | –             | 12        | 40            | mV     |
| Dropout Voltage                        | Refer to Electrical Characteristic by Dropout Voltage (VR3)                             | $V_{DIF}$                       | –             | –         | –             | –      |
| Supply Current                         | $V_{OUT} + 0.5 \text{ V} \leq V_{IN} \leq 6.0 \text{ V}$<br>$I_{OUT} = 30 \text{ mA}$   | $I_{SS}$                        | –             | 70        | 120           | μA     |
| Supply Current (Standby)               | $f = 1.0 \text{ kHz}$ , sinusoidal 0.5 Vp-p<br>$V_{IN} - V_{OUT} = 1.0 \text{ V}$       | $I_{standby}$                   | –             | 0.1       | 1.0           | μA     |
| Line Regulation                        | –                                                                                       | $\Delta V_{OUT}/\Delta V_{IN}$  | –             | 0.05      | 0.20          | %/V    |
| Ripple Rejection                       | $I_{OUT} = 30 \text{ mA}$<br>$-40^{\circ}\text{C} \leq T_{opt} \leq 85^{\circ}\text{C}$ | RR                              | –             | 70        | –             | dB     |
| Input Voltage                          | $V_{OUT} = 0 \text{ V}$                                                                 | $V_{IN}$                        | –             | –         | 6.0           | V      |
| Output Voltage Temperature Coefficient | –                                                                                       | $\Delta V_{OUT}/\Delta T$       | –             | $\pm 100$ | –             | ppm/°C |
| Short Current Limit                    | BW = 10 Hz – 100 kHz                                                                    | $I_{LIM}$                       | –             | 50        | –             | mA     |
| CE Pull-down Resistance                | –                                                                                       | $R_{DN}$                        | 2.5           | 5.0       | 10            | MΩ     |
| CE Input Voltage “H”                   | –                                                                                       | $V_{CEH}$                       | 1.5           | –         | $V_{IN}$      | V      |
| CE Input Voltage “L”                   | –                                                                                       | $V_{CEL}$                       | 0.00          | –         | 0.25          | V      |
| Output Noise                           | –                                                                                       | $e_n$                           | –             | 60        | –             | μVrms  |

## ELECTRICAL CHARACTERISTICS BY OUTPUT VOLTAGE (VR3)


| Output Voltage<br>$V_{OUT}$ (V) | Dropout Voltage $V_{DIF}$ (V) |      |      |
|---------------------------------|-------------------------------|------|------|
|                                 | Condition                     | Typ  | Max  |
| $2.0 \leq V_{OUT} \leq 2.4$     | $I_{OUT} = 80 \text{ mA}$     | 0.24 | 0.38 |
| $2.5 \leq V_{OUT} \leq 2.7$     |                               | 0.22 | 0.28 |
| $2.8 \leq V_{OUT} \leq 3.3$     |                               | 0.16 | 0.24 |

# NCP4523



**Figure 1. Block Diagram**

## NCP4523




**Figure 2. Operation**


Fluctuation of each regulator's output voltage, or  $V_{OUT1,2,3}$  is detected individually. Then it is put back to an error amplifier through feedback resistors, or  $R1_1$ ,  $R2_1$ ,  $R1_2$ ,  $R2_2$ ,  $R1_3$ ,  $R2_3$  and compared with a reference voltage and compensated for the result and make a constant voltage.

In each regulator, short protection is made with a current limit circuit and standby mode is available by a chip enable circuit.


# NCP4523



**Figure 3. Basic Test Circuit**



**Figure 4. Test Circuit for Supply Current**



**Figure 5. Test Circuit for Line Transient Response**

# NCP4523




Figure 6. Test Circuit for Load Transient Response




Figure 7. Test Circuit for Ripple Rejection




Figure 8. Supply Current vs Input Voltage




Figure 9. Output Voltage vs. Output Current




Figure 10. Output Voltage vs. Output Current




Figure 11. Output Voltage vs. Output Current




Figure 12. Output Voltage vs. Input Voltage




Figure 13. Output Voltage vs. Input Voltage




Figure 14. Output Voltage vs. Input Voltage




Figure 15. Ripple Rejection vs. Input Voltage (DC Bias)




Figure 16. Ripple Rejection vs. Input Voltage (DC Bias)




Figure 17. Ripple Rejection vs. Input Voltage (DC Bias)




Figure 18. Ripple Rejection vs. Input Voltage (DC Bias)




Figure 19. Ripple Rejection vs. Input Voltage (DC Bias)




Figure 20. Ripple Rejection vs. Input Voltage (DC Bias)




Figure 21. Output Voltage vs. Temperature




Figure 22. Output Voltage vs. Temperature




Figure 23. Output Voltage vs. Temperature




Figure 24. Supply Current vs. Temperature




Figure 25. Supply Current vs. Temperature




Figure 26. Supply Current vs. Temperature




Figure 27. Dropout Voltage vs. Set Output Voltage




Figure 28. Dropout Voltage vs. Set Output Voltage




Figure 29. Dropout Voltage vs. Set Output Voltage




Figure 30. Ripple Rejection vs. Frequency




Figure 31. Ripple Rejection vs. Frequency




Figure 32. Ripple Rejection vs. Frequency

# NCP4523




Figure 33. Ripple Rejection vs. Frequency




Figure 34. Ripple Rejection vs. Frequency




Figure 35. Ripple Rejection vs. Frequency




Figure 36. Dropout Voltage vs. Output Current




Figure 37. Dropout Voltage vs. Output Current






Figure 38. Dropout Voltage vs. Output Current


# NCP4523



**Figure 39. Line Transient Response**




**Figure 40. Line Transient Response**




**Figure 41. Line Transient Response**


# NCP4523



**Figure 42. Line Transient Response**




**Figure 43. Line Transient Response**




**Figure 44. Line Transient Response**


# NCP4523



**Figure 45. Line Transient Response**




**Figure 46. Line Transient Response**




**Figure 47. Line Transient Response**

# NCP4523



**Figure 48. Load Transient Response**

# NCP4523



**Figure 49. Load Transient Response**

# NCP4523




Figure 50. Load Transient Response

## Technical Notes

(Pin numbers of the diagram below are applied to NCP4523)

To use this IC with ceramic capacitors, ESR should be set in the range of the following graphs. Test circuit for Noise level measurement is shown below.




Figure 51.

Noise level is measured with a spectrum analyzer and hatched area shows stable areas of which noise level is approximately equal or less than  $40\text{ }\mu\text{V}$  (Avg.). The relation between Load Current ( $I_{\text{OUT}}$ ) and Equivalent Series Resistors (ESR) value of external output capacitor with the stable area is shown below.




Figure 52. Ceramic Capacitor 1.0  $\mu\text{F}$




Figure 53. Ceramic Capacitor 2.2  $\mu\text{F}$




Figure 54. Ceramic Capacitor 1.0  $\mu\text{F}$




Figure 55. Ceramic Capacitor 2.2  $\mu\text{F}$




Figure 56. Ceramic Capacitor 1.0  $\mu\text{F}$




Figure 57. Ceramic Capacitor 2.2  $\mu\text{F}$

# NCP4523

## ORDERING INFORMATION


| Device        | S/N for Voltage Setting | Output Voltage |     |     | Marking      | Package          | Shipping <sup>†</sup> |
|---------------|-------------------------|----------------|-----|-----|--------------|------------------|-----------------------|
|               |                         | VR1            | VR2 | VR2 | Product Code |                  |                       |
| NCP4523G1T1   | 1                       | 2.8            | 2.8 | 2.8 | B01A         | SSOP-8           | 3000 Tape and Reel    |
| NCP4523G1T1G  | 1                       | 2.8            | 2.8 | 2.8 | B01A         | SSOP-8 (Pb-Free) | 3000 Tape and Reel    |
| NCP4523G3T1   | 3                       | 3.0            | 3.0 | 3.0 | B03A         | SSOP-8           | 3000 Tape and Reel    |
| NCP4523G3T1G  | 3                       | 3.0            | 3.0 | 3.0 | B03A         | SSOP-8 (Pb-Free) | 3000 Tape and Reel    |
| NCP4523G20T1  | 20                      | 2.35           | 2.8 | 2.8 | B20A         | SSOP-8           | 3000 Tape and Reel    |
| NCP4523G20T1G | 20                      | 2.35           | 2.8 | 2.8 | B20A         | SSOP-8 (Pb-Free) | 3000 Tape and Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

# NCP4523

## PACKAGE DIMENSIONS

SSOP-8  
G SUFFIX  
CASE 487-01  
ISSUE O




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION D APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.25 AND 0.30 MM FROM TERMINAL.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

| DIM | INCHES    |       | MILLIMETERS |      |
|-----|-----------|-------|-------------|------|
|     | MIN       | MAX   | MIN         | MAX  |
| A   | 0.106     | 0.122 | 2.70        | 3.10 |
| B   | 0.102     | 0.118 | 2.60        | 3.00 |
| C   | 0.039     | 0.051 | 1.00        | 1.30 |
| D   | 0.004     | 0.012 | 0.10        | 0.30 |
| E   | 0.073     | 0.081 | 1.85        | 2.05 |
| F   | 0.012     | 0.024 | 0.30        | 0.60 |
| G   | 0.026 TYP |       | 0.65 TYP    |      |
| H   | 0.019 TYP |       | 0.475 TYP   |      |
| J   | 0.004     | 0.006 | 0.11        | 0.14 |
| K   | 0.000     | 0.008 | 0.00        | 0.20 |
| L   | 0.150     | 0.165 | 3.80        | 4.20 |

### SOLDERING FOOTPRINT\*



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA  
**Phone:** 480-829-7710 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 480-829-7709 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada

**Japan:** ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
**Phone:** 81-3-5773-3850

**ON Semiconductor Website:** <http://onsemi.com>

**Order Literature:** <http://www.onsemi.com/litorder>

For additional information, please contact your  
local Sales Representative.