


# Air Slide Table

## Series **MXS**


ø6, ø8, ø12, ø16, ø20, ø25

### Features

- Work table and air cylinder are integrated. Air slide table is ideal for precise assembly.
- Improved workpiece mounting repeatability.
- Wide variety of options: Adjuster option, with stroke adjuster, with shock absorber, etc.
- Shock absorber and symmetric types are released.



Standard Type



Symmetric Type

### Specifications

| Bore size (mm)                | 6                                                                                                                               | 8  | 12 | 16 | 20  | 25 |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------|----|----|----|-----|----|
| Piping port size              | M3                                                                                                                              | M5 |    |    | 1/8 |    |
| Fluid                         | Air                                                                                                                             |    |    |    |     |    |
| Action                        | Double acting                                                                                                                   |    |    |    |     |    |
| Operating pressure            | 0.15 to 0.7 MPa                                                                                                                 |    |    |    |     |    |
| Proof pressure                | 1.05 MPa                                                                                                                        |    |    |    |     |    |
| Ambient and fluid temperature | -10 to 60°C                                                                                                                     |    |    |    |     |    |
| Piston speed                  | 50 to 500 mm/s                                                                                                                  |    |    |    |     |    |
| Cushion                       | Rubber bumper (Standard, With stroke adjuster)<br>Shock absorber (Option)                                                       |    |    |    |     |    |
| Lubrication                   | Non-lube                                                                                                                        |    |    |    |     |    |
| Auto switch (Option)          | Reed switch D-A9□<br>Solid state switch (2-wire, 3-wire) D-M9□<br>2-colour indication solid state switch (2-wire, 3-wire) D-F9□ |    |    |    |     |    |
| Stroke length tolerance       | +1<br>0 mm                                                                                                                      |    |    |    |     |    |

### Further functional options available

Please contact us.




With buffer mechanism



With end lock





### How to Order



Auto Switch Specifications  
Refer to switch section.

Dimensions: MXS6: Standard type

Basic style




| Model   | F  | N | G  | H  | NN | GA | HA | I  | J  | K    | M   | Z    | ZZ  |
|---------|----|---|----|----|----|----|----|----|----|------|-----|------|-----|
| MXS6-10 | 20 | 4 | 6  | 25 | 2  | 11 | 20 | 10 | 17 | 22.5 | 42  | 41.5 | 48  |
| MXS6-20 | 30 | 4 | 6  | 35 | 2  | 21 | 20 | 10 | 27 | 32.5 | 52  | 51.5 | 58  |
| MXS6-30 | 20 | 6 | 11 | 20 | 3  | 31 | 20 | 7  | 40 | 42.5 | 62  | 61.5 | 68  |
| MXS6-40 | 28 | 6 | 13 | 30 | 3  | 43 | 30 | 19 | 50 | 52.5 | 84  | 83.5 | 90  |
| MXS6-50 | 38 | 6 | 17 | 24 | 4  | 41 | 48 | 25 | 60 | 62.5 | 100 | 99.5 | 106 |

(mm)

# Dimensions: MXS6L: Symmetric Type

## Basic style



| Model    | F  | N | G  | H  | NN | GA | HA | I  | J  | K    | M   | Z    | ZZ  |
|----------|----|---|----|----|----|----|----|----|----|------|-----|------|-----|
| MXS6L-10 | 20 | 4 | 6  | 25 | 2  | 11 | 20 | 10 | 17 | 22.5 | 42  | 41.5 | 48  |
| MXS6L-20 | 30 | 4 | 6  | 35 | 2  | 21 | 20 | 10 | 27 | 32.5 | 52  | 51.5 | 58  |
| MXS6L-30 | 20 | 6 | 11 | 20 | 3  | 31 | 20 | 7  | 40 | 42.5 | 62  | 61.5 | 68  |
| MXS6L-40 | 28 | 6 | 13 | 30 | 3  | 43 | 30 | 19 | 50 | 52.5 | 84  | 83.5 | 90  |
| MXS6L-50 | 38 | 6 | 17 | 24 | 4  | 41 | 48 | 25 | 60 | 62.5 | 100 | 99.5 | 106 |





## Basic style



(mm)

# Dimensions: MXS8L: Symmetric Type

## Basic style



| Model    | F  | N | G  | H  | NN | GA | HA | I    | J    | K    | KA    | NA | M   | Z     | ZZ  |
|----------|----|---|----|----|----|----|----|------|------|------|-------|----|-----|-------|-----|
| MXS8L-10 | 25 | 4 | 9  | 28 | 2  | 17 | 20 | 13   | 19.5 | 23.5 | —     | 2  | 49  | 48.5  | 56  |
| MXS8L-20 | 25 | 4 | 12 | 30 | 2  | 12 | 30 | 8.5  | 29   | 33.5 | —     | 2  | 54  | 53.5  | 61  |
| MXS8L-30 | 40 | 4 | 13 | 20 | 3  | 33 | 20 | 9.5  | 39   | 43.5 | —     | 2  | 65  | 64.5  | 72  |
| MXS8L-40 | 50 | 4 | 15 | 28 | 3  | 43 | 28 | 10.5 | 56   | 53.5 | —     | 2  | 83  | 82.5  | 90  |
| MXS8L-50 | 38 | 6 | 20 | 23 | 4  | 43 | 46 | 24.5 | 60   | 63.5 | 82.5  | 4  | 101 | 100.5 | 108 |
| MXS8L-75 | 50 | 6 | 27 | 28 | 5  | 83 | 56 | 38.5 | 96   | 88.5 | 132.5 | 4  | 151 | 150.5 | 158 |


## Basic style



| Model     | F  | N | G  | H  | NN | GA  | HA | I  | J   | K     | KA    | NA | M   | Z   | ZZ  |
|-----------|----|---|----|----|----|-----|----|----|-----|-------|-------|----|-----|-----|-----|
| MXS12-10  | 35 | 4 | 15 | 40 | 2  | 15  | 40 | 10 | 40  | 26.5  | —     | 2  | 71  | 70  | 80  |
| MXS12-20  | 35 | 4 | 15 | 40 | 2  | 15  | 40 | 10 | 40  | 36.5  | —     | 2  | 71  | 70  | 80  |
| MXS12-30  | 35 | 4 | 15 | 40 | 2  | 15  | 40 | 10 | 40  | 46.5  | —     | 2  | 71  | 70  | 80  |
| MXS12-40  | 50 | 4 | 17 | 25 | 3  | 42  | 25 | 10 | 52  | 56.5  | —     | 2  | 83  | 82  | 92  |
| MXS12-50  | 35 | 6 | 15 | 36 | 3  | 51  | 36 | 22 | 60  | 66.5  | —     | 2  | 103 | 102 | 112 |
| MXS12-75  | 55 | 6 | 25 | 36 | 4  | 61  | 72 | 43 | 85  | 91.5  | 125.5 | 4  | 149 | 148 | 158 |
| MXS12-100 | 65 | 6 | 35 | 38 | 5  | 111 | 76 | 52 | 130 | 116.5 | 179.5 | 4  | 203 | 202 | 212 |

# Dimensions: MXS12L: Symmetric Type


## Basic style



| Model      | F  | N | G  | H  | NN | GA  | HA | I  | J   | K     | KA    | NA | M   | Z   | ZZ  |
|------------|----|---|----|----|----|-----|----|----|-----|-------|-------|----|-----|-----|-----|
| MXS12L-10  | 35 | 4 | 15 | 40 | 2  | 15  | 40 | 10 | 40  | 26.5  | —     | 2  | 71  | 70  | 80  |
| MXS12L-20  | 35 | 4 | 15 | 40 | 2  | 15  | 40 | 10 | 40  | 36.5  | —     | 2  | 71  | 70  | 80  |
| MXS12L-30  | 35 | 4 | 15 | 40 | 2  | 15  | 40 | 10 | 40  | 46.5  | —     | 2  | 71  | 70  | 80  |
| MXS12L-40  | 50 | 4 | 17 | 25 | 3  | 42  | 25 | 10 | 52  | 56.5  | —     | 2  | 83  | 82  | 92  |
| MXS12L-50  | 35 | 6 | 15 | 36 | 3  | 51  | 36 | 22 | 60  | 66.5  | —     | 2  | 103 | 102 | 112 |
| MXS12L-75  | 55 | 6 | 25 | 36 | 4  | 61  | 72 | 43 | 85  | 91.5  | 125.5 | 4  | 149 | 148 | 158 |
| MXS12L-100 | 65 | 6 | 35 | 38 | 5  | 111 | 76 | 52 | 130 | 116.5 | 179.5 | 4  | 203 | 202 | 212 |

Dimensions: MXS16: Standard type

Basic style







| Model     | F  | N | G  | H  | NN | GA  | HA | I  | J   | K   | KA  | NA | M   | Z   | ZZ  |
|-----------|----|---|----|----|----|-----|----|----|-----|-----|-----|----|-----|-----|-----|
| MXS16-10  | 35 | 4 | 16 | 40 | 2  | 16  | 40 | 10 | 40  | 29  | —   | 2  | 76  | 75  | 87  |
| MXS16-20  | 35 | 4 | 16 | 40 | 2  | 16  | 40 | 10 | 40  | 39  | —   | 2  | 76  | 75  | 87  |
| MXS16-30  | 35 | 4 | 16 | 40 | 2  | 16  | 40 | 10 | 40  | 49  | —   | 2  | 76  | 75  | 87  |
| MXS16-40  | 40 | 4 | 16 | 50 | 2  | 16  | 50 | 10 | 50  | 59  | —   | 2  | 86  | 85  | 97  |
| MXS16-50  | 30 | 6 | 21 | 30 | 3  | 51  | 30 | 15 | 60  | 69  | —   | 2  | 101 | 100 | 112 |
| MXS16-75  | 55 | 6 | 26 | 35 | 4  | 61  | 70 | 40 | 85  | 94  | 125 | 4  | 151 | 150 | 162 |
| MXS16-100 | 65 | 6 | 39 | 35 | 5  | 109 | 70 | 55 | 118 | 119 | 173 | 4  | 199 | 198 | 210 |
| MXS16-125 | 70 | 8 | 19 | 35 | 7  | 159 | 70 | 68 | 155 | 144 | 223 | 4  | 249 | 248 | 260 |

(mm)

# Dimensions: MXS16L: Symmetric Type

## Basic style







| Model      | F  | N | G  | H  | NN | GA  | HA | I  | J   | K   | KA  | NA | M   | Z   | ZZ  |
|------------|----|---|----|----|----|-----|----|----|-----|-----|-----|----|-----|-----|-----|
| MXS16L-10  | 35 | 4 | 16 | 40 | 2  | 16  | 40 | 10 | 40  | 29  | —   | 2  | 76  | 75  | 87  |
| MXS16L-20  | 35 | 4 | 16 | 40 | 2  | 16  | 40 | 10 | 40  | 39  | —   | 2  | 76  | 75  | 87  |
| MXS16L-30  | 35 | 4 | 16 | 40 | 2  | 16  | 40 | 10 | 40  | 49  | —   | 2  | 76  | 75  | 87  |
| MXS16L-40  | 40 | 4 | 16 | 50 | 2  | 16  | 50 | 10 | 50  | 59  | —   | 2  | 86  | 85  | 97  |
| MXS16L-50  | 30 | 6 | 21 | 30 | 3  | 51  | 30 | 15 | 60  | 69  | —   | 2  | 101 | 100 | 112 |
| MXS16L-75  | 55 | 6 | 26 | 35 | 4  | 61  | 70 | 40 | 85  | 94  | 125 | 4  | 151 | 150 | 162 |
| MXS16L-100 | 65 | 6 | 39 | 35 | 5  | 109 | 70 | 55 | 118 | 119 | 173 | 4  | 199 | 198 | 210 |
| MXS16L-125 | 70 | 8 | 19 | 35 | 7  | 159 | 70 | 68 | 155 | 144 | 223 | 4  | 249 | 248 | 260 |

## Basic style

Page 580

### Dimensions: MXS20L: Symmetric Type


## Basic style



| (mm)       |    |    |   |    |    |    |     |    |    |     |     |     |    |     |       |     |
|------------|----|----|---|----|----|----|-----|----|----|-----|-----|-----|----|-----|-------|-----|
| Model      | F  | FF | N | G  | H  | NN | GA  | HA | I  | J   | K   | KA  | NA | M   | Z     | ZZ  |
| MXS20L-10  | 50 | 40 | 4 | 15 | 45 | 2  | 25  | 35 | 10 | 44  | 31  | —   | 2  | 83  | 81.5  | 97  |
| MXS20L-20  | 50 | 40 | 4 | 15 | 45 | 2  | 25  | 35 | 10 | 44  | 41  | —   | 2  | 83  | 81.5  | 97  |
| MXS20L-30  | 50 | 40 | 4 | 15 | 45 | 2  | 25  | 35 | 10 | 44  | 51  | —   | 2  | 83  | 81.5  | 97  |
| MXS20L-40  | 60 | 50 | 4 | 15 | 55 | 2  | 35  | 35 | 10 | 54  | 61  | —   | 2  | 93  | 91.5  | 107 |
| MXS20L-50  | 35 | 35 | 6 | 15 | 35 | 3  | 50  | 35 | 10 | 69  | 71  | —   | 2  | 108 | 106.5 | 122 |
| MXS20L-75  | 60 | 60 | 6 | 19 | 35 | 4  | 54  | 70 | 10 | 108 | 96  | —   | 2  | 147 | 145.5 | 161 |
| MXS20L-100 | 70 | 70 | 6 | 37 | 35 | 5  | 107 | 70 | 58 | 113 | 121 | 169 | 4  | 200 | 198.5 | 214 |
| MXS20L-125 | 70 | 70 | 8 | 41 | 38 | 6  | 155 | 76 | 70 | 155 | 146 | 223 | 4  | 254 | 252.5 | 268 |
| MXS20L-150 | 80 | 80 | 8 | 19 | 44 | 7  | 195 | 88 | 87 | 190 | 171 | 275 | 4  | 306 | 304.5 | 320 |





Dimensions: MXS25: Standard type

Basic style



Cross section AA

Cross section BB




(mm)

| Model     | F  | FF | N | G  | H  | NN | GA  | HA | I  | J   | K   | KA  | NA | M   | Z     | ZZ  |
|-----------|----|----|---|----|----|----|-----|----|----|-----|-----|-----|----|-----|-------|-----|
| MXS25-10  | 50 | 40 | 4 | 22 | 45 | 2  | 22  | 45 | 12 | 47  | 35  | —   | 2  | 92  | 90.5  | 108 |
| MXS25-20  | 50 | 40 | 4 | 22 | 45 | 2  | 22  | 45 | 12 | 47  | 45  | —   | 2  | 92  | 90.5  | 108 |
| MXS25-30  | 50 | 40 | 4 | 22 | 45 | 2  | 22  | 45 | 12 | 47  | 55  | —   | 2  | 92  | 90.5  | 108 |
| MXS25-40  | 60 | 50 | 4 | 22 | 55 | 2  | 22  | 55 | 12 | 57  | 65  | —   | 2  | 102 | 100.5 | 118 |
| MXS25-50  | 35 | 35 | 6 | 20 | 35 | 3  | 55  | 35 | 12 | 70  | 75  | —   | 2  | 115 | 113.5 | 131 |
| MXS25-75  | 60 | 60 | 6 | 26 | 35 | 4  | 61  | 70 | 33 | 90  | 100 | —   | 2  | 156 | 154.5 | 172 |
| MXS25-100 | 70 | 70 | 6 | 32 | 35 | 5  | 102 | 70 | 50 | 114 | 125 | 162 | 4  | 197 | 195.5 | 213 |
| MXS25-125 | 75 | 75 | 8 | 40 | 38 | 6  | 154 | 76 | 67 | 155 | 150 | 218 | 4  | 255 | 253.5 | 271 |
| MXS25-150 | 80 | 80 | 8 | 30 | 40 | 7  | 190 | 80 | 82 | 180 | 175 | 258 | 4  | 295 | 293.5 | 311 |


# Dimensions: MXS25L: Symmetric Type

## Basic style




| Model      | F  | FF | N | G  | H  | NN | GA  | HA | I  | J   | K   | KA  | NA | M   | Z     | ZZ  |
|------------|----|----|---|----|----|----|-----|----|----|-----|-----|-----|----|-----|-------|-----|
| MXS25L-10  | 50 | 40 | 4 | 22 | 45 | 2  | 22  | 45 | 12 | 47  | 35  | —   | 2  | 92  | 90.5  | 108 |
| MXS25L-20  | 50 | 40 | 4 | 22 | 45 | 2  | 22  | 45 | 12 | 47  | 45  | —   | 2  | 92  | 90.5  | 108 |
| MXS25L-30  | 50 | 40 | 4 | 22 | 45 | 2  | 22  | 45 | 12 | 47  | 55  | —   | 2  | 92  | 90.5  | 108 |
| MXS25L-40  | 60 | 50 | 4 | 22 | 55 | 2  | 22  | 55 | 12 | 57  | 65  | —   | 2  | 102 | 100.5 | 118 |
| MXS25L-50  | 35 | 35 | 6 | 20 | 35 | 3  | 55  | 35 | 12 | 70  | 75  | —   | 2  | 115 | 113.5 | 131 |
| MXS25L-75  | 60 | 60 | 6 | 26 | 35 | 4  | 61  | 70 | 33 | 90  | 100 | —   | 2  | 156 | 154.5 | 172 |
| MXS25L-100 | 70 | 70 | 6 | 32 | 35 | 5  | 102 | 70 | 50 | 114 | 125 | 162 | 4  | 197 | 195.5 | 213 |
| MXS25L-125 | 75 | 75 | 8 | 40 | 38 | 6  | 154 | 76 | 67 | 155 | 150 | 218 | 4  | 255 | 253.5 | 271 |
| MXS25L-150 | 80 | 80 | 8 | 30 | 40 | 7  | 190 | 80 | 82 | 180 | 175 | 258 | 4  | 295 | 293.5 | 311 |

With shock absorber (ø6) MXS8-□□BS, BT, B




\* Dimensions not indicated are the same as the basic style.



| Model   | Stroke adjustable range |            | A dimension<br>(Retracted side mounting) |
|---------|-------------------------|------------|------------------------------------------|
|         | Extending               | Retracting |                                          |
| MXS8-10 | Max.20                  | 5          | 22                                       |
| MXS8-20 |                         | 15         | 27                                       |
| MXS8-30 |                         | 15         | 26                                       |
| MXS8-40 |                         | 5          | 18                                       |
| MXS8-50 |                         | 20         | 29                                       |
| MXS8-75 |                         | 20         | 29                                       |


With shock absorber(ø12) MXS12-□□BS, BT, B



\* Other dimensions not indicated are the same as the basic style.

| Model     | Stroke adjustment range |            | A dimension<br>(Retracted side mounting) |
|-----------|-------------------------|------------|------------------------------------------|
|           | Extending               | Retracting |                                          |
| MXS12-10  | Max. 20                 | 2          | 7                                        |
| MXS12-20  |                         | 5          | 17                                       |
| MXS12-30  |                         | 15         | 27                                       |
| MXS12-40  |                         | 15         | 25                                       |
| MXS12-50  |                         | 5          | 15                                       |
| MXS12-75  |                         | 15         | 28                                       |
| MXS12-100 |                         | 15         | 28                                       |


With shock absorber(ø16) MXS16-□□BS, BT, B



\* Other dimensions not indicated are the same as the basic style.

| Model     | Stroke adjustment range |            | A dimension<br>(Retracted side mounting) |
|-----------|-------------------------|------------|------------------------------------------|
|           | Extending               | Retracting |                                          |
| MXS16-10  | Max. 25                 | 5          | 11                                       |
| MXS16-20  |                         | 10         | 21                                       |
| MXS16-30  |                         | 20         | 31                                       |
| MXS16-40  |                         | 20         | 31                                       |
| MXS16-50  |                         | 15         | 26                                       |
| MXS16-75  |                         | 20         | 32                                       |
| MXS16-100 |                         | 20         | 32                                       |
| MXS16-125 |                         | 20         | 32                                       |

### With shock absorber(ø20) MXS20-□□BS, BT, B




\* Dimensions not indicated are the same as the basic style.

(mm)

| Model     | Stroke adjustable range |            | A dimension<br>(Retracted side mounting) |
|-----------|-------------------------|------------|------------------------------------------|
|           | Extending               | Retracting |                                          |
| MXS20-10  | Max. 40                 | 5          | 28                                       |
| MXS20-20  |                         | 15         | 38                                       |
| MXS20-30  |                         | 25         | 48                                       |
| MXS20-40  |                         | 35         | 48                                       |
| MXS20-50  |                         | 30         | 43                                       |
| MXS20-75  |                         | 15         | 29                                       |
| MXS20-100 |                         | 35         | 49                                       |
| MXS20-125 |                         | 35         | 49                                       |
| MXS20-150 |                         | 35         | 49                                       |

### With shock absorber(ø25) MXS25-□□BS, BT, B



\* Dimensions not indicated are the same as the basic style.

(mm)

| Model     | Stroke adjustable range |            | A dimension<br>(Retracted side mounting) |
|-----------|-------------------------|------------|------------------------------------------|
|           | Extending               | Retracting |                                          |
| MXS25-10  | Max. 35                 | 5          | 26                                       |
| MXS25-20  |                         | 15         | 36                                       |
| MXS25-30  |                         | 25         | 46                                       |
| MXS25-40  |                         | 35         | 46                                       |
| MXS25-50  |                         | 30         | 43                                       |
| MXS25-75  |                         | 15         | 27                                       |
| MXS25-100 |                         | 35         | 48                                       |
| MXS25-125 |                         | 35         | 46                                       |
| MXS25-150 |                         | 35         | 46                                       |

### Option Specifications

#### How to Order Stroke Adjuster (Accessory)

MXS - AS 12 L - X11

##### Stroke adjuster

|    |                 |                |
|----|-----------------|----------------|
| AS | Stroke adjuster | Extension end  |
| AT | Stroke adjuster | Retraction end |
| BS | Shock absorber  | Extension end  |
| BT | Shock absorber  | Retraction end |

##### Applicable bore size (mm)

|    |     |
|----|-----|
| 6  | ø6  |
| 8  | ø8  |
| 12 | ø12 |
| 16 | ø16 |
| 20 | ø20 |
| 25 | ø25 |

##### Symmetric type

|     |                |
|-----|----------------|
| Nil | Standard type  |
| L   | Symmetric type |

##### Adjustable range (Stroke adjuster only)

|      | 5 mm  | Standard |
|------|-------|----------|
| -X11 | 15 mm | Option   |
| -X12 | 25 mm |          |

\* -X12 (adjustable range: 25 mm) is not available in Series MXS6.

\* -X11 and -X12 are not available for shock absorber type.

\* W/ shock absorber is not available in Series MXS6.

#### How to Order Adjusting Bolt

MXS - A 12 27 - X11

##### Applicable bore size (mm)

|       |     |
|-------|-----|
| MXS6  | ø6  |
| MXS8  | ø8  |
| MXS12 | ø12 |
| MXS16 | ø16 |
| MXS20 | ø20 |
| MXS25 | ø25 |


##### Adjustment range

|     |       |
|-----|-------|
| Nil | 5 mm  |
| X11 | 15 mm |
| X12 | 25 mm |

\* -X12 (adjustable range: 25 mm) is not available in Series MXS6.

\* Symmetric type is also the same.

#### Dimensions of Adjusting Bolt



| Applicable size | Model         | Stroke adjustment range (mm) | A    | B   | C  | D   | M          |
|-----------------|---------------|------------------------------|------|-----|----|-----|------------|
| MXS6(L)         | MXS-A627      | 5                            | 16.5 | 2.5 | 7  | 3   | M5         |
|                 | MXS-A627-X11  | 15                           | 26.5 |     |    |     |            |
| MXS8(L)         | MXS-A827      | 5                            | 16.5 | 3   | 8  | 3.5 | M6         |
|                 | MXS-A827-X11  | 15                           | 26.5 |     |    |     |            |
|                 | MXS-A827-X12  | 25                           | 36.5 |     |    |     |            |
| MXS12(L)        | MXS-A1227     | 5                            | 20   | 4   | 12 | 4   | M8 x 1     |
|                 | MXS-A1227-X11 | 15                           | 30   |     |    |     |            |
|                 | MXS-A1227-X12 | 25                           | 40   |     |    |     |            |
| MXS16(L)        | MXS-A1627     | 5                            | 24.5 | 5   | 14 | 4   | M10 x 1    |
|                 | MXS-A1627-X11 | 15                           | 34.5 |     |    |     |            |
|                 | MXS-A1627-X12 | 25                           | 44.5 |     |    |     |            |
| MXS20(L)        | MXS-A2027     | 5                            | 27.5 | 6   | 17 | 5   | M12 x 1.25 |
|                 | MXS-A2027-X11 | 15                           | 37.5 |     |    |     |            |
|                 | MXS-A2027-X12 | 25                           | 47.5 |     |    |     |            |
| MXS25(L)        | MXS-A2527     | 5                            | 32.5 | 6   | 19 | 6   | M14 x 1.5  |
|                 | MXS-A2527-X11 | 15                           | 42.5 |     |    |     |            |
|                 | MXS-A2527-X12 | 25                           | 52.5 |     |    |     |            |