

μCom-10Gb +

*Harsh Environment 10Gb
Ethernet Micro Connectors*



μCom-Series is a new range of connectors designed to address the latest trends of the industry : **miniaturization** and **high speed**, with the highest resistance for use in the **harshest environments**.

μCom-10Gb + is the first product of this new range.

MAIN FEATURES

- 10Gb+ exceeds 10Gb/s Ethernet following IEEE 802.3an-2006 : **10GBase-T**
- Cat.6A connector according to TIA568C.2 and ISO/IEC11801 standard
- Environmental testing based on **MIL-DTL-38999 series III** military specifications
- Miniature : **15 mm(.59") max** external diameter

FEATURES AND BENEFITS


- 4 pairs totally insulated throughout the connector
➔ minimum cross-talk between the four pairs
- Patent pending special interfacial shapes
➔ minimum perturbation at the interface of each pair
- Thread coupling mechanism
➔ 2000 mating cycles & high vibration resistance
- Machined Brass shells and RoHS compliant plating
➔ shell to shell continuity and 500h salt spray resistance
- Machined & gold plated Solder and Crimp contacts
➔ design & performance according to the innercontact of M39029/77-429#16 M39029/76-425#16 38999 contact
- Solder contact : max AWG24
- Crimp contact : AWG 24 to 26
- IP68 sealing mated and unmated for receptacles
- 1500 Vrms Dielectric Withstanding voltage
- Temperature range : - 55°C / + 125°C

MARKETS & APPLICATIONS

- **DEFENSE** : C4ISR, Battlefield Communications, Shipboard, Ground Vehicles Vetronics.
- **AERONAUTICAL** : In Flight Entertainment, Avionics, Communication Systems.
- **RAIL MASS TRANSIT** : Passenger Information Systems, Communication Systems.



TRANSMISSION DATA




Insertion loss



← Amphenol performance

← IEEE 802.3an Standard requirement


Next 1-2



← IEEE 802.3an Standard requirement

← Amphenol performance

Return loss



← IEEE 802.3an Standard requirement

← Amphenol performance




FEMALE RECEPTACLES



Female receptacle for printed circuit board

Part number: **UCOM-10G+ R P x**




x: see the 'How to order' below to complete your part number



Panel mount female receptacle with metallic band backshell

Part number: UCOM-10G+ R x x

x: see the 'How to order' below to complete your part number



HOW TO ORDER Female receptacles

UCOM - 10G+ **P**

Shell

R: receptacle (push pull or thread)

Contacts termination

P: PCB

S: solder

C: crimp

Shell plating

B: black nickel

G: olive drab cadmium

U: unplated brass

NOTA:

- UCOM for order designation
- μ Com for marking on connectors


MALE PLUGS



Plug with cable gland backshell

Part number: UCOM-10G+ PT x G x



x: see the 'How to order' below to complete your part number



Plug with metallic band backshell

Part number: UCOM-10G+ PT x B

x: see the 'How to order' below to complete your part number



HOW TO ORDER Male plugs

UCOM - 10G+ P T C B G A

Shell

P: plug

Mating (for plugs only)

T: thread

Contacts termination

C: crimp

S: solder

Shell plating

B: black nickel

G: olive drab cadmium

U: unplated brass

Backshell type

G: gland

B: band

Cable diameter (for gland backshell only)

A: for cable diam 7.5mm

B: to be defined

NOTA:

- UCOM for order designation
- μCom for marking on connectors



FEMALE IN-LINE RECEPTACLES



Female in-line receptacle with cable gland backshell

Part number: UCOM-10G+ L x x G x



x: see the 'How to order' below to complete your part number



Female in-line receptacle with metallic band backshell

Part number: UCOM-10G+ L x x B

x: see the 'How to order' below to complete your part number



HOW TO ORDER Female in-line receptacles

UCOM - 10G+ L S B G A

Shell

L: in line receptacle

Contacts termination

C: crimp

S: solder

Shell plating

B: black nickel

G: olive drab cadmium

U: unplated brass

Backshell type

G: gland

B: band

Cable diameter (for gland backshell only)

A: for cable diam 7.5mm

B: to be defined

NOTA:

- UCOM for order designation
- μCom for marking on connectors


CORDSETS

μCom plug - μCom plug cordset

Part number:

UCOM-10G+ **C** x x x xxx

x: see the 'How to order' on the next page to complete your part number




μCom plug - RJ45 plug cordset

Part number:

UCOM-10G+ **D** x x x xxx

x: see the 'How to order' on the next page to complete your part number




μCom panel mount receptacle - RJ45 plug

Part number:

UCOM-10G+ **E** x x xxx

x: see the 'How to order' on the next page to complete your part number




μCom plug - μCom inline receptacle

Part number:

UCOM-10G+ **F** x x x xxx

x: see the 'How to order' below
to complete your part number



Type of cable used: **CAT 7 HFFR** - According to EN 50288-4-2



- Stranded bare copper wire (26 AWG)
- 4 screened twisted pairs: 2 wires twisted to a pair, Alulaminated foil overlapped
- Shield braiding of tinned copper wires, about 80% coverage
- Strain member of Kevlar
- Jacket in black Polyurethane (PUR), glossy finish, acc to DIN VDE 0282
- External diameter 7.0 +/-0.3 mm
- UV & Hydrolysis resistant, Halogen free, RoHS compliant
- Max Pull force: 800 N, Weight : about 54 kg/km
- Temperature : - 40°C / + 85°C

HOW TO ORDER Cordsets

	UCOM - 10G+	C	T	C	B	015
Shell						
C: μCom plug - μCom plug cordset						
D: μCom plug - RJ45 plug cordset						
E: μCom panel mount receptacle - RJ45 plug cordset						
F: μCom plug - μCom inline receptacle cordset						
Open versions:						
G: μCom plug - no connector at the end						
H: μCom panel mount receptacle - no connector at the end						
J: μCom inline receptacle - no connector at the end						
Mating (for plugs only)						
T: thread						
Contacts termination						
C: crimp						
S: solder						
Shell plating						
B: black nickel						
G: olive drab cadmium						
U: unplated brass						
Total length - For other lengths, please consult us						
005: 50 cm [19.68]						
010: 1.0 m [39.37]						
015: 1.5 m [59.05]						
020: 2.0 m [78.74]						
050: 5.0 m [196.85]						
100: 10.0 m [393.70]						

NOTA:

- UCOM** for order designation
- μCom** for marking on connectors

ACCESSORIES

CAPS for receptacles

IP68 metallic cap


Part number: **31057** **X**

X to be replaced by

B for Black nickel plating

G for Olive drab cadmium plating

U for Unplated brass



IP68 neoprene cap - Part number: **31091**

Nota: plan a type M3 hole on the panel



CAPS for plugs

Cap in neoprene

Part number: **31092**



CAPS for in line receptacles


Cap in neoprene

Part number: **31093**



Dummy female receptacle

Part number: **31131** **X**



X to be replaced by

B for Black nickel plating

G for Olive drab cadmium plating

U for Unplated brass

TOOLS



Nut clamping tool for receptacle

Part number: **31055**



Insertion tool for crimp contacts

Part number: **31056**



Contact positioner

for M22520/2-01 crimping tool

Part number: **31095**

Other tools:

Brazing tool for receptacle

Part number: **31132**

Brazing tool for plug

Part number: **31133**