


RUGGED RELIABLE MICRO SOCKETS

(1.00 mm) .0394" PITCH • CLM/MLE SERIES



CLM

Mates:

FTM, FTMH, MW

MLE

Mates:

FTM, FTMH, MW

SPECIFICATIONS

Insulator Material: Black LCP
Contact Material:

CLM: Phosphor Bronze

MLE: BeCu

Plating:

CLM: Au or Sn over

50 μ " (1.27 μ m) Ni

MLE: Au over 10 μ " (0.25 μ m) Ni

Current Rating (CLM/FTM):

2.8 A per pin

(2 pins powered)

Current Rating (MLE/FTM):

2.9 A per pin (2 pins powered)

Operating Temp Range:

-55 °C to +125 °C

Max Cycles:

CLM: 100 with 10 μ " (0.25 μ m) Au

Voltage Rating:

MLE: 310 VAC

Insertion Depth:

CLM:

Top Entry = (1.40 mm) .055" min.,

Bottom Entry =

(2.41 mm) .095" min.

(Add board thickness for

correct post OAL)

MLE:

(1.63 mm) .064" to

(3.18 mm) .125" with

(0.38 mm) .015" wiper,



pass-through, or (2.44 mm) .096"

minimum for bottom entry


Normal Force:

CLM: 40 grams (0.39 N) average

**TIGER
CLAW
CONTACT**



PIN/ROW	A
04-15	(3.56) .140
16-50	(7.11) .280



-PA

-P

MLE

- 1

**NO. PINS
PER ROW**

- 01

**PLATING
OPTION**

- DV

OPTIONS

02 thru 50

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (02-25)



(0.15 mm) .006" max (26-50)*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

**TIGER
BEAM
CONTACT**



-G

= 10 μ "

(0.25 μ m)

Gold

-A

= Alignment Pin

(3 positions minimum)

Metal or plastic

at Samtec discretion

-K

= (4.00 mm) .1575" DIA

Polyimide film

Pick & Place Pad

(5 positions minimum)

-P

= Metal Pick & Place Pad

(5 positions minimum)

-TR

= Tape & Reel

-FR

= Full Reel Tape & Reel

(must order maximum

quantity per reel;

contact Samtec for

quantity breaks)

-P

-A

ALSO AVAILABLE

MOQ Required

Alignment pin

Other Gold plating options



Note:

Some lengths, styles and options are non-standard, non-returnable.

samtec.com?CLM or samtec.com?MLE

F-221 (Rev 29MAR21)

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.