




RECOMMENDED HOLE PATTERN
SCALE 10:1









VIEW F-F




SECTION G-G
ROTATED 90°CW

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com		
ltr	ecn no	dr	date	linear	angles				
AF				.XX±.01/.X±.3		projection	 INCH/MM		
				.XXX±.005/.XX±.13					
				.XXX±.0020/.XXX±.051			title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
				0°±2°					
				dr J. SHREINER 1/16/90		scale	product family QUICKIE		code -
				enr M. SMYK 1/16/90		5:1			
				chr M. SMYK 1/16/90			size 65823		sheet 2 of 21
				appd M. SMYK 1/16/90					
21	sheet index	revision sheet							





NOTES:

- RECOMMENDED MOUNTING SCREW SIZE: #2-56 FILLISTER HD MACH SCREW, 3/8" LG FOR 1/16" & 3/32" BOARD, 7/16" LG FOR 1/8" BOARD.
- MOLDING MAT'L: 30% GLASS FILLED POLYESTER, FLAME RETARDANT PER UL-94V-0, COLOR: BLUE.
- PIN MAT'L: 3/4 HARD PHOS BRONZE ALLOY UNS C-51000.
- 1° MAX DRAFT PERMISSIBLE ON ALL SURFACES UNLESS OTHERWISE SPECIFIED.
- PLATING ON LEAD-IN PORTION OF PIN IS MANUFACTURING OPTION.
- B** BASIC DIM SHALL BE LOCATED SYMMETRICAL TO DATUM -Y-.
- LOW PROFILE LATCHES TO BE USED WITH FEMALE CONNECTOR WITHOUT STRAIN RELIEF. STANDARD LATCHES TO BE USED WITH FEMALE CONNECTOR WITH STRAIN RELIEF.
- .040±.003/.02±.08 DIA HOLE TYP FOR SQ PINS, .035±.003/.89±.08 DIA HOLE TYP FOR RND PINS.
- A. RETENTION FEATURE AVAILABLE ON CONNECTORS WITH .105/2.67, .120/3.05, OR .150/3.81 TAIL LENGTH. RETENTION P/N INCLUDES THE LETTER "R" AFTER THE EXISTING P/N.
EXAMPLE: 65823-XXX FOR EXISTING P/N
65823-XXXR FOR RETENTION P/N
RETENTION FEATURE LOCATION IS MANUFACTURERS OPTION.
B. ROUND PINS HAVE 15 LBS/6.8 KGS MAX INSERTION AND .25 LB/.1 KG MIN RETENTION FORCE WHEN USED IN .035±.003/.89±.08 DIA HOLES AND .062/1.57 THICK PC BOARD.
C. SQUARE PINS HAVE A 15 LBS/6.8 KG MAX INSERTION AND .5 LB/.2 KG MIN RETENTION FORCE WHEN USED IN .040±.003/1.02±.08 DIA HOLES AND .062/1.57 THICK PC BOARD.
- 65496-***LF IS JUST A LEAD FREE PRODUCT.
- THE HOUSING OF XXXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.
- PLATING OPTION: MAYBE EITHER GOLD OR GXT
PLATING AT MANUFACTURER'S OPTION.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com		
ltr	ecn no	dr	date						
AF				linear	.XX±.01/.X±.3 .XXX±.005/.XX±.13 .XXX±.0020/.XXX±.051	projection	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
				angles	0°±2°				
				dr	J. SHREINER 1/16/90	INCH/MM	product family QUICKIE size dwg no		
				enrg	M. SMYK 1/16/90				
				chr	M. SMYK 1/16/90	scale	A 65823		
				appd	M. SMYK 1/16/90	5:1			
	sheet	revision							
21	index	sheet							



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-001(LF)	2x5	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" / .76 Au OVER 50u" / 1.27uNi	A
-002(LF)			SQ				.105/2.67		150u" / 3.81u Sn	
-003(LF)			RND				.150/3.81		30u" / .76 Au OVER 50u" / 1.27uNi	
-004(LF)			SQ				.150/3.81		150u" / 3.81u Sn	
-005(LF)			SQ				.675/17.15		30u" / .76 Au OVER 50u" / 1.27uNi	
-006(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u" / 3.81u Sn	A
-007(LF)	2x7		RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u" / .76 Au OVER 50u" / 1.27uNi	C
-008(LF)			SQ				.105/2.67		150u" / 3.81u Sn	
-009(LF)			RND				.150/3.81		30u" / .76 Au OVER 50u" / 1.27uNi	
-010(LF)			SQ				.150/3.81		150u" / 3.81u Sn	
-011(LF)			SQ				.675/17.15		30u" / .76 Au OVER 50u" / 1.27uNi	
-012(LF)	2x7		SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u" / 3.81u Sn	C
-013(LF)	2x8		RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u" / .76 Au OVER 50u" / 1.27uNi	D
-014(LF)			SQ				.105/2.67		150u" / 3.81u Sn	
-015(LF)			RND				.150/3.81		30u" / .76 Au OVER 50u" / 1.27uNi	
-016(LF)			SQ				.150/3.81		150u" / 3.81u Sn	
-017(LF)			SQ				.675/17.15		30u" / .76 Au OVER 50u" / 1.27uNi	
-018(LF)	2x8		SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u" / 3.81u Sn	
-019(LF)	2x10		RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u" / .76 Au OVER 50u" / 1.27uNi	
-020(LF)			SQ				.105/2.67		150u" / 3.81u Sn	
-021(LF)			RND				.150/3.81		30u" / .76 Au OVER 50u" / 1.27uNi	
-022(LF)			SQ				.150/3.81		150u" / 3.81u Sn	
-023(LF)			SQ				.675/17.15		30u" / .76 Au OVER 50u" / 1.27uNi	
-024(LF)	2x10		SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u" / 3.81u Sn	
-025(LF)	2x13		RND	2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1	30u" / .76 Au OVER 50u" / 1.27uNi	
-026(LF)			SQ				.105/2.67		150u" / 3.81u Sn	
-027(LF)			RND				.150/3.81		30u" / .76 Au OVER 50u" / 1.27uNi	
-028(LF)			SQ				.150/3.81		150u" / 3.81u Sn	
-029(LF)			SQ				.675/17.15		30u" / .76 Au OVER 50u" / 1.27uNi	
-030(LF)	2x13		SQ	2.060/52.32	1.200/30.48	1.520/38.61	.675/17.15	1.66/42.1	150u" / 3.81u Sn	
-031(LF)	2x17		RND	2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3	30u" / .76 Au OVER 50u" / 1.27uNi	
-032(LF)			SQ				.105/2.67		150u" / 3.81u Sn	
-033(LF)			RND				.150/3.81		30u" / .76 Au OVER 50u" / 1.27uNi	
-034(LF)			SQ				.150/3.81		150u" / 3.81u Sn	
-035(LF)			SQ				.675/17.15		30u" / .76 Au OVER 50u" / 1.27uNi	
65823-036(LF)	2x17	ND	SQ	2.460/62.48	1.600/40.64	1.920/48.77	.675/17.15	2.06/52.3	150u" / 3.81u Sn	D

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com				
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE				
AF					.XXX±.005/.XX±.13								
					.XXXX±.0020/.XXX±.051								
				angles	0°±2°				product family QUICKIE size dwg no A 65823				
				dr	J. SHREINER	1/16/90							
				enrg	M. SMYK	1/16/90							
				chr	M. SMYK	1/16/90							
				appd	M. SMYK	1/16/90							
sheet index		revision sheet						scale 5:1		sheet 4 of 21			



1 | 2

3 |

4

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-037(LF)	2x20	ND	RND	2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9	30u"/.76u Au OVER 50u"/1.27u Ni	D
↑ -038(LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u"/3.81u Sn	↑
↑ -039(LF)	↑	↑	RND	↑	↑	↑	.150/3.81	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -040(LF)	↑	↑	SQ	↑	↑	↑	.150/3.81	↑	150u"/3.81u Sn	↑
↑ -041(LF)	↑	↑	SQ	↑	↑	↑	.675/17.15	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -042(LF)	2x20	↑	SQ	2.760/70.10	1.900/48.26	2.220/56.39	.675/17.15	2.36/59.9	150u"/3.81u Sn	↑
↑ -043(LF)	2x25	↑	RND	3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -044(LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u"/3.81u Sn	↑
↑ -045(LF)	↑	↑	RND	↑	↑	↑	.150/3.81	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -046(LF)	↑	↑	SQ	↑	↑	↑	.150/3.81	↑	150u"/3.81u Sn	↑
↑ -047(LF)	↑	↑	SQ	↑	↑	↑	.675/17.15	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -048(LF)	2x25	ND	SQ	3.260/82.80	2.400/60.96	2.720/69.09	.675/17.15	2.86/72.6	150u"/3.81u Sn	D
↑ -049(LF)	2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u Au OVER 50u"/1.27u Ni	A
↑ -050(LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u"/3.81u Sn	↑
↑ -051(LF)	↑	↑	RND	↑	↑	↑	.150/3.81	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -052(LF)	↑	↑	SQ	↑	↑	↑	.150/3.81	↑	150u"/3.81u Sn	↑
↑ -053(LF)	↑	↑	SQ	↑	↑	↑	.675/17.15	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -054(LF)	2x5	↑	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/3.81u Sn	A
↑ -055(LF)	2x7	↑	RND	1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9	30u"/.76u Au OVER 50u"/1.27u Ni	C
↑ -056(LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u"/3.81u Sn	↑
↑ -057(LF)	↑	↑	RND	↑	↑	↑	.150/3.81	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -058(LF)	↑	↑	SQ	↑	↑	↑	.150/3.81	↑	150u"/3.81u Sn	↑
↑ -059(LF)	↑	↑	SQ	↑	↑	↑	.675/17.15	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -060(LF)	2x7	↑	SQ	1.460/37.08	.600/15.24	.920/23.37	.675/17.15	1.06/26.9	150u"/3.81u Sn	C
↑ -061(LF)	2x8	↑	RND	1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4	30u"/.76u Au OVER 50u"/1.27u Ni	D
↑ -062(LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u"/3.81u Sn	↑
↑ -063(LF)	↑	↑	RND	↑	↑	↑	.150/3.81	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -064(LF)	↑	↑	SQ	↑	↑	↑	.150/3.81	↑	150u"/3.81u Sn	↑
↑ -065(LF)	↑	↑	SQ	↑	↑	↑	.675/17.15	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -066(LF)	2x8	↑	SQ	1.560/39.62	.700/17.78	1.020/25.91	.675/17.15	1.16/29.4	150u"/3.81u Sn	↑
↑ -067(LF)	2x10	↑	RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -068(LF)	↑	↑	SQ	↑	↑	↑	.105/2.67	↑	150u"/3.81u Sn	↑
↑ -069(LF)	↑	↑	RND	↑	↑	↑	.150/3.81	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
↑ -070(LF)	↑	↑	SQ	↑	↑	↑	.150/3.81	↑	150u"/3.81u Sn	↑
↑ -071(LF)	↑	↑	SQ	↑	↑	↑	.675/17.15	↑	30u"/.76u Au OVER 50u"/1.27u Ni	↑
65823-072(LF)	2x10	STD	SQ	1.760/44.70	.900/22.86	1.220/30.99	.675/17.15	1.36/34.5	150u"/3.81u Sn	D

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	
AF					.XXX±.005/.XX±.13					
					.XXXX±.0020/.XXX±.051					
				angles	0°±2°				product family QUICKIE	
				dr	J. SHREINER	1/16/90	code —			
				enr	M. SMYK	1/16/90				
				appd	M. SMYK	1/16/90				
PDM: Rev: AF				STATUS			scale 5:1		Released 65823 Printed: Apr 12, 2011	
							A		sheet 5 of 21	



A

B

	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-073 <LF>	2x13	STD	RND	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	. 105/2. 67	1. 66/42. 1	30u" / . 76u Au OVER 50u" / 1. 27u Ni	D
-074 <LF>			SQ				. 105/2. 67		150u" / 3. 81u' 1/27u Ni	
-075 <LF>			RND				. 150/3. 81		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-076 <LF>			SQ				. 150/3. 81		150u" / 3. 81u' 1/27u Ni	
-077 <LF>			SQ				. 675/17. 15		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-078 <LF>	2x13		SQ	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	. 675/17. 15	1. 66/42. 1	150u" / 3. 81u' 1/27u Ni	
-079 <LF>	2x17		RND	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	. 105/2. 67	2. 06/52. 3	30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-080 <LF>			SQ				. 105/2. 67		150u" / 3. 81u' 1/27u Ni	
-081 <LF>			RND				. 150/3. 81		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-082 <LF>			SQ				. 150/3. 81		150u" / 3. 81u' 1/27u Ni	
-083 <LF>			SQ				. 675/17. 15		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-084 <LF>	2x17		SQ	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	. 675/17. 15	2. 06/52. 3	150u" / 3. 81u' 1/27u Ni	
-085 <LF>	2x20		RND	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	. 105/2. 67	2. 36/59. 9	30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-086 <LF>			SQ				. 105/2. 67		150u" / 3. 81u' 1/27u Ni	
-087 <LF>			RND				. 150/3. 81		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-088 <LF>			SQ				. 150/3. 81		150u" / 3. 81u' 1/27u Ni	
-089 <LF>			SQ				. 675/17. 15		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-090 <LF>	2x20		SQ	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	. 675/17. 15	2. 36/59. 9	150u" / 3. 81u' 1/27u Ni	
-091 <LF>	2x25		RND	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	. 105/2. 67	2. 86/72. 6	30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-092 <LF>			SQ				. 105/2. 67		150u" / 3. 81u' 1/27u Ni	
-093 <LF>			RND				. 150/3. 81		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-094 <LF>			SQ				. 150/3. 81		150u" / 3. 81u' 1/27u Ni	
-095 <LF>			SQ				. 675/17. 15		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-096 <LF>	2x25	STD	SQ	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	. 675/17. 15	2. 86/72. 6	150u" / 3. 81u' 1/27u Ni	
-097 <LF>	2x30	ND	RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-098 <LF>			SQ				. 105/2. 67		150u" / 3. 81u' 1/27u Ni	
-099 <LF>			RND				. 150/3. 81		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-100 <LF>			SQ				. 150/3. 81		150u" / 3. 81u' 1/27u Ni	
-101 <LF>			SQ				. 675/17. 15		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-102 <LF>		ND	SQ				. 675/17. 15		150u" / 3. 81u' 1/27u Ni	
-103 <LF>		STD	RND				. 105/2. 67		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-104 <LF>			SQ				. 105/2. 67		150u" / 3. 81u' 1/27u Ni	
-105 <LF>			RND				. 150/3. 81		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-106 <LF>			SQ				. 150/3. 81		150u" / 3. 81u' 1/27u Ni	
-107 <LF>			SQ				. 675/17. 15		30u" / . 76u Au OVER 50u" / 1. 27u Ni	
65823-108 <LF>	2x30	STD	SQ	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 675/17. 15	3. 36/85. 3	150u" / 3. 81u' 1/27u Ni	D


mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
AF					.XXX±.005/.XX±.13				
					.XXX±.0020/.XXX±.051				
				angles	0°±2°		product family QUICKIE		
				dr	J. SHREINER 1/16/90				code —
				enr	M. SMYK 1/16/90				
				chr	M. SMYK 1/16/90				
				appd	M. SMYK 1/16/90				
sheet index				revision sheet		scale 5:1	A	65823	

A

B



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-109(LF)	2x5	ND	SQ	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" / .76u Au OVER 50u" / 1.27u Ni	A
-110(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-111(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-112(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-113(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-114(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-115(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-116(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-117(LF)	2x30	ND		3.760/95.50	2.900/73.66	3.220/81.79		3.36/85.3		D
-118(LF)	2x5	STD		1.260/32.00	.400/10.16	.720/18.29		.86/21.8		A
-119(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-120(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-121(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-122(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-123(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-124(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-125(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-126(LF)	2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3	30u" / .76u Au OVER 50u" / 1.27u Ni	D
-127(LF)	2x5	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8	30u" / .76u GXT/GOLD FLASH	A
-128(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-129(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-130(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-131(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-132(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-133(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-134(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-135(LF)	2x30	ND		3.760/95.50	2.900/73.66	3.220/81.79		3.36/85.3		D
-136(LF)	2x5	STD		1.260/32.00	.400/10.16	.720/18.29		.86/21.8		A
-137(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-138(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-139(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-140(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-141(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-142(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-143(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-144(LF)	2x30	STD	RND	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30u" / .76u GXT/GOLD FLASH	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	product family QUICKIE	code —
AF					.XXX±.005/.XX±.13				
					.XXX±.0020/.XXX±.051				
				angles	0°±2°	INCH/MM ←→	scale 5:1	size A	sheet 7 of 21
				dr	J. SHREINER 1/16/90				
				enr	M. SMYK 1/16/90				
				chr	M. SMYK 1/16/90	sheet index	revision sheet		
				appd	M. SMYK 1/16/90				
21									



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-145 (LF)	2x5	LP	RND	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	30u' /. 76u Au OVER 50u' /1. 27u Ni	A
↑ -146 (LF)	↑	↑	SQ	↑	↑	↑	. 105/2. 67	↑	150u' /3. 81u Sn	↑
-147 (LF)			RND	↑	↑	↑	. 150/3. 81	↑	30u' /. 76u Au OVER 50u' /1. 27u Ni	↑
-148 (LF)			SQ	↑	↑	↑	. 150/3. 81	↑	150u' /3. 81u Sn	↑
-149 (LF)			SQ	↓	↓	↓	. 675/17. 15	↓	30u' /. 76u Au OVER 50u' /1. 27u Ni	↓
-150 (LF)	2x5		SQ	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 675/17. 15	. 86/21. 8	150u' /3. 81u Sn	A
-151 (LF)	2x7		RND	1. 460/37. 08	. 600/15. 24	. 920/23. 37	. 105/2. 67	1. 06/26. 9	30u' /. 76u Au OVER 50u' /1. 27u Ni	C
-152 (LF)	↑	↑	SQ	↑	↑	↑	. 105/2. 67	↑	150u' /3. 81u Sn	↑
-153 (LF)			RND	↑	↑	↑	. 150/3. 81	↑	30u' /. 76u Au OVER 50u' /1. 27u Ni	↑
-154 (LF)			SQ	↑	↑	↑	. 150/3. 81	↑	150u' /3. 81u Sn	↑
-155 (LF)	↓	↓	SQ	↓	↓	↓	. 675/17. 15	↓	30u' /. 76u Au OVER 50u' /1. 27u Ni	↓
-156 (LF)	2x7		SQ	1. 460/37. 08	. 600/15. 24	. 920/23. 37	. 675/17. 15	1. 06/26. 9	150u' /3. 81u Sn	C
-157 (LF)	2x8		RND	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	. 105/2. 67	1. 16/29. 4	30u' /. 76u Au OVER 50u' /1. 27u Ni	D
-158 (LF)	↑	↑	SQ	↑	↑	↑	. 105/2. 67	↑	150u' /3. 81u Sn	↑
-159 (LF)			RND	↑	↑	↑	. 150/3. 81	↑	30u' /. 76u Au OVER 50u' /1. 27u Ni	↑
-160 (LF)			SQ	↑	↑	↑	. 150/3. 81	↑	150u' /3. 81u Sn	↑
-161 (LF)	↓	↓	SQ	↓	↓	↓	. 675/17. 15	↓	30u' /. 76u Au OVER 50u' /1. 27u Ni	↓
-162 (LF)	2x8		SQ	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	. 675/17. 15	1. 16/29. 4	150u' /3. 81u Sn	
-163 (LF)	2x10		RND	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	. 105/2. 67	1. 36/34. 5	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-164 (LF)	↑	↑	SQ	↑	↑	↑	. 105/2. 67	↑	150u' /3. 81u Sn	
-165 (LF)			RND	↑	↑	↑	. 150/3. 81	↑	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-166 (LF)			SQ	↑	↑	↑	. 150/3. 81	↑	150u' /3. 81u Sn	
-167 (LF)	↓	↓	SQ	↓	↓	↓	. 675/17. 15	↓	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-168 (LF)	2x10		SQ	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	. 675/17. 15	1. 36/34. 5	150u' /3. 81u Sn	
-169 (LF)	2x13		RND	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	. 105/2. 67	1. 66/42. 1	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-170 (LF)	↑	↑	SQ	↑	↑	↑	. 105/2. 67	↑	150u' /3. 81u Sn	
-171 (LF)			RND	↑	↑	↑	. 150/3. 81	↑	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-172 (LF)			SQ	↑	↑	↑	. 150/3. 81	↑	150u' /3. 81u Sn	
-173 (LF)	↓	↓	SQ	↓	↓	↓	. 675/17. 15	↓	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-174 (LF)	2x13		SQ	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	. 675/17. 15	1. 66/42. 1	150u' /3. 81u Sn	
-175 (LF)	2x17		RND	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	. 105/2. 67	2. 06/52. 3	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-176 (LF)	↑	↑	SQ	↑	↑	↑	. 105/2. 67	↑	150u' /3. 81u Sn	
-177 (LF)			RND	↑	↑	↑	. 150/3. 81	↑	30u' /. 76u Au OVER 50u' /1. 27u Ni	
-178 (LF)			SQ	↑	↑	↑	. 150/3. 81	↑	150u' /3. 81u Sn	
-179 (LF)	↓	↓	SQ	↓	↓	↓	. 675/17. 15	↓	30u' /. 76u Au OVER 50u' /1. 27u Ni	
65823-180 (LF)	2x17	LP	SQ	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	. 675/17. 15	2. 06/52. 3	150u' /3. 81u Sn	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection ⊕	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	product family QUICKIE	code -	
AF					.XXX±.005/.XX±.13					
					.XXX±.0020/.XXX±.051					
				angles	0°±2°	INCH/MM ↔	scale 5:1	A	sheet 8 of 21	
				dr	J. SHREINER					1/16/90
				enr	M. SMYK					1/16/90
				chr	M. SMYK	1/16/90				
				appd	M. SMYK	1/16/90				
sheet index		revision sheet								





	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-181(LF)	2x20	LP	RND	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	. 105/2. 67	2. 36/59. 9	30u" / . 76u OVER 50u" / 1. 27u Ni	D
-182(LF)			SQ				. 105/2. 67		150u" / 3. 81u Sn	
-183(LF)			RND				. 150/3. 81		30u" / . 76u OVER 50u" / 1. 27u Ni	
-184(LF)			SQ				. 150/3. 81		150u" / 3. 81u Sn	
-185(LF)			SQ				. 675/17. 15		30u" / . 76u OVER 50u" / 1. 27u Ni	
-186(LF)	2x20		SQ	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	. 675/17. 15	2. 36/59. 9	150u" / 3. 81u Sn	
-187(LF)	2x25		RND	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	. 105/2. 67	2. 86/72. 6	30u" / . 76u OVER 50u" / 1. 27u Ni	
-188(LF)			SQ				. 105/2. 67		150u" / 3. 81u Sn	
-189(LF)			RND				. 150/3. 81		30u" / . 76u OVER 50u" / 1. 27u Ni	
-190(LF)			SQ				. 150/3. 81		150u" / 3. 81u Sn	
-191(LF)			SQ				. 675/17. 15		30u" / . 76u OVER 50u" / 1. 27u Ni	
-192(LF)	2x25		SQ	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	. 675/17. 15	2. 86/72. 6	150u" / 3. 81u Sn	
-193(LF)	2x30		RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	30u" / . 76u OVER 50u" / 1. 27u Ni	
-194(LF)			SQ				. 105/2. 67		150u" / 3. 81u Sn	
-195(LF)			RND				. 150/3. 81		30u" / . 76u OVER 50u" / 1. 27u Ni	
-196(LF)			SQ				. 150/3. 81		150u" / 3. 81u Sn	
-197(LF)			SQ				. 675/17. 15		30u" / . 76u OVER 50u" / 1. 27u Ni	
-198(LF)	2x30			3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 675/17. 15	3. 36/85. 3	150u" / 3. 81u Sn	D
-199(LF)	2x5			1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	30u" / . 76u OVER 50u" / 1. 27u Ni	A
-200(LF)	2x7			1. 460/37. 08	. 600/15. 24	. 920/23. 37		1. 06/26. 9		C
-201(LF)	2x8			1. 560/39. 62	. 700/17. 78	1. 020/25. 91		1. 16/29. 4		D
-202(LF)	2x10			1. 760/44. 70	. 900/22. 86	1. 220/30. 99		1. 36/34. 5		
-203(LF)	2x13			2. 060/52. 32	1. 200/30. 48	1. 520/38. 61		1. 66/42. 1		
-204(LF)	2x17			2. 460/62. 48	1. 600/40. 64	1. 920/48. 77		2. 06/52. 3		
-205(LF)	2x20			2. 760/70. 10	1. 900/48. 26	2. 220/56. 39		2. 36/59. 9		
-206(LF)	2x25			3. 260/82. 80	2. 400/60. 96	2. 720/69. 09		2. 86/72. 6		
-207(LF)	2x30		SQ	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	30u" / . 76u OVER 50u" / 1. 27u Ni	D
-208(LF)	2x5		RND	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 150/3. 81	. 86/21. 8	30u" / . 76u GXT/GOLD FLASH	A
-209(LF)	2x7			1. 460/37. 08	. 600/15. 24	. 920/23. 37		1. 06/26. 9		C
-210(LF)	2x8			1. 560/39. 62	. 700/17. 78	1. 020/25. 91		1. 16/29. 4		D
-211(LF)	2x10			1. 760/44. 70	. 900/22. 86	1. 220/30. 99		1. 36/34. 5		
-212(LF)	2x13			2. 060/52. 32	1. 200/30. 48	1. 520/38. 61		1. 66/42. 1		
-213(LF)	2x17			2. 460/62. 48	1. 600/40. 64	1. 920/48. 77		2. 06/52. 3		
-214(LF)	2x20			2. 760/70. 10	1. 900/48. 26	2. 220/56. 39		2. 36/59. 9		
-215(LF)	2x25			3. 260/82. 80	2. 400/60. 96	2. 720/69. 09		2. 86/72. 6		
65823-216(LF)	2x30	LP	RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 150/3. 81	3. 36/85. 3	30u" / . 76u GXT/GOLD FLASH	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection INCH/MM	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	product family QUICKIE	code —
AF					.XXX±.005/.XX±.13				
					.XXX±.0020/.XXX±.051				
					0°±2°				
				dr	J. SHREINER	1/16/90	scale 5:1	A	sheet 9 of 21
				engr	M. SMYK	1/16/90			
				chr	M. SMYK	1/16/90			
				appd	M. SMYK	1/16/90			
sheet index	revision sheet								
21									




	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-217(LF)	2x5	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u" / .76u GXT/GOLD FLASH	A
-218(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-219(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-220(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-221(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-222(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-223(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-224(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-225(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-226(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8		A
-227(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-228(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-229(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-230(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-231(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-232(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-233(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-234(LF)	2x30	ND	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.675/17.15	3.36/85.3		D
-235(LF)	2x5	STD	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8		A
-236(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-237(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-238(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-239(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-240(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-241(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-242(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
-243(LF)	2x30		RND	3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		D
-244(LF)	2x5		SQ	1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		A
-245(LF)	2x7			1.460/37.08	.600/15.24	.920/23.37		1.06/26.9		C
-246(LF)	2x8			1.560/39.62	.700/17.78	1.020/25.91		1.16/29.4		D
-247(LF)	2x10			1.760/44.70	.900/22.86	1.220/30.99		1.36/34.5		
-248(LF)	2x13			2.060/52.32	1.200/30.48	1.520/38.61		1.66/42.1		
-249(LF)	2x17			2.460/62.48	1.600/40.64	1.920/48.77		2.06/52.3		
-250(LF)	2x20			2.760/70.10	1.900/48.26	2.220/56.39		2.36/59.9		
-251(LF)	2x25			3.260/82.80	2.400/60.96	2.720/69.09		2.86/72.6		
65823-252(LF)	2x30	STD	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3	30u" / .76u GXT/GOLD FLASH	D

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
AF					.XXX±.005/.XX±.13						
					.XXX±.0020/.XXX±.051						
				angles	0°±2°				product family QUICKIE size dwg no A 65823		
				dr	J. SHREINER	1/16/90	INCH/MM				
				enr	M. SMYK	1/16/90					
				chr	M. SMYK	1/16/90		scale 5:1			
				appd	M. SMYK	1/16/90	A				
	sheet	revision									
21	index	sheet									




	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-253(LF)	2x5	LP	RND	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	30u" / . 76u GXT/GOLD FLASH	A
↑ -254(LF)	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -255(LF)	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -256(LF)	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -257(LF)	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -258(LF)	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -259(LF)	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -260(LF)	2x25	↑	↓	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6	↓	↓
↑ -261(LF)	2x30	↑	RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	↑	D
↑ -262(LF)	2x5	↑	SQ	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 675/17. 15	. 86/21. 8	↑	A
↑ -263(LF)	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -264(LF)	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -265(LF)	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -266(LF)	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -267(LF)	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -268(LF)	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -269(LF)	2x25	↓	↓	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6	↓	↓
↑ -270(LF)	2x30	LP	SQ	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 675/17. 15	3. 36/85. 3	30u" / . 76u GXT/GOLD FLASH	D
↑ -271(LF)	2x5	ND	RND	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	15u" . 38u Au OVER 50u" /1. 27u Ni	A
↑ -272(LF)	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -273(LF)	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -274(LF)	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -275(LF)	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -276(LF)	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -277(LF)	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -278(LF)	2x25	↑	↑	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6	↓	↓
↑ -279(LF)	2x30	↑	↑	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	↑	D
↑ -280(LF)	2x5	↑	↑	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 150/3. 81	. 86/21. 8	↑	A
↑ -281(LF)	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -282(LF)	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -283(LF)	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -284(LF)	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -285(LF)	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -286(LF)	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -287(LF)	2x25	↓	↓	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6	↓	↓
65823-288(LF)	2x30	ND	RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 150/3. 81	3. 36/85. 3	15u" . 38u Au OVER 50u" /1. 27u Ni	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	product family QUICKIE	code —
AF					.XXX±.005/.XX±.13				
					.XXX±.0020/.XXX±.051				
				angles	0°±2°	INCH/MM ←→	scale 5:1	size A	sheet 11 of 21
				dr	J. SHREINER 1/16/90				
				enr	M. SMYK 1/16/90				
				chr	M. SMYK 1/16/90	sheet 21	revision sheet		
				appd	M. SMYK 1/16/90				



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-289<LF>	2x5	ND	SQ	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	15u". 38u Au OVER 50u"/1. 27u Ni	A
↑ -290<LF>	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -291<LF>	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -292<LF>	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -293<LF>	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -294<LF>	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -295<LF>	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -296<LF>	2x25	↑	↑	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↑	2. 86/72. 6	↑	↓
↑ -297<LF>	2x30	ND	SQ	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	↑	D
↑ -298<LF>	2x5	STD	RND	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 675/17. 15	. 86/21. 8	↑	A
↑ -299<LF>	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -300<LF>	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -301<LF>	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -302<LF>	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -303<LF>	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -304<LF>	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -305<LF>	2x25	↑	↑	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↑	2. 86/72. 6	↑	↓
↑ -306<LF>	2x30	↑	↑	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 675/17. 15	3. 36/85. 3	↑	D
↑ -307<LF>	2x5	↑	↑	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	↑	A
↑ -308<LF>	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -309<LF>	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -310<LF>	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -311<LF>	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -312<LF>	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -313<LF>	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -314<LF>	2x25	↑	↓	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↑	2. 86/72. 6	↑	↓
↑ -315<LF>	2x30	↑	RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	↑	D
↑ -316<LF>	2x5	↑	SQ	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 150/3. 81	. 86/21. 8	↑	A
↑ -317<LF>	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
↑ -318<LF>	2x8	↑	↑	1. 560/39. 62	. 700/17. 78	1. 020/25. 91	↑	1. 16/29. 4	↑	D
↑ -319<LF>	2x10	↑	↑	1. 760/44. 70	. 900/22. 86	1. 220/30. 99	↑	1. 36/34. 5	↑	↑
↑ -320<LF>	2x13	↑	↑	2. 060/52. 32	1. 200/30. 48	1. 520/38. 61	↑	1. 66/42. 1	↑	↑
↑ -311<LF>	2x17	↑	↑	2. 460/62. 48	1. 600/40. 64	1. 920/48. 77	↑	2. 06/52. 3	↑	↑
↑ -312<LF>	2x20	↑	↑	2. 760/70. 10	1. 900/48. 26	2. 220/56. 39	↑	2. 36/59. 9	↑	↑
↑ -313<LF>	2x25	↑	↓	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↑	2. 86/72. 6	↑	↓
65823-313<LF>	2x30	STD	SQ	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 150/3. 81	3. 36/85. 3	15u". 38u Au OVER 50u"/1. 27u Ni	D

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	product family QUICKIE	code —
AF					.XXX±.005/.XX±.13						
					.XXX±.0020/.XXX±.051						
					angles	0°±2°					
					dr	J. SHREINER	1/16/90				
				enr	M. SMYK	1/16/90	INCH/MM ←→	scale 5:1	size A	sheet 12 of 21	
				chr	M. SMYK	1/16/90					
				appd	M. SMYK	1/16/90					
sheet index		revision sheet									
21											



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-325 (LF)	2x5	LP	RND	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 105/2. 67	. 86/21. 8	15u" / . 38u Au OVER 50u" / 1. 27u Ni	A
↑ -326 (LF)	2x7	↑	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9	↑	C
-327 (LF)	2x8			1. 560/39. 62	. 700/17. 78	1. 020/25. 91		1. 16/29. 4		D
-328 (LF)	2x10			1. 760/44. 70	. 900/22. 86	1. 220/30. 99		1. 36/34. 5		↑
-329 (LF)	2x13			2. 060/52. 32	1. 200/30. 48	1. 520/38. 61		1. 66/42. 1		↑
-330 (LF)	2x17			2. 460/62. 48	1. 600/40. 64	1. 920/48. 77		2. 06/52. 3		
-331 (LF)	2x20			2. 760/70. 10	1. 900/48. 26	2. 220/56. 39		2. 36/59. 9		
-332 (LF)	2x25			3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6		↓
-333 (LF)	2x30			3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3		D
-334 (LF)	2x5			1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 150/3. 81	. 86/21. 8		A
-335 (LF)	2x7			1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9		C
-336 (LF)	2x8			1. 560/39. 62	. 700/17. 78	1. 020/25. 91		1. 16/29. 4		D
-337 (LF)	2x10			1. 760/44. 70	. 900/22. 86	1. 220/30. 99		1. 36/34. 5		↑
-338 (LF)	2x13			2. 060/52. 32	1. 200/30. 48	1. 520/38. 61		1. 66/42. 1		↑
-339 (LF)	2x17			2. 460/62. 48	1. 600/40. 64	1. 920/48. 77		2. 06/52. 3		
-340 (LF)	2x20			2. 760/70. 10	1. 900/48. 26	2. 220/56. 39		2. 36/59. 9		
-341 (LF)	2x25			3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6		↓
-342 (LF)	2x30		RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 150/3. 81	3. 36/85. 3		D
-343 (LF)	2x5		SQ	1. 260/32. 00	. 400/10. 16	. 720/18. 29	. 675/17. 15	. 86/21. 8		A
-344 (LF)	2x7		↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9		C
-345 (LF)	2x8			1. 560/39. 62	. 700/17. 78	1. 020/25. 91		1. 16/29. 4		D
-346 (LF)	2x10			1. 760/44. 70	. 900/22. 86	1. 220/30. 99		1. 36/34. 5		↑
-347 (LF)	2x13			2. 060/52. 32	1. 200/30. 48	1. 520/38. 61		1. 66/42. 1		↑
-348 (LF)	2x17			2. 460/62. 48	1. 600/40. 64	1. 920/48. 77		2. 06/52. 3		
-349 (LF)	2x20			2. 760/70. 10	1. 900/48. 26	2. 220/56. 39		2. 36/59. 9		
-350 (LF)	2x25			3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6		
-351 (LF)	2x30	LP	SQ	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 675/17. 15	3. 36/85. 3	15u" / . 38u Au OVER 50u" / 1. 27u Ni	↓
-352 (LF)	2x25	66258	RND	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	. 105/2. 67	2. 86/72. 6	30u" / . 76u Au OVER 50u" / 1. 27u Ni	D
-353 (LF)	2x7	ND	↑	1. 460/37. 08	. 600/15. 24	. 920/23. 37	↑	1. 06/26. 9		C
-354 (LF)	2x8	↑		1. 560/39. 62	. 700/17. 78	1. 020/25. 91		1. 16/29. 4		D
-355 (LF)	2x10			1. 760/44. 70	. 900/22. 86	1. 220/30. 99		1. 36/34. 5		↑
-356 (LF)	2x13			2. 060/52. 32	1. 200/30. 48	1. 520/38. 61		1. 66/42. 1		↑
-357 (LF)	2x17			2. 460/62. 48	1. 600/40. 64	1. 920/48. 77		2. 06/52. 3		↑
-358 (LF)	2x20			2. 760/70. 10	1. 900/48. 26	2. 220/56. 39		2. 36/59. 9		↑
↓ -359 (LF)	2x25	↓	↓	3. 260/82. 80	2. 400/60. 96	2. 720/69. 09	↓	2. 86/72. 6		↓
65823-360 (LF)	2x30	ND	RND	3. 760/95. 50	2. 900/73. 66	3. 220/81. 79	. 105/2. 67	3. 36/85. 3	30u" / . 76u Au OVER 50u" / 1. 27u Ni	D


*CUSTOMER SPECIAL

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
AF					.XXX±.005/.XX±.13				
				angles	.XXX±.0020/.XXX±.051	INCH/MM 	product family QUICKIE		
				dr	0°±2°			size dwg no	
				enr	J. SHREINER 1/16/90	scale 5:1	A		
				chr	M. SMYK 1/16/90			sheet 13 of 21	
				appd	M. SMYK 1/16/90				
sheet index		revision sheet							




	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-361(LF)	2x5	ND	RND	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	30u"/.76u Au OVER 50u"/1.27u Ni	A
↑ -362(LF)	↑	ND	RND	↑	↑	↑	↑	↑	30u"/.76u Au OVER 50u"/1.27u Ni	B
-363(LF)		ND	RND						15"/.38u Au OVER 50u"/1.27u Ni	↑
-364(LF)		ND	RND						30u"/.76u GXT/GOLD FLASH	
-365(LF)		ND	SQ						150u"/3.81u Sn	
-366(LF)		STD	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-367(LF)		STD	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-368(LF)		STD	RND						30u"/.76u GXT/GOLD FLASH	
-369(LF)		STD	SQ						150u"/3.81u Sn	
-370(LF)		LP	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-371(LF)		LP	RND						15"/.38u Au OVER 50u"/1.27u Ni	
↓ -372(LF)		LP	RND				↓		30u"/.76u GXT/GOLD FLASH	
-373(LF)		LP	SQ				.105/2.67		150u"/3.81u Sn	
-374(LF)		ND	RND				.150/3.81		30u"/.76u Au OVER 50u"/1.27u Ni	
-375(LF)		ND	RND				↑		15"/.38u Au OVER 50u"/1.27u Ni	
-376(LF)		ND	RND						30u"/.76u GXT/GOLD FLASH	
-377(LF)		ND	SQ						150u"/3.81u Sn	
-378(LF)		STD	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-379(LF)		STD	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-380(LF)		STD	RND						30u"/.76u GXT/GOLD FLASH	
-381(LF)		STD	SQ						150u"/3.81u Sn	
-382(LF)		LP	RND						30u"/.76u Au OVER 50u"/1.27u Ni	
-383(LF)		LP	RND						15"/.38u Au OVER 50u"/1.27u Ni	
-384(LF)		LP	RND						30u"/.76u GXT/GOLD FLASH	
-385(LF)		LP	SQ				.150/3.81		150u"/3.81u Sn	
-386(LF)		ND	SQ				.675/17.15		30u"/.76u Au OVER 50u"/1.27u Ni	
-387(LF)		ND	↑				↑		15"/.38u Au OVER 50u"/1.27u Ni	
-388(LF)		ND							30u"/.76u GXT/GOLD FLASH	
-389(LF)		ND							150u"/3.81u Sn	
-390(LF)		STD							30u"/.76u Au OVER 50u"/1.27u Ni	
-391(LF)		STD							15"/.38u Au OVER 50u"/1.27u Ni	
-392(LF)		STD							30u"/.76u GXT/GOLD FLASH	
-393(LF)		STD							150u"/3.81u Sn	
-394(LF)		LP							30u"/.76u Au OVER 50u"/1.27u Ni	
↓ -395(LF)	↓	LP	↓	↓	↓	↓	↓	↓	15"/.38u Au OVER 50u"/1.27u Ni	↓
65823-396(LF)	2x5	LP	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	30u"/.76u GXT/GOLD FLASH	B

*CUSTOMER SPECIAL

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE			
AF					.XXX±.005/.XX±.13							
					.XXX±.0020/.XXX±.051							
				angles	0°±2°			INCH/MM scale 5:1	product family QUICKIE size dwg no A 65823			
				dr	J. SHREINER	1/16/90						
				enr	M. SMYK	1/16/90						
				chr	M. SMYK	1/16/90						
				appd	M. SMYK	1/16/90						
sheet index		revision sheet										
21												




	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-397(LF)	2x5	LP	SQ	1.260/32.00	.400/10.16	.720/18.29	.675/17.15	.86/21.8	150u"/3.81u Sn	B
-398(LF)	2x10	66258-001	RND	1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5	30u"/.76u Au OVER 50u"/1.27u Ni	D
-399(LF)	2x5	ND	SQ	1.260/32.00	.400/10.16	.720/18.29	.105/2.67	.86/21.8	15u"/.38u Au OVER 50u"/1.27u Ni	A
-400(LF)		STD					.105/2.67			
-401(LF)		LP					.105/2.67			
-402(LF)		ND					.150/3.81			
-403(LF)		STD					.150/3.81			
-404(LF)		LP					.150/3.81			A
-405(LF)		ND					.105/2.67			B
-406(LF)		STD					.105/2.67			
-407(LF)		LP					.105/2.67			
-408(LF)		ND					.150/3.81			
-409(LF)		STD					.150/3.81			
-410(LF)	2x5	LP		1.260/32.00	.400/10.16	.720/18.29	.150/3.81	.86/21.8		B
-411(LF)	2x7	ND		1.460/37.08	.600/15.24	.920/23.37	.105/2.67	1.06/26.9		C
-412(LF)		STD					.105/2.67			
-413(LF)		LP					.105/2.67			
-414(LF)		ND					.150/3.81			
-415(LF)		STD					.150/3.81			
-416(LF)	2x7	LP		1.460/37.08	.600/15.24	.920/23.37	.150/3.81	1.06/26.9		C
-417(LF)	2x8	ND		1.560/39.62	.700/17.78	1.020/25.91	.105/2.67	1.16/29.4		D
-418(LF)		STD					.105/2.67			
-419(LF)		LP					.105/2.67			
-420(LF)		ND					.150/3.81			
-421(LF)		STD					.150/3.81			
-422(LF)	2x8	LP		1.560/39.62	.700/17.78	1.020/25.91	.150/3.81	1.16/29.4		
-423(LF)	2x10	ND		1.760/44.70	.900/22.86	1.220/30.99	.105/2.67	1.36/34.5		
-424(LF)		STD					.105/2.67			
-425(LF)		LP					.105/2.67			
-426(LF)		ND					.150/3.81			
-427(LF)		STD					.150/3.81			
-428(LF)	2x10	LP		1.760/44.70	.900/22.86	1.220/30.99	.150/3.81	1.36/34.5		
-429(LF)	2x13	ND		2.060/52.32	1.200/30.48	1.520/38.61	.105/2.67	1.66/42.1		
-430(LF)		STD					.105/2.67			
-431(LF)		LP					.105/2.67			
65823-432(LF)	2x13	ND	SQ	2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1	15u"/.38u Au OVER 50u"/1.27u Ni	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE	product family QUICKIE	code —	
AF					.XXX±.005/.XX±.13					
					.XXX±.0020/.XXX±.051					
				angles	0°±2°	INCH/MM ←→	scale 5:1	size A	sheet 15 of 21	
				dr	J. SHREINER					1/16/90
				enr	M. SMYK					1/16/90
				chr	M. SMYK	1/16/90				
				appd	M. SMYK	1/16/90				
sheet index		revision sheet								
21										



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-433<LF>	2x13	STD	SQ	2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1	15u" / .38u Au OVER 50u" / 1.27u Ni	D
-434<LF>	2x13	LP		2.060/52.32	1.200/30.48	1.520/38.61	.150/3.81	1.66/42.1		
-435<LF>	2x17	ND		2.460/62.48	1.600/40.64	1.920/48.77	.105/2.67	2.06/52.3		
-436<LF>		STD					.105/2.67			
-437<LF>		LP					.105/2.67			
-438<LF>		ND					.150/3.81			
-439<LF>		STD					.150/3.81			
-440<LF>	2x17	LP		2.460/62.48	1.600/40.64	1.920/48.77	.150/3.81	2.06/52.3		
-441<LF>	2x20	ND		2.760/70.10	1.900/48.26	2.220/56.39	.105/2.67	2.36/59.9		
-442<LF>		STD					.105/2.67			
-443<LF>		LP					.105/2.67			
-444<LF>		ND					.150/3.81			
-445<LF>		STD					.150/3.81			
-446<LF>	2x20	LP		2.760/70.10	1.900/48.26	2.220/56.39	.150/3.81	2.36/59.9		
-447<LF>	2x25	ND		3.260/82.80	2.400/60.96	2.720/69.09	.105/2.67	2.86/72.6		
-448<LF>		STD					.105/2.67			
-449<LF>		LP					.105/2.67			
-450<LF>		ND					.150/3.81			
-451<LF>		STD					.150/3.81			
-452<LF>	2x25	LP		3.260/82.80	2.400/60.96	2.720/69.09	.150/3.81	2.86/72.6		
-453<LF>	2x30	ND		3.760/95.50	2.900/73.66	3.220/81.79	.105/2.67	3.36/85.3		
-454<LF>		STD					.105/2.67			
-455<LF>		LP					.105/2.67			
-456<LF>		ND					.150/3.81			
-457<LF>		STD					.150/3.81			
-458<LF>	2x30	LP	SQ	3.760/95.50	2.900/73.66	3.220/81.79	.150/3.81	3.36/85.3		
-459<LF>	2x12	ND	RND	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.6		
-460<LF>		STD								
-461<LF>		LP							15u" / .38u Au OVER 50u" / 1.27u Ni	
-462<LF>		ND							30u" / .76u Au OVER 50u" / 1.27u Ni	
-463<LF>		STD							30u" / .76u Au OVER 50u" / 1.27u Ni	
-464<LF>		LP							30u" / .76u Au OVER 50u" / 1.27u Ni	
-465<LF>		ND							30u" / .76u GXT/GOLD FLASH	
-466<LF>		STD							30u" / .76u GXT/GOLD FLASH	
-467<LF>		LP	RND						30u" / .76u GXT/GOLD FLASH	
65823-468<LF>	2x12	ND	SQ	1.960/49.80	1.100/27.94	1.420/36.07	.105/2.67	1.56/39.6	150u" / 3.81u Sn	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE			
AF					.XXX±.005/.XX±.13					
					.XXX±.0020/.XXX±.051					
					angles 0°±2°					
				dr	J. SHREINER	1/16/90	product family QUICKIE			
				engr	M. SMYK	1/16/90			code —	
				chr	M. SMYK	1/16/90				sheet 16 of 21
				appd	M. SMYK	1/16/90				
sheet index				revision sheet			scale 5:1	A	65823	




	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-469(LF)	2x12	STD	SQ	1. 960/49. 80	1. 100/27. 94	1. 420/36. 07	. 105/2. 67	1. 56/39. 62	150u"/3. 81u TIN	D
-470(LF)		LP	SQ				. 105/2. 67		150u"/3. 81u TIN	
-471(LF)		ND	RND				. 150/3. 81		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-472(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-473(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-474(LF)		ND							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-475(LF)		STD							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-476(LF)		LP							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-477(LF)		ND							30u"/. 76u GXT/GOLD FLASH	
-478(LF)		STD							30u"/. 76u GXT/GOLD FLASH	
-479(LF)		LP	RND						30u"/. 76u GXT/GOLD FLASH	
-480(LF)		ND	SQ						150u"/3. 81u TIN	
-481(LF)		STD							150u"/3. 81u TIN	
-482(LF)		LP					. 150/3. 81		150u"/3. 81u TIN	
-483(LF)		ND					. 105/2. 67		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-484(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-485(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-486(LF)		ND							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-487(LF)		STD							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-488(LF)		LP							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-489(LF)		ND							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-490(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-491(LF)		LP					. 105/2. 67		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-492(LF)		ND					. 675/17. 15		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-493(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-494(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-495(LF)		ND							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-496(LF)		STD							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-497(LF)		LP							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-498(LF)		ND							30u"/. 76u GXT/GOLD FLASH	
-499(LF)		STD							30u"/. 76u GXT/GOLD FLASH	
-500(LF)		LP							30u"/. 76u GXT/GOLD FLASH	
-501(LF)		ND							150u"/3. 81u TIN	
-502(LF)		STD							150u"/3. 81u TIN	
-503(LF)	2x12	LP	SQ	1. 960/49. 80	1. 100/27. 94	1. 420/36. 07	. 675/17. 15	1. 56/39. 62	150u"/3. 81u TIN	
65823-504(LF)	2x15	ND	RND	2. 260/57. 40	1. 400/35. 56	1. 720/43. 69	. 105/2. 67	1. 86/47. 24	15u"/. 38u Au OVER 50u"/1. 27u Ni	D

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
AF					.XXX±.005/.XX±.13						
					.XXXX±.0020/.XXX±.051						
					0°±2°						
				dr	J. SHREINER	1/16/90	INCH/MM ←→	product family QUICKIE	code —		
				enrg	M. SMYK	1/16/90					
				chr	M. SMYK	1/16/90					
				appd	M. SMYK	1/16/90					
sheet index				revision sheet				scale 5:1		sheet 17 of 21	
21											





	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-505(LF)	2x15	STD	RND	2. 260/57. 40	1. 400/35. 56	1. 720/43. 69	. 105/2. 67	1. 86/47. 2	15u"/. 38u Au OVER 50u"/1. 27u Ni	D
-506(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-507(LF)		ND							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-508(LF)		STD							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-509(LF)		LP							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-510(LF)		ND							30u"/. 76u GXT GOLD FLASH	
-511(LF)		STD							30u"/. 76u GXT GOLD FLASH	
-512(LF)		LP	RND						30u"/. 76u GXT GOLD FLASH	
-513(LF)		ND	SQ						150u"/3. 81u TIN	
-514(LF)		STD	SQ						150u"/3. 81u TIN	
-515(LF)		LP	SQ				. 105/2. 67		150u"/3. 81u TIN	
-516(LF)		ND	RND				. 150/3. 81		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-517(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-518(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-519(LF)		ND							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-520(LF)		STD							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-521(LF)		LP							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-522(LF)		ND							30u"/. 76u GXT GOLD FLASH	
-523(LF)		STD							30u"/. 76u GXT GOLD FLASH	
-524(LF)		LP	RND						30u"/. 76u GXT GOLD FLASH	
-525(LF)		ND	SQ						150u"/3. 81u TIN	
-526(LF)		STD							150u"/3. 81u TIN	
-527(LF)		LP					. 150/3. 81		150u"/3. 81u TIN	
-528(LF)		ND					. 105/2. 67		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-529(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-530(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-531(LF)		ND							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-532(LF)		STD							30u"/. 76u Au OVER 50u"/1. 27u Ni	
-533(LF)		LP					. 105/2. 67		30u"/. 76u Au OVER 50u"/1. 27u Ni	
-534(LF)		ND					. 150/3. 81		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-535(LF)		STD					. 150/3. 81		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-536(LF)		LP					. 150/3. 81		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-537(LF)		ND					. 675/17. 15		15u"/. 38u Au OVER 50u"/1. 27u Ni	
-538(LF)		STD							15u"/. 38u Au OVER 50u"/1. 27u Ni	
-539(LF)		LP							15u"/. 38u Au OVER 50u"/1. 27u Ni	
65823-540(LF)	2x15	ND	SQ	2. 260/57. 40	1. 400/35. 56	1. 720/43. 69	. 675/17. 15	1. 86/47. 2	30u"/. 76u Au OVER 50u"/1. 27u Ni	D

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3			projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE		
AF					.XXX±.005/.XX±.13						
					.XXXX±.0020/.XXX±.051						
				angles	0°±2°			INCH/MM scale 5:1	product family QUICKIE size dwg no A 65823		code — sheet 18 of 21
				dr	J. SHREINER	1/16/90					
				enrg	M. SMYK	1/16/90					
				chr	M. SMYK	1/16/90					
				appd	M. SMYK	1/16/90					
sheet index				revision sheet							
21											



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM E	TERMINAL PLATING NOTE 12	STYLE
65823-541(LF)	2x15	STD	SQ	2. 260/57. 40	1. 400/35. 56	1. 720/48. 69	. 675/17. 15	1. 86/47. 2	30u" / . 76u Au OVER 50u" / 1. 27u Ni	D
-542(LF)		LP							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-543(LF)		ND							30u" / . 76u GXT/GOLD FLASH	
-544(LF)		STD							30u" / . 76u GXT/GOLD FLASH	
-545(LF)		LP							30u" / . 76u GXT/GOLD FLASH	
-546(LF)		ND							150u" / 3. 81u TIN	
-547(LF)		STD							150u" / 3. 81u TIN	
-548(LF)	2x15	LP	SQ	2. 260/57. 40	1. 400/35. 56	1. 720/43. 69	. 675/17. 15	1. 86/47. 2	150u" / 3. 81u TIN	
-549(LF)	2x22	ND	RND	2. 960/75. 20	2. 100/53. 34	2. 420/61. 47	. 105/2. 67	2. 56/65. 0	15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-550(LF)		STD							15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-551(LF)		LP							15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-552(LF)		ND							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-553(LF)		STD							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-554(LF)		LP							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-555(LF)		ND							30u" / . 76u GXT/GOLD FLASH	
-556(LF)		STD							30u" / . 76u GXT/GOLD FLASH	
-557(LF)		LP	RND						30u" / . 76u GXT/GOLD FLASH	
-558(LF)		ND	SQ						150u" / 3. 81u TIN	
-559(LF)		STD	SQ						150u" / 3. 81u TIN	
-560(LF)		LP	SQ				. 105/2. 67		150u" / 3. 81u TIN	
-561(LF)		ND	RND				. 150/3. 81		15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-562(LF)		STD							15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-563(LF)		LP							15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-564(LF)		ND							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-565(LF)		STD							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-566(LF)		LP							30u" / . 76u Au OVER 50u" / 1. 27u Ni	
-567(LF)		ND							30u" / . 76u GXT/GOLD FLASH	
-568(LF)		STD							30u" / . 76u GXT/GOLD FLASH	
-569(LF)		LP	RND						30u" / . 76u GXT/GOLD FLASH	
-570(LF)		ND	SQ						150u" / 3. 81u TIN	
-571(LF)		STD							150u" / 3. 81u TIN	
-572(LF)		LP					. 150/3. 81		150u" / 3. 81u TIN	
-573(LF)		ND					. 105/2. 67		15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-574(LF)		STD							15u" / . 38u Au OVER 50u" / 1. 27u Ni	
-575(LF)		LP							15u" / . 38u Au OVER 50u" / 1. 27u Ni	
65823-576(LF)	2x22	ND	SQ	2. 960/75. 20	2. 100/53. 34	2. 420/61. 47	. 105/2. 67	2. 56/65. 0	30u" / . 76u Au OVER 50u" / 1. 27u Ni	D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com					
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3		projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE					
AF					.XXX±.005/.XX±.13								
					.XXX±.0020/.XXX±.051								
				angles	0°±2°		INCH/MM 	product family QUICKIE					
				dr	J. SHREINER	1/16/90				scale 5:1	A	65823	sheet 19 of 21
				enrg	M. SMYK	1/16/90							
				chr	M. SMYK	1/16/90							
				appd	M. SMYK	1/16/90							
sheet index		revision sheet											



	SIZE	LATCHES NOTE 7	PIN SHAPE	DIM A	DIM B	DIM C	DIM D	DIM F	TERMINAL PLATING NOTE 12	STYLE
65823-609 (LF)	2X5	-	RND	32.00	10.16	18.29	2.67	7.24	50u"/1.27 u Au OVER 50u"/1.27u Ni	A
-610 (LF)	2X5	-	↑	32.00	10.16	18.29	↑	↑	↑	B
-611 (LF)	2X7	-	↑	37.00	15.24	23.37	↑	↑	↑	C
-612 (LF)	2X8	-	↑	39.60	17.18	25.91	↑	↑	↑	D
-613 (LF)	2X10	-	↑	44.70	22.86	30.99	↑	↑	↑	↑
-614 (LF)	2X13	-	↑	52.30	30.48	38.61	↑	↑	↑	↑
-615 (LF)	2X17	-	↑	62.40	40.64	48.77	↑	↑	↑	↑
-616 (LF)	2X20	-	↑	70.10	48.26	56.39	↑	↑	↑	↑
-617 (LF)	2X25	-	↑	82.80	60.96	69.09	↑	↑	↑	↓
-618 (LF)	2X30	-	↑	95.50	76.66	81.79	↑	↑	↑	D
-619 (LF)	2X5	STD	↑	32.00	10.16	18.29	↑	↑	↑	A
-620 (LF)	2X5	↑	↑	32.00	10.16	18.29	↑	↑	↑	B
-621 (LF)	2X7	↑	↑	37.00	15.24	23.37	↑	↑	↑	C
-622 (LF)	2X8	↑	↑	39.60	17.18	25.91	↑	↑	↑	D
-623 (LF)	2X10	↑	↑	44.70	22.86	30.99	↑	↑	↑	↑
-624 (LF)	2X13	↑	↑	52.30	30.48	38.61	↑	↑	↑	↑
-625 (LF)	2X17	↑	↑	62.40	40.64	48.77	↑	↑	↑	↑
-626 (LF)	2X20	↑	↑	70.10	48.26	56.39	↑	↑	↑	↑
-627 (LF)	2X25	↑	↑	82.80	60.96	69.09	↑	↑	↑	↑
-628 (LF)	2X30	STD	RND	95.50	76.66	81.79	2.67	7.24	50u"/1.27 u Au OVER 50u"/1.27u Ni	D

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI www.fciconnect.com			
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3		projection 	title HEADER, QUICKIE SEA, HORSE, RIGHT ANGLE				
AF					.XXX±.005/.XX±.13							
					.XXX±.0020/.XXX±.051							
				angles	0°±2°			product family QUICKIE			code —	
				dr	J. SHREINER	1/16/90						
				enrg	M. SMYK	1/16/90						
				chr	M. SMYK	1/16/90	scale 5:1	A 65823			sheet 21 of 21	
				appd	M. SMYK	1/16/90						
sheet index	revision sheet											