






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J		A1	REVISED	ECR-08-029319	19NOV08	T.F
		A2	REVISED	PER ECO-09-024927	09NOV09	KK

APVD	K.I
AEG	




1. MATERIAL & FINISH
HOUSING : GLASS FILLED LCP
CONTACT : COPPER ALLOY
FINISH-SEE NOTES 2
LATCH : STAINLESS STEEL. TIN PL.
2. CONTACT PLATING
Au (0.0003) PL. AT CONTACT, TIN PL. AT
TINE OVER Ni PL.
- 3 TOLERANCE : NON CUMULATIVE.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




4 OBSOLETE	BLACK	6.15	5316437-2
	NATURAL	2.98	5316437-1
	HOUSING COLOR	A	PART No.

GENERAL TOLERANCE
10≥:±0.2
30≥ >10:±0.25
100≥ >30:±0.3
ANGLES:±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	LEO ZHOU	20APR05	 Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: mm		CHK	STEVEN YAO	20APR05				
		APVD	IENOMOTO	20APR05	NAME MIII SOCKET 88P HIGH PROFILE TYPE			
		PRODUCT SPEC 108-5403						
		APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL SEE NOTES	FINISH SEE NOTES	WEIGHT			A2	00779	C=5316437	
CUSTOMER DRAWING				SCALE	2:1	SHEET	1 OF 2	REV A2

REVISIONS					
LOC	DIST	P	LTR	DESCRIPTION	DATE
J				SEE SHEET 1	



(88 PIN SMALL OUTLINE DIMM)
RECOMMENDED DIMENSIONS OF "88 PIN SMALL OUTLINE DIMM" P.C.BOARD

6.35	5.0V
3.18	3.3V
B	TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: mm		CHK		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD		MIII SOCKET 88P HIGH PROFILE TYPE	
MATERIAL		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO	
FINISH		APPLICATION SPEC		A2 00779 C=5316437	
		WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		—	
		SCALE 2:1		SHEET 2 OF 2 REV A2	