800 mA, 2.85 V, SCSI-2 **Active Terminator, Low Dropout Voltage Regulator**


The MC34268 is a medium current, low dropout positive voltage regulator specifically designed for use in SCSI-2 active termination circuits. This device offers the circuit designer an economical solution for precision voltage regulation, while keeping power losses to a minimum. The regulator consists of a 1.0 V dropout composite PNP/NPN pass transistor, current limiting, and thermal limiting. These devices are packaged in the SOIC-8 and DPAK-3 and SOT-223 surface mount power packages.

Applications include active SCSI-2 terminators and post regulation of switching power supplies.

Features

- 2.85 V Output Voltage for SCSI-2 Active Termination
- 1.0 V Dropout
- Output Current in Excess of 800 mA
- Thermal Protection
- Short Circuit Protection
- Output Trimmed to 1.4% Tolerance
- No Minimum Load Required
- Space Saving DPAK-3, SOT-223 and SOIC-8 Surface Mount Power Packages
- Pb-Free Packages are Available

Simplified Block Diagram





ON Semiconductor®

http://onsemi.com

MARKING DIAGRAMS



SOIC-8 **D SUFFIX CASE 751**




A = Assembly Location

L = Wafer Lot

Y = Year

W = Work Week





DPAK-3 **DT SUFFIX** CASE 369A





SOT-223 ST SUFFIX **CASE 318E**





Pin 1. Ground 2. Output

3. Input 4. Output

Heatsink surface (shown as terminal 4 in

case outline drawing) is connected to Pin 2. **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 3 of this data sheet.

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Power Supply Input Voltage	V _{in}	15	V
Power Dissipation and Thermal Characteristics			
DT Suffix, Plastic Package, Case 369A			
$T_A = 25$ °C, Derate Above $T_A = 25$ °C	P_{D}	Internally Limited	W
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	5.0	°C/W
Thermal Resistance, Junction-to-Air	$R_{\theta JA}$	87	°C/W
D Suffix, Plastic Package, Case 751			
$T_A = 25$ °C, Derate Above $T_A = 25$ °C	P_{D}	Internally Limited	W
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	22	°C/W
Thermal Resistance, Junction-to-Air	$R_{\theta JA}$	140	°C/W
ST Suffix, Plastic Package, Case 318E			
T _A = 25°C, Derate Above T _A = 25°C	P_{D}	Internally Limited	W
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	15	°C/W
Thermal Resistance, Junction-to-Air	$R_{\theta JA}$	245	°C/W
Operating Ambient Temperature Range	T _A	0 to +125	°C
Maximum Die Junction Temperature	TJ	+150	°C
Storage Temperature	T _{stg}	– 55 to +150	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

ELECTRICAL CHARACTERISTICS

 $(V_{in}$ = 4.25 V, C_{O} = 10 μ F, for typical values T_{A} = 25°C, for min/max values T_{A} = 0°C to +125°C, unless otherwise noted.)

Characteristic	Symbol	Min	Тур	Max	Unit
Output Voltage (T_A = 25°C, I_O = 0 mA) Output Voltage, over Line, Load, and Temperature (V_{in} = 3.9 V to 15 V, I_O = 0 mA to 490 mA)	Vo	2.81 2.76	2.85 2.85	2.89 2.93	V
Line Regulation (V_{in} = 4.25 V to 15 V, I_{O} = 0 mA, T_{A} = 25°C)	Reg _{line}	_	-	0.3	%
Load Regulation (I _O = 0 mA to 800 mA, T _A = 25°C)	Reg _{load}	-	-	0.5	%
Dropout Voltage (I _O = 490 mA)		-	0.95	1.1	V
Ripple Rejection (f = 120 Hz)	RR	55	-	-	dB
Maximum Output Current (V _{in} = 5.0 V)	I _(max)	800	-	-	mA
Bias Current (V _{in} = 4.25 V, I _O = 0 mA)		-	5.0 to 3.0	8.0	mA
Minimum Load Current to maintain Regulation (V _{in} = 15 V)	I _{L(min)}	-	-	0	mA




Figure 1. Dropout Voltage versus
Output Load Current




Figure 2. Transient Load Regulation




Figure 3. Typical SCSI Application

Figure 3 is a circuit of a typical SCSI terminator application. The MC34268 is designed specifically to provide 2.85 V required to drive a SCSI-2 bus. The output current capability of the regulator is in excess of 800 mA; enough to drive standard SCSI-2, fast SCSI-2, and some wide SCSI-2 applications. The typical dropout voltage is less than 1.0 V, allowing the IC to regulate to input voltages less than 4.0 V. Internal protective features include current and thermal limiting.

The MC34268 requires an external 10 μF capacitor with an ESR of less than 10 Ω for stability over temperature. With economical electrolytic capacitors, cold temperature operation can pose a stability problem. As temperature decreases, the capacitance also decreases and the ESR increases, which could cause the circuit to oscillate. Tantalum capacitors may be a better choice if small size is a requirement. Also, the capacitance and ESR of a tantalum capacitor is more stable over temperature.




Figure 4. SOIC-8 Thermal Resistance versus P.C.B. Copper Length




Figure 5. DPAK-3 Thermal Resistance versus P.C.B. Copper Length


ORDERING INFORMATION

Device	Package	Shipping Information [†] 98 Units / Rail		
MC34268D	SOIC-8			
MC34268DG	SOIC-8 (Pb-Free)	98 Units / Rail		
MC34268DR2	SOIC-8	2500 Units / Tape & Reel		
MC34268DR2G	SOIC-8 (Pb-Free)	2500 Units / Tape & Reel		
MC34268DT	DPAK-3	75 Units / Rail		
MC34268DTG	DPAK-3 (Pb-Free)	75 Units / Rail		
MC34268DTRK	DPAK-3	2500 Units / Tape & Reel		
MC34268DTRKG	DPAK-3 (Pb-Free)	2500 Units / Tape & Reel		
MC34268STT3	SOT-223	4000 Units / Tape & Reel		

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

SOIC-8 **D SUFFIX** CASE 751-07 **ISSUE AB**



NOTES:

- NOTES:

 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.


 2. CONTROLLING DIMENSION: MILLIMETER.

 3. DIMENSION A AND B DO NOT INCLUDE MOLD PROTRUSION.

 4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER CIDE.
- 4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE.
 5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT MAXIMUM MATERIAL CONDITION.
 6. 751-01 THRU 751-06 ARE OBSOLETE. NEW STANDARD IS 751-07.

	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
Α	4.80	5.00	0.189	0.197
В	3.80	4.00	0.150	0.157
С	1.35	1.75	0.053	0.069
D	0.33	0.51	0.013	0.020
G	1.27 BSC		0.050 BSC	
Н	0.10	0.25	0.004 0.010	
J	0.19	0.25	0.007	0.010
K	0.40	1.27	0.016	0.050
M	0 °	8 °	0 ° 8	
N	0.25	0.50	0.010	0.020
S	5.80	6.20	0.228	0.244

SOLDERING FOOTPRINT*




SOIC-8

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS


DPAK-3 **DT SUFFIX** CASE 369A-13 **ISSUE AB**



- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.250	5.97	6.35
В	0.250	0.265	6.35	6.73
С	0.086	0.094	2.19	2.38
D	0.027	0.035	0.69	0.88
E	0.033	0.040	0.84	1.01
F	0.037	0.047	0.94	1.19
G	0.180 BSC		4.58 BSC	
Н	0.034	0.040	0.87	1.01
J	0.018	0.023	0.46	0.58
K	0.102	0.114	2.60	2.89
L	0.090 BSC		2.29 BSC	
R	0.175	0.215	4.45	5.46
S	0.020	0.050	0.51	1.27
U	0.020		0.51	
٧	0.030	0.050	0.77	1.27
Z	0.138		3.51	

SOLDERING FOOTPRINT*





DPAK-3

^{*}For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

SOT-223 ST SUFFIX CASE 318E-04 ISSUE K






NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI
 VIA EM 1000
- Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.

DOITHTOLEING DIMENTOION. INTOIN.					
	INCHES		MILLIN	IETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.249	0.263	6.30	6.70	
В	0.130	0.145	3.30	3.70	
С	0.060	0.068	1.50	1.75	
D	0.024	0.035	0.60	0.89	
F	0.115	0.126	2.90	3.20	
G	0.087	0.094	2.20	2.40	
Н	0.0008	0.0040	0.020	0.100	
J	0.009	0.014	0.24	0.35	
K	0.060	0.078	1.50	2.00	
L	0.033	0.041	0.85	1.05	
M	0 °	10 °	0 °	10 °	
S	0.264	0.287	6.70	7.30	

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082–1312 USA Phone: 480–829–7710 or 800–344–3860 Toll Free USA/Canada Fax: 480–829–7709 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2–9–1 Kamimeguro, Meguro–ku, Tokyo, Japan 153–0051 Phone: 81–3–5773–3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.