

TURCK
works

Industrial
Automation




Universal Magnetic Field Sensors



www.turck.com

The **BIM-UNT**, a universal magnetic field sensor, is the latest addition to the inductive-magnetic family of switches by **TURCK**. It has the ability to detect the position of a piston on all types of standard pneumatic cylinders. The sensor is polarity protected, has reliable switching points and a fast response time. It is immune to high levels of EMC and vibration, and is IP 67 rated for use in harsh environments.

The **BIM-UNT** not only offers improved packaging and performance, it also simplifies maintenance, helps prevent over-stocking and streamlines the production process. Additionally, it comes with compatible accessories to help ease installation.







Mounting Advantages

The **BIM-UNT** universal magnetic field sensor is designed to detect the piston on all standard pneumatic cylinders. The sensor can be direct mounted with the help of cost-efficient accessories, making it one of the most versatile sensors on the market.

- A strategically placed wire and screw holds the sensor down – even when the cable is tugged on – and helps eliminate cable strain.
- The sensor is equipped with a simple and robust mounting system to ensure stability during operation. This makes it easy to install and ensures fewer re-adjustments of the sensor.
- Economical accessories, from precision mounts and wire-strain accessories, to optional clips that hold the wire in place in any shaped groove. This eliminates the need for expensive custom-fit accessories.

Types and Technical Data


Housing Styles	Part Number	ID Number	Connection
BIM-UNT Potted-In Cable 	BIM-UNT-AP6X	S4685720	PUR cable, 2 m, PNP
	BIM-UNT-AN6X	S4685702	PUR cable, 2 m, NPN
	BIM-UNT-AP6X 7M	S4685721	PUR cable, 7 m, PNP
	BIM-UNT-AN6X 7M	S4685701	PUR cable, 7 m, NPN
BIM-UNT <i>picofast</i>® Snap Lock Quick Disconnect 	BIM-UNT-AP6X-0.3M-PSG 3S	S4685722	Pigtail M8x1, snap lock / fixed thread, 0.3 m PUR cable, PNP
	BIM-UNT-AN6X-0.3M-PSG 3S	S4685705	Pigtail M8x1, snap lock / fixed thread, 0.3 m PUR cable, NPN
BIM-UNT <i>picofast</i>® Quick Disconnect 	BIM-UNT-AP6X-0.3M-PSG 3M	S4685723	Pigtail M8x1, threaded coupling nut, 0.3 m PUR cable, PNP
	BIM-UNT-AN6X-0.3M-PSG 3M	S4685706	Pigtail M8x1, threaded coupling nut, 0.3 m PUR cable, NPN
	BIM-UNT-AP6X-0.6M-PSG 3M	S4685724	Pigtail M8x1, threaded coupling nut, 0.6 m PUR cable, PNP
BIM-UNT <i>eurofast</i>® Quick Disconnect 	BIM-UNT-AP6X-0.3M-RS 4T	S46857260	Pigtail M12x1, threaded coupling nut, 0.3 m PUR cable, PNP

Mounting and Adjustment Accessories

Dimensional Drawings	Part Number	ID Number	Description
	KLR-UNT1	M6970623	Accessory for mounting on a round/tie-rod cylinder, diameter = 8-25 mm.
	KLR-UNT2	M6970624	Accessory for mounting on a round/tie-rod cylinder, diameter = 25-63 mm.
	KLDT-UNT2	S6913351	Accessory for mounting on a dovetail cylinder, L = 7 mm.
	KLDT-UNT3	S6913352	Accessory for mounting on a dovetail cylinder, L = 9.4 mm.
	KLDT-UNT4	S6913353	Accessory for mounting on a dovetail cylinder, L = 11.5 mm.
	KLDT-UNT5	S6913354	Accessory for mounting on a dovetail cylinder, L = 12.6 mm.
	KLZ1-INT	M6970410	Accessory for mounting on a tie-rod cylinder, diameter = 32-40 mm.
	KLZ2-INT	M6970411	Accessory for mounting on a tie-rod cylinder, diameter = 50-63 mm.
	KLZ3-INT	M6970412	Accessory for mounting on a tie-rod cylinder, diameter = 80-100 mm.
	UNT-Adjusting Bracket	S4685750	Adjustable precision-tuning accessory for locating the switching points. Can be used multiple times.
	UNT-Stopper	S4685751	Accessory for marking the switching points on T-groove cylinders.
	INT Cable Clip	M6900456	Accessory for securing the cable in place to avoid cable strain. Packing unit = 10 pieces. (One piece included in the BIM-UNT.)


Stable and Reliable Mounting

After the sensor has been inserted into the cylinder's groove, a *quick-mount* tab on the side of the sensor helps seat the sensor until the screw is tightened. This makes it easy to mount the sensor with one hand, even while it is facing downwards. The screw is made of a tool steel alloy and can be tightened with the help of a 1.5 mm Allen wrench or a standard flat-head screwdriver. This ensures stability and resistance to vibration under the harshest conditions.




Compact Housing Style & LED

The **BIM-UNT** comes with enhanced packaging and performance. It is only 28 mm in length, making it one of the most compact sensors on the market. The bright LED located on top of the sensor makes it possible to check the switching status from any convenient working angle. The sensing face is located near the front of the sensor, allowing the position of the piston rod to be consistently detected — even on compact, short stroke cylinders.



Standards

Magneto Resistive technology enables the sensor to detect the exact position of the magnet, while avoiding multiple switching points. It also exceeds the IEC standard specifications, EN60947-5-2 and EN 61000-4-6, making it compliant with these standards and immune to high levels of EMC.



Ambient Temperature -25 to +70 °C (-13 to 158 °F)
Operating Voltage 10 to 30 VDC
Ripple Vpp $\infty 10\% U_{ss}$
Rated Operating Current DC $\infty 150 \text{ mA}$
No-load Current I_o $\infty 15 \text{ mA}$
Off-state Current $\infty 0.1 \text{ mA}$
Switching Frequency $\infty 1 \text{ kHz}$
Output Function 3-wire, N.O., PNP
Short-circuit Protection Yes / Cyclic
Voltage Drop I_e $\infty 1.8 \text{ V}$
Wire-break/Reverse Polarity Protection Yes / Completely
Vibration Resistance 55 Hz (1mm)
Shock Resistance 30 g (11 ms)
Degree of Protection IP67
Overtravel Speed 10 m/s



TURCK USA

TURCK Inc.
 3000 Campus Drive
 Minneapolis, MN 55441
 Phone: (763) 553-7300
 Fax: (763) 553-0708
 Application Support:
 1-800-544-7769

TURCK Mexico

TURCK MEXICO S. DE R.L. DE C.V.
 Carr Saltillo-Zacatecas km 4.5 s/n
 Parque Industrial "La Angostura"
 Saltillo, COAH. C.P. 25070
 MEXICO
 Phone: +52 (844) 411-6647/46
 Fax: +52 (844) 482-6926
 Toll Free: 01-800-01-88725 (Mexico only)
 email: ventasmexico@turck.com

TURCK Canada

CHARTWELL
 ELECTRONICS, INC.
 140 Duffield Drive
 Markham, Ontario
 Canada, L6G 1B5
 Phone: (905) 513-7100
 Fax: (905) 513-7101
 Toll Free: 1-877-513-7769

TURCK

World Headquarters

Hans TURCK GmbH & Co. KG
 Witzlebenstrasse 7
 D-45472 Muelheim der Ruhr
 Federal Republic Of Germany
 Phone: (+49) 208-49 52-0
 Fax: (+49) 208-49 52 264

....Sense It!....Connect It!....Bus It!....Solve It!