



(Ω)



*NET IMPEDANCE (Z)			
Frequency	300 MHz	500 MHz	1 GHz
Nominal (REF)	275 Ω	340 Ω	200 Ω
Minimum	- Ω	272 Ω	- Ω



CASE DIMENSIONS(SPEC): mm [in]

DIMENSIONS ARE IN mm[INCHES].		THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND
CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF
THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT
WRITTEN AUTHORIZATION FROM STEWARD.

NOTES:

1. ASSEMBLED PART #: HFA150068-0A2
2. CASE COLOR: BLACK - "0A2"

AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture REF 2927

Steward

B	REMOVE NOTES 1, 3, & 5 REMOVE CORE & CASE P/1s REV CASE DIMS & TOLS ADD DIM E TO CASE ADJUST CORE DIM B, C, & D TOLERANCES	PROJECT/PART NUMBER:		REV	PART TYPE:	DRAWN BY:
		05/15/06		B	FERRITE	JRK
A	ORIGINAL DRAFT	DATE:		SCALE:	MATERIAL:	
		09/02/04		NTS	NiZn Ferrite	
REV	DESCRIPTION	JRK	CAD #:	TOL. #		
			HF A150068-0A2-B			