

ECTA 544 Plastic Circular Push-Pull IP67 Connector System with Crimp Contacts

Materials

Shells – Thermoplastic UL94V-0
 Contacts – Copper Alloy
 Contact Plating – Gold over Nickel
 Inserts – Thermoplastic UL94V-0

Mechanical

Temp Range – -40°C ~ 125°C
Durability
 Machined Contacts – 1000 Cycles
 Stamped Contacts – 250 Cycles

Also Available

Polarization – 3 Positions
 Contacts – Fibre Optic and Coaxial
 Right Angle Plugs & In-Line Receptacles













Related Information

Tools – Catalogue ECTA 544

Contacts for Connectors must be ordered separately see below

Contacts for Connectors must be ordered separately see below													
Plug ØD		Backshell		Mating Halves (If Plug has Pins, Receptacle must have Sockets)									
Shell	mm	Type	Cable Ø	In-Line Plug includes backshell		Square Flange Receptacle							
1	24.8	MDA	2~6mm										
		MDB	4~8mm										
2	32.5	MDA	7~12mm										
		MDB	10~14mm										
3	38.8	MDA	9~16mm										
		MDB	13~18mm										
Inserts		Part Number				Part Number							
		Sockets		Pins		Sockets		Pins					
103		5440MDA103F		5440MDA103M		5440MDB103F		5440MDB103M		5440E103F		5440E103M	
105		5440MDA105F		5440MDA105M		5440MDB105F		5440MDB105M		5440E105F		5440E105M	
107		5440MDA107F		5440MDA107M		5440MDB107F		5440MDB107M		5440E107F		5440E107M	
203		5440MDA203F		5440MDA203M		5440MDB203F		5440MDB203M		5440E203F		5440E203M	
205		5440MDA205F		5440MDA205M		5440MDB205F		5440MDB205M		5440E205F		5440E205M	
209		5440MDA209F		5440MDA209M		5440MDB209F		5440MDB209M		5440E209F		5440E209M	
212		5440MDA212F		5440MDA212M		5440MDB212F		5440MDB212M		5440E212F		5440E212M	
219		5440MDA219F		5440MDA219M		5440MDB219F		5440MDB219M		5440E219F		5440E219M	
293		5440MDA293F		5440MDA293M		5440MDB293F		5440MDB293M		5440E293F		5440E293M	
295		5440MDA295F		5440MDA295M		5440MDB295F		5440MDB295M		5440E295F		5440E295M	
327		5440MDA327F		5440MDA327M		5440MDB327F		5440MDB327M		5440E327F		5440E327M	

Inserts

Insert Representation	103 3 1000V/5A or 10A		105 5 630V/5A or 10A		107 7 630V/5A or 10A		203 3 1000V/25A		205 5 800V/25A		209 9 630V/5A or 10A	
Inserts Shown from the Plug Mating Side												
Inserts Shown from the Plug Mating Side												
Insert Contacts Rating	212 12 630V/5A or 10A		219 19 630V/5A or 10A		293 3 1000V/15A		295 5 1000V/15A		327 27 630V/5A or 10A			

Crimp Contacts

Machined Contacts					Stamped Contacts				
Part Numbers		Wire Ø Max	Contacts /Package	Current	Part Numbers		Wire Ø Max	Contacts /Package	Current
Pins	Sockets				Pins	Sockets			
5440020M100	5440020F100	2.6	100	10A	5440220M100	5440220F100	1.52	100	5A
5440016M100	5440016F100	3.2		15A	5440320M100	5440320F100	1.02		
5440012M100	5440012F100	4.5		25A	Consult representative for Crimp Toll requirements. Contacts on Strips available.				

Accessories

Accessories		Caps						
	For Receptacles			For Plugs				
	Shell Size	Part Number	Shell Size	Part Number				
	1	54401BE	1	54401BM				
	2	54402BE	2	54402BM				
	3	54403BE	3	54403BM				
	Part Number	Shell	Description	Description	Shell	Part Number		
	5440JT01	1	O Ring Seal for Receptacles	Insert/Extract Tool to Disconnect Insert and Extract Contacts	1	5440OT01		
	5440JT02	2			2	5440OT02		
	5440JT03	3			3	5440OT03		

AirLB

Current indicated as maximum/contact at 40°C. IP67

ECTA 133 Metal Circular Push-Pull IP67 Connector System

Materials

Shells	– Aluminum Alloy
Shell Plating	– Nickel
Locking Ring	– Black Anodized
Contacts	– Copper Alloy
Contact Plating	– Gold over Nickel
Inserts	– Fiber Glass UL94-V0

Also Available

Terminations	– Crimp and PCB
Polarization	– 4 Positions
Shells	– Various <i>next page</i>
Other	– Fibre Optic Inserts

Mechanical

Temp Range	– -40°C ~ 125°C
Durability	– 1000 Cycles



















Related Information

Full Catalogue	– ECTA 133
Accessories	– Next Page
Tools	– Catalogue ECTA 133

Connector Solutions below are Solder Terminated Standard Polarization (for Crimp replace 'Z' with 'S' and for PCB with 'Y')




Plug ØD		Mating Halves (Plug mates with any one type of Receptacle. If Plug has Pins, Receptacle must have Sockets)							
Shell	mm	Receptacle				Requires Backshell		Plug	
0	15								
1	20								
2	24								
3	26								
4	30.5								
5	36								
6	49.8								
7	56.2								
Inserts		Square Flange		Jam Nut		In-Line		In-Line	
Power	Signal	Sockets	Pins	Sockets	Pins	Sockets	Pins	Sockets	Pins
	003	1332E003FZ	1332E003MZ	1332EV003FZ	1332EV003MZ	1332P003FZ	1332P003MZ	1332M003FZ	1332M003MZ
	006	1332E006FZ	1332E006MZ	1332EV006FZ	1332EV006MZ	1332P006FZ	1332P006MZ	1332M006FZ	1332M006MZ
	103	1332E103FZ	1332E103MZ	1332EV103FZ	1332EV103MZ	1332P103FZ	1332P103MZ	1332M103FZ	1332M103MZ
103		1331E103FZ	1331E103MZ	1331EV103FZ	1331EV103MZ	1331P103FZ	1331P103MZ	1331M103FZ	1331M103MZ
	107	1332E107FZ	1332E107MZ	1332EV107FZ	1332EV107MZ	1332P107FZ	1332P107MZ	1332M107FZ	1332M107MZ
193		1331E193FZ	1331E193MZ	1331EV193FZ	1331EV193MZ	1331P193FZ	1331P193MZ	1331M193FZ	1331M193MZ
	204	1332E204FZ	1332E204MZ	1332EV204FZ	1332EV204MZ	1332P204FZ	1332P204MZ	1332M204FZ	1332M204MZ
205		1331E205FZ	1331E205MZ	1331EV205FZ	1331EV205MZ	1331P205FZ	1331P205MZ	1331M205FZ	1331M205MZ
	212	1332E212FZ	1332E212MZ	1332EV212FZ	1332EV212MZ	1332P212FZ	1332P212MZ	1332M212FZ	1332M212MZ
295		1331E295FZ	1331E295MZ	1331EV295FZ	1331EV295MZ	1331P295FZ	1331P295MZ	1331M295FZ	1331M295MZ
303		1331E303FZ	1331E303MZ			1331P303FZ	1331P303MZ	1331M303FZ	1331M303MZ
	319	1332E319FZ	1332E319MZ			1332P319FZ	1332P319MZ	1332M319FZ	1332M319MZ
405		1331E405FZ	1331E405MZ			1331P405FZ	1331P405MZ	1331M405FZ	1331M405MZ
	426	1332E426FZ	1332E426MZ			1332P426FZ	1332P426MZ	1332M426FZ	1332M426MZ
	541	1332E541FZ	1332E541MZ			1332P541FZ	1332P541MZ	1332M541FZ	1332M541MZ
605		1331E605FZ	1331E605MZ			1331P605FZ	1331P605MZ	1331M605FZ	1331M605MZ
706		1331E706FZ	1331E706MZ			1331P706FZ	1331P706MZ	1331M706FZ	1331M706MZ

Inserts

Insert Representation Inserts Shown from the Plug Mating Side						
Inserts Contacts Rating	003 3 500V/7.5A	006 6 320V/5A	103 3 500V/10A	103 2+PE 1000V/13A	107 7 500V/7.5A	193 2+PE 800V/13A
Insert Representation Inserts Shown from the Plug Mating Side						
Inserts Contacts Rating	204 4 500V/25A	205 4+PE 800V/13A	212 12 500V/7.5A	295 4+PE 800V/13A	303 2+PE 1000V/40A	319 19 500V/7.5A
Insert Representation Inserts Shown from the Plug Mating Side						
Inserts Contacts Rating	405 4+PE 1000V/13A	426 26 500V/7.5A	541 41 500V/7.5A	605 2+PE x 100A/2 x 10A 1000V	706 4+PE x 125A/1 x 10A 1000V	

AirLB
Current indicated as maximum/contact at 40°C. IP67 Rating dependant on Backshell
The following Inserts are not compatible: Power 103 and Signal 103; Signal 103 and 193; 205 and 295

ECTA 133 Metal Circular Push-Pull IP67 Connector System Accessories

Backshell IP67				IP67 Backshell				
	Part Number	Shell	Cable Ø (mm)		Part Number	Shell	Cable Ø (mm)	
	1330 0 P2	0	4.5~6		1330 1 P3	1	9~12.5	
	1330 1 P1	1	5~6.5		1330 2 P3	2	11.5~14.5	
	1330 1 P2	1	6.5~9		1330 3 P2	3	12.5~15	
	1330 2 P1	2	8~10		1330 3 P3	3	15~18	
	1330 2 P2	2	10~13.5		1330 4 P1	4	15~18	
	1330 3 P1	3	10.5~12.5		1330 4 P2	4	18~21	
Backshell IP67 with Braid Clamping and Cable Clamp				Backshell IP67 with Braid Clamping				
	Part Number	Shell	Cable Ø (mm)		Part Number	Shell	Cable Ø (mm)	
	1330 1 PES 1	1	5.5~9		1330 0 PEM	0	2.5~5	
	1330 1 PES 2	1	9~12		1330 1 PEM	1	8~13	
	1330 2 PES 1	2	5.5~9		1330 2 PEM	2	8~13	
	1330 2 PES 2	2	9~12		1330 3 PEM	3	13~18	
	1330 3 PES 1	3	10~18		1330 4 PEM	4	13~ 18	
	1330 4 PES 1	4	10~ 18					
Adapter with Metric Thread				Backshell IP30 with Cable Clamp				
 The PM Adapter is designed for use on any standard backshell with metric thread (to IP67)	Part Number	Shell	Thread		Part Number	Shell	Cable Ø (mm)	
	1330 0 PM 12	0	M12 x 1,5		1330 1 DS 1	1	2~6	
	1330 1 PM 16	1	M16 x 1,5		1330 1 DS 2	1	7~10	
	1330 1 PM 20	1	M20 x 1,5		1330 1 DS 3	1	10~13	
	1330 2 PM 16	2	M16 x 1,5		1330 2 DS 2	2	10.5~14	
	1330 2 PM 20	2	M20 x 1,5		1330 2 DS 3	2	14~17.5	
	1330 3 PM 20	3	M20 x 1,5		1330 3 DS 1	3	12.5~14.5	
	1330 3 PM 25	3	M25 x 1,5		1330 3 DS 2	3	14.5~18	
	1330 4 PM 20	4	M20 x 1,5		1330 4 DS 0	4	11.75~15.5	
	1330 4 PM 25	4	M25 x 1,5		1330 4 DS 1	4	15.5~18	
	1330 5 PM 25	5	M25 x 1,5		1330 4 DS 2	4	18~ 21.5	
	1330 6 PM 32	6	M32 x 1,5		Also available: 90°Adapter for plug and cable-cable plug extension			
	1330 7 PM 50	7	M50 x 1,5					
Metal Cap for All Receptacles (IP67)			Metal Cap for Plug (IP67)			Flange Seal		
	Part Number	Shell		Part Number	Shell		Part Number	Shell
	1330 0 BE	0		1330 0 BM	0		1330 0 JE	0
	1330 1 BE	1		1330 1 BM	1		1330 1 JE	1
	1330 2 BE	2		1330 2 BM	2		1330 2 JE	2
	1330 3 BE	3		1330 3 BM	3		1330 3 JE	3
	1330 4 BE	4		1330 4 BM	4		1330 4 JE	4
	1330 5 BE	5		1330 5 BM	5		1330 5 JE	5
Also available upon request, a single hole fixing bulkhead with pressure differentials up to 5 bars. The technical characteristics are identical to those of standard connectors.						1330 6 JE	6	
						1330 7 JE	7	

Also available upon request, a single hole fixing bulkhead with pressure differentials up to 5 bars.
The technical characteristics are identical to those of standard connectors.

SOCAPEX™ SL61 19 Contact Lighting Connectors

Amphenol's SOCAPEX connector is accepted as a worldwide standard in the Lighting Industry

Materials

Body - Aluminium Alloy
Inserts - Alkyde
Contacts - Machined Gold Plated

Electrical





Working Voltage - 400V
Current - 25A

Configuration

Number of Contacts - 19
Coupling Nut - Threaded
Backshell - Two Piece
Cable Clamp - Adaptable
Termination - Solder
Temperature Range - -40°C ~ 85°C

Also Available

- Right Angle Versions
- Various Shell Sizes and Contacts
- Cap Accessories
- Crimp Versions
- Earth Protection
- Cadmium-Free Versions

Part Number	SLFMD419AR	SLFFDR419AR	SLEME419AR	SLEF419AR
Description	Cable Pin Plug	In-Line Socket Receptacle	Panel Pin Plug	Panel Socket Receptacle
Representation				
Diagram				

AirLB/ASF-T