


PIN RECEPTACLES

FOR .025" - .037" DIAMETER PINS AND .025" SQUARE PINS

0401/6401

X401-0-15-XX-47-XX-04-0

Press-fit in .064 mounting hole




Basic Part Number	Length A
0401-0	.340
6401-0	.540

1303

1303-0-15-XX-47-XX-04-0


Press-fit in .061 mounting hole



8303

8303-0-15-XX-47-XX-04-0


Press-fit in .061 mounting hole



4095

4095-0-15-XX-47-XX-04-0

Press-fit in .061 mounting hole



8806


8806-0-18-XX-47-XX-40-0

Surface mount


Also available on 12mm wide carrier tape:

4,000 parts per 13" reel

Order as: 8806-0-58-XX-47-XX-10-0



P.C.B. Layout



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - 47 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ 80 200 μ " TIN OVER NICKEL (RoHS)

◆ 15 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ 80 200 μ " TIN OVER NICKEL (RoHS)

◆ 27 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#47 CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com