

EXAMINED BY :	EMERGING DISPLAY TECHNOLOGIES CORPORATION	FILE NO . CAS-50342						
<i>Vincent Uh</i>		ISSUE : OCT.25,2002						
APPROVED BY:		TOTAL PAGE : 1 0						
<i>Roger Yang</i>		VERSION : 4						
<table border="1"><thead><tr><th>CUSTOMER</th><th>ACCEPTANCE</th><th>SPECIFICATIONS</th></tr></thead><tbody><tr><td colspan="3"> MODEL NO. : <u>EG 6 4 E 0 0 B C W U</u> FOR MESSRS : _____ CUSTOMER'S APPROVAL DATE : _____ BY : _____ </td></tr></tbody></table>			CUSTOMER	ACCEPTANCE	SPECIFICATIONS	MODEL NO. : <u>EG 6 4 E 0 0 B C W U</u> FOR MESSRS : _____ CUSTOMER'S APPROVAL DATE : _____ BY : _____		
CUSTOMER	ACCEPTANCE	SPECIFICATIONS						
MODEL NO. : <u>EG 6 4 E 0 0 B C W U</u> FOR MESSRS : _____ CUSTOMER'S APPROVAL DATE : _____ BY : _____								

EMERGING DISPLAY
TECHNOLOGIES CORPORATION

MODEL NO.

E G 6 4 E 0 0 B C W U

VERSION

4

RECORDS OF REVISION

DOC . FIRST ISSUE

NOV.5,1994

D A T E	REVISED DRAWING NO.	S U M M A R Y																			
APR.28,'95	1	(2)MODULE SIZE 273.0W*142.0H*20.0D CHANGE TO 273.0W*141.0H*20.0D																			
	3	SYMBOL	MIN	TYP	MAX																
		VEE-VSS		-20.5	-21.0	-21.5															
		CHANGE TO																			
		VEE-VSS		—	-19.0	—															
		SYMBOL	CONDITION	MIN	TYP	MAX															
		VDD-VO		Ta=10℃	—	—	26.5														
JUL.15,2002	2			Ta=25℃		—	23.5	—													
				Ta=40℃		20.4	—	—													
		CHANGE TO																			
	3	VDD-VO		Ta=10℃	—	22.5	—														
				Ta=25℃		—	21.5	—													
				Ta=40℃		—	20.5	—													
		7. OUTLINE DIMENSION REVISE THE WHOLE PAGE																			
3.2 ENVIRONMENTAL ABSOLUTE MAXIMUM RATINGS	<table><tr><td rowspan="2">I T E M</td><td colspan="2">OPERATING</td><td colspan="2">STORAGE</td><td rowspan="2">COMMENT</td></tr><tr><td>MIN.</td><td>MAX.</td><td>MIN.</td><td>MAX.</td></tr><tr><td>AMBIENT TEMPERATURE</td><td>10℃</td><td>40℃</td><td>-20℃</td><td>60℃</td><td>NOTE (2) (3) →</td></tr></table>					I T E M	OPERATING		STORAGE		COMMENT	MIN.	MAX.	MIN.	MAX.	AMBIENT TEMPERATURE	10℃	40℃	-20℃	60℃	NOTE (2) (3) →
	I T E M	OPERATING		STORAGE			COMMENT														
		MIN.	MAX.	MIN.	MAX.																
	AMBIENT TEMPERATURE	10℃	40℃	-20℃	60℃	NOTE (2) (3) →															
	<table><tr><td rowspan="2">I T E M</td><td colspan="2">OPERATING</td><td colspan="2">STORAGE</td><td rowspan="2">COMMENT</td></tr><tr><td>MIN.</td><td>MAX.</td><td>MIN.</td><td>MAX.</td></tr><tr><td>AMBIENT TEMPERATURE</td><td>0℃</td><td>50℃</td><td>-20℃</td><td>60℃</td><td>NOTE (2) (3)</td></tr></table>					I T E M	OPERATING		STORAGE		COMMENT	MIN.	MAX.	MIN.	MAX.	AMBIENT TEMPERATURE	0℃	50℃	-20℃	60℃	NOTE (2) (3)
I T E M	OPERATING		STORAGE		COMMENT																
	MIN.	MAX.	MIN.	MAX.																	
AMBIENT TEMPERATURE	0℃	50℃	-20℃	60℃	NOTE (2) (3)																
4. ELECTRICAL CHARACTERISTICS																					
RECOMMENDED LCD DRIVING VOLTAGE :																					
Ta = 10℃ → 0℃ , Ta = 40℃ → 50℃																					
10	11.2 POWER SUPPLY FOR CCFL BACK-LIGHT																				
	RECOMMENDED INVERTER : 1A-EM02A1(EMERGING DISPLAY) → RECOMMENDED INVERTER : CXA-M10M-L (TDK)																				
OCT.25,2002	9	10. INTERFACE SIGNALS																			
		PIN NO	SYMBOL	LEVEL	FUNCTION																
		5	VO	—	OPERATING VOLTAGE FOR LCD DRIVING																
		↓																			
		8	VEE	—	POWER SUPPLY FOR LCD DRIVING																
		↓																			
		5	VEE	—	POWER SUPPLY FOR LCD DRIVING																
		↓																			
		8	VO	—	OPERATING VOLTAGE FOR LCD DRIVING																

TABLE OF CONTENTS

NO.	ITEM	PAGE
=====		
1.	GENERAL SPECIFICATIONS -----	1
2.	MECHANICAL SPECIFICATIONS -----	1
3.	ABSOLUTE MAXIMUM RATINGS -----	2
4.	ELECTRICAL CHARACTERISTICS -----	3
5.	TIMING CHARACTERISTICS -----	4~5
6.	OPTICAL CHARACTERISTICS -----	6
7.	OUTLINE DIMENSION -----	7
8.	BLOCK DIAGRAM -----	8
9.	DETAIL DRAWING OF DOT MATRIX -----	9
10.	INTERFACE SIGNALS -----	9
11.	POWER SUPPLY -----	10

1. GENERAL SPECIFICATIONS

1.1 GENERAL SPECIFICATIONS

PLEASE REFER TO :

CUSTOMER ACCEPTANCE STANDARD SPECIFICATIONS :

E U - 0 0 1 A

1.2 THIS INDIVIDUAL SPECIFICATION IS PRIOR TO GENERAL SPECIFICATIONS.

2. MECHANICAL SPECIFICATIONS

- (1) NUMBER OF DOTS ----- 640W * 200H DOTS
- (2) MODULE SIZE ----- 273.0W * 141.0H * 20.0D mm
- (3) EFFECTIVE AREA ----- 232.0W * 106.0H mm
- (4) ACTIVE AREA ----- 223.97W * 97.97 H mm
- (5) DOT SIZE ----- 0.32 W * 0.46 H mm
- (6) DOT PITCH ----- 0.35W * 0.49H mm
- (7) LCD TYPE ----- STN , BLUE , TRANSMISSIVE,NEGATIVE
- (8) DRIVING METHOD ----- 1 / 200 DUTY MULTIPLEX DRIVE
- (9) VIEWING DIRECTION ----- 12 O'CLOCK
- (10) BACK- LIGHT ----- CCFL

3. ABSOLUTE MAXIMUM RATINGS

3.1 ELECTRICAL ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	MIN .	MAX .	UNIT	COMMENT
POWER SUPPLY FOR LOGIC	VDD – VSS	0	6 . 0	V	
POWER SUPPLY FOR LCD DRIVING	VDD – VEE	0	27 . 0	V	
INPUT VOLTAGE	VI	VSS	VDD	V	
STATIC ELECTRICITY	—	—	1 0 0	V	NOTE (1)

NOTE (1) : TEST METHOD AND CONDITIONS :

AFTER CHARGING UP 200 PF CAPACITOR BY STATED VOLTAGE ,
THE CAPACITOR IS CONNECTED WITH INTERFACE PINS OF THE
MODULE .

3.2 ENVIRONMENTAL ABSOLUTE MAXIMUM RATINGS.

I T E M	OPERATING		STORAGE		COMMENT
	MIN .	MAX .	MIN .	MAX .	
AMBIENT TEMPERATURE	0 °C	5 0 °C	- 2 0 °C	6 0 °C	NOTE (2) (3)
HUMIDITY	—	8 5 % RH	—	8 5 % RH	WITHOUT CONDENSATION
VIBRATION	—	2.45 m / s ² (0 . 25 G)	—	11.76 m / s ² (1 . 2 G)	10~100 HZ XYZ DIRECTIONS 1 Hr . EACH
SHOCK	—	29.4 m / s ² (3 G)	—	490.0 m / s ² (5 0 G)	1 Mseconds XYZ DIRECTIONS 1 TIME EACH
CORROSIVE GAS	NOT ACCEPTABLE		NOT ACCEPTABLE		

NOTE (2) : Ta AT -20°C : 48HR MAX .

60°C : 48HR MAX .

NOTE (3) : BACKGROUND COLOR CHANGES SLIGHTLY DEPENDING ON AMBIENT
TEMPERATURE THIS PHENOMENON IS REVERSIBLE .


4. ELECTRICAL CHARACTERISTICS

Ta = 25 °C			VDD = 5.0 V			
PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
POWER SUPPLY VOLTAGE FOR LOGIC	VDD-VSS	—	4.75	5.0	5.25	V
POWER SUPPLY VOLTAGE FOR LCD DRIVE	VEE-VSS	—	—	-19.0	—	V
INPUT VOLTAGE NOTE (1)	VIH	H LEVEL	0.8*VDD	—	—	V
	VIL	L LEVEL	—	—	0.2*VDD	V
POWER SUPPLY CURRENT FOR LOGIC	IDD	VDD - VSS = 5.0 V VEE - VSS = -19.0	—	9	—	mA
POWER SUPPLY CURRENT FOR LCD DRIVE	IEE	VDD - VSS = 5.0 V VEE - VSS = -19.0	—	8	—	mA
RECOMMENDED LCD DRIVING VOLTAGE NOTE (2)	VDD - VO Ø = 10 ° θ = 180 °	Ta = 0 °C	—	22.5	—	V
		Ta = 25 °C	—	21.5	—	V
		Ta = 50 °C	—	20.5	—	V
FLM FREQUENCY	f FLM	—	70	75	80	HZ
POWER SUPPLY FOR CCFL	VOLTAGE	VCCFL	—	300	—	Vrms
	FREQUENCY	f CCFL	—	30K	—	HZ
	CURRENT	IL	—	5	—	mA

NOTE (1): APPLIED TO TERMINALS M, FLM, CL1, CL2, UD0~UD3, DISPOFF .


NOTE (2): RECOMMENDED LCD DRIVING VOLTAGE MAY FLUCTUATE ABOUT
± 1.0V BY EACH MODULE .

5. TIMING CHARACTERISTICS
5.1 INTERFACE TIMING



5.2 SWITCHING CHARACTERISTICS

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Frequency of maximum clock	fcp	—	—	8	MHZ
CL1 , CL2 , pulse width	tw	45	—	—	ns
Rise , fall time	tr,tf	—	—	30	ns
Data setup time	tDSU	20	—	—	ns
Data hold time	tDHD	20	—	—	ns
CL1 setup time	tLSU	80	—	—	ns
CL1 → CL2 time	tLC	80	—	—	ns
FLM setup time	tsetup	100	—	—	ns
FLM hold time	thold	100	—	—	ns
M delay time	tDF	—	—	300	ns



6. OPTICAL CHARACTERISTICS

Ta = 25 °C

VDD = 5.0 V

VDD - VO = 21.5 V

I T E M	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT	NOTE
VIEWING AREA	Ø 2 - Ø 1	K ≥ 2.0	40	—	—	deg.	1
CONTRAST RATIO	K	Ø = 10 ° θ = 180 °	—	5	—	—	1
RESPONSE TIME	tr(rise)	Ø = 10 ° θ = 180 °	—	250	—	ms	1
	tf(fall)	Ø = 10 ° θ = 180 °	—	350	—	ms	1
BRIGHTNESS OF BACKLIGHT	B	—	—	30	—	cd / m ²	1
RISE TIME OF BACKLIGHT	TC	—	—	3	—	MINUTE	
BRIGHTNESS UNIFORMITY	—	—	—	—	± 20	%	2

NOTE (1) : PLEASE REFER TO :


CUSTOMER ACCEPTANCE STANDARD SPECIFICATIONS. (EU - 001A)

NOTE (2) : BRIGHTNESS UNIFORMITY IS DEFINED AS FOLLOWING


$$\sum_X = \left[\frac{(\text{MAXIMUN BRIGHTNESS OR MINIMUN BRIGHTNESS}) - \text{AVERAGE BRIGHTNESS}}{\text{AVERAGE BRIGHTNESS}} \right] \times 100\%$$

NOT SPECIFIED TOLERANCE IS ± 0.4

8. BLOCK DIAGRAM



9. DETAIL DRAWING OF DOT MATRIX



UNIT : mm
SCALE : NTS
NOT SPECIFIED TOLERANCE IS ± 0.1

10. INTERFACE SIGNALS

IF1 :


PIN NO	SYMBOL	LEVEL	FUNCTION
1	FLM	H	THE FLM SIGNAL INDICATING THE BEGINNING OF EACH DISPLAY CYCLE
2	CL1	H $\rightarrow$ L	DISPLAY DATA LATCH
3	CL2	H $\rightarrow$ L	DISPLAY DATA SHIFT
4	M	H / L	CONTROL SIGNAL FOR AC DRIVING
5	VEE	—	POWER SUPPLY FOR LCD DRIVING
6	VDD	—	POWER SUPPLY FOR LOGIC CIRCUIT
7	VSS	—	GROUND
8	VO	—	OPERATING VOLTAGE FOR LCD DRIVING
9	D0	H / L	DISPLAY DATA
10	D1	H / L	
11	D2	H / L	
12	D3	H / L	
13~16	NC	—	NO CONNECTION

IF2 :

INTERFACE	PIN	SINGAL	VEVEL	FUNCTION
CCFL	1	VCCFL	—	POWER SUPPLY FOR CCFL DRIVING
	2~5	NC	—	NO CONNECTION
	6	VCCFL	—	POWER SUPPLY FOR CCFL DRIVING

11. POWER SUPPLY


11.1 POWER SUPPLY FOR LCM



VDD - V0 : LCD DRIVING VOLTAGE

VR : 100K Ω ~ 200K Ω

11.2 POWER SUPPLY FOR CCFL BACK - LIGHT



RECOMMENDED INVERTER : CXA-M10M-L (TDK)

11.3 TIMING OF POWER SUPPLY AND INTERFACE SIGNAL

